

Asset Tracking Internal Antenna

1575 MHz|GPS



COMPACT ANTENNA IS IDEAL FOR COVERT INSTALLATIONS

The Internal GPS antenna enables direction and location information in a compact housing. The antenna measures only 63.5 x 63.5 x 13 mm, allowing covert installation into vehicle interiors. It performs well with or without a ground plane.

Laird Technologies is a leading supplier of mobile antenna solutions for automotive, asset tracking and consumer electronics industries. Products include cellular antennas (AMPS, GSM/DCS/PCS, UMTS), GPS antennas, entertainment antennas (AM/FM, DAB, DVB-T, Satellite radio, TV), mobile communication antennas (Bluetooth, DSRC, RKE, TPMS, WiFi), satellite communication antennas and battery packs.

Leveraging our experience in M2M wireless modules, Laird Technologies also designs smart antennas integrating functionalities such as cellular, WiFi and Bluetooth® modems, GPS receivers and vehicle networking. All of these capabilities can be further integrated into M2M Devices, that add control electronics and firmware to provide the latest evolution in telematics systems.

FEATURES

- High gain antenna for excellent satellite reception
- Compact, ideally suited for stealth applications
- Built-in ground plane to increase mounting flexibility
- Can be combined with Cellular Blade antenna (part # 637109)

BENEFITS

- Low total-cost implementation
- Easy installation
- Easy concealment
- Small package size
- Meets enhanced environmental specifications
- Ground plane independent

APPLICATIONS

- General automotive aftermarket
- Fleet logistics, tracking, and diagnostics
- Theft protection
- Vehicle and asset recovery
- Navigation systems
- Infotainment systems
- On-board computing

global solutions: local support™

Americas: +810.695.9810
Europe: +44.1628.858.940
Asia: +852.2268.6567

www.lairdtech.com



Innovative **Technology**
for a **Connected** World

Asset Tracking Internal Antenna

1575 MHz|GPS

Internal GPS

GPS

ANTENNA SPECIFICATION

Frequency Range	1574.42 -1576.42 MHz
Peak Gain	4.5 dBic @ Boresight
Polarization	RHCP
Impedance	50 Ω
Output VSWR (Min. Performance)	$\leq 2:1$

LNA SPECIFICATION

Gain (Max)	28 dB
Noise Figure	≤ 1.5 dB
Supply Voltage	3.3 ± 0.3 V
Current	12 mA
Input P1dB	≥ -27 dBm
Output VSWR	$\leq 2:1$

MECHANICAL SPECIFICATION

Dimension	63.5 x 63.5 x 13 mm
Radome Material	Cyclopy
Connector	SMA
Cable Length	4000 mm
Cable Type	RG-174
Mounting Method	Hook and Loop, Adhesive

ENVIRONMENTAL SPECIFICATION

Operating Temperature	-40°C to +85°C
Humidity	Operation 95% RH at 65°C
Ingress Protection	IP-50
Drop Test / Shock	50 g shocks 10x3 axis / 1 meter drop 6 axis
Vibration	10-1000 Hz vibration 1 hour 3 axis

ORDERING INFORMATION

Part Number	637108
Customization available w/MOQ	Cable type, length, connector type, mounting style

Order with 637109
for a combination
GPS/Cellular solution.
Part #637110.



TEL-DS-INTERNAL GPS 1210

Any information furnished by Laird Technologies, Inc. and its agents is believed to be accurate and reliable. Responsibility for the use and application of Laird Technologies materials rests with the end user, since Laird Technologies and its agents cannot be aware of all potential uses. Laird Technologies makes no warranties as to the fitness, merchantability or suitability of any Laird Technologies materials or products for any specific or general uses. Laird Technologies shall not be liable for incidental or consequential damages of any kind. All Laird Technologies products are sold pursuant to the Laird Technologies' Terms and Conditions of sale in effect from time to time, a copy of which will be furnished upon request. © Copyright 2010 Laird Technologies, Inc. All Rights Reserved. Laird, Laird Technologies, the Laird Technologies Logo, and other marks are trademarks or registered trademarks of Laird Technologies, Inc. or an affiliate company thereof. Other product or service names may be the property of third parties. Nothing herein provides a license under any Laird Technologies or any third party intellectual property rights.