

10112684 - X XX-YY Z LF

SEE NOTE 4

INDICATES THAT PRODUCT IS RoHS COMPATIBLE, SEE NOTE 3

PACKAGING :

A = Tape and reel with Pick-up cap.
See GS-14-1516 As available




U = Tube without Pick-up cap.
Only for contacts qty from 4 to 25.
See GS-14-1551

Blank = Bli box for contacts qty 2 and 3
See note 5


CONTACTS QTY : 02 to 25 = N

STYLE	01	02	03
DIM C POST LENGTH	3.2	2.0	4.0

PLATING : G= 0.76 μ Gold/GXT on mating area
2-6 μ Pure Tin on solder area
F= Gold flash on mating area
2-6 μ pure Tin on solder area
T= 2-6 μ pure Tin on mating area
2-6 μ pure Tin on solder area
All with 1.27 Ni underplating



VIEW WITH
PICK-UP CAP
SCALE 4:1



NOTES :

1- MATERIALS :

BODY : High Temp thermoplastic 30% GF, COLOR BLACK UL94 V-0
PIN : COPPER ALLOY

2- 7N MIN PIN RETENTION IN EITHER DIRECTION

3- RoHS COMPATIBLE PRODUCT SPECIFICATION :

a- PLATING : LF means the product is Lead Free,
2 μ MIN matte Tin over 1.27 μ Nickel underplating.

b- MANUFACTURING PRODUCT SPECIFICATION :

Housing will withstand exposure to 260 $^{\circ}$ C peak temperature for 30 secondes in a convection infra-red or vapor phase oven.

c- LABELLING :

Meets packaging specs as per GS-14-920

d- LEGAL STATMENT : See GS-47-0004

4- ONE TIP OF BODY MIGHT BE WITHOUT INDENTS AS PER EXTREMITY OF MOLDED BODY.

5- MINIMUM QUANTITY IN BLI BOX : 500

spec ref		GS-12-652			dr		A Parrenin		2014/02/28		projection		mm		size		A3		scale		8:1		
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED			eng		A Parrenin		2014/03/18						ecn no		ELX-B-17233-1						
ISO 406																							
ISO 1101																							
					chr		D Conveycey		2014/03/19								rel level						
					appr		Gert Drosbeke		2014/03/21				product family				Released						
surface		-		linear		0.X		±0.30				title		UNSHROUDED HEADER SMT		dwg no		10112684C		rev		D	
				0.XX		±0.13																	
				0.XXX		±0.05																	
				angular		0°		±1°															
ISO 1302						www.fci.com		cat. no.		-		Product - Customer Drw				sheet 1 of 1							