





Rev	AWO #	Description	Date	Appr
-		RELEASED	11/16/04	

APPROVED: _____
DATE: _____ TITLE: _____



SPECIFICATION:
Material:
Insulator: PBT, glass reinforced, rated UL-94V-0
Insulator Color: Black
Contacts: Brass
Contact Plating:
Gold Flash over Nickel underplate on contact area, Tin over Copper underplate on solder tails
Electrical:
Operating Voltage: 250V AC max.
Current rating: 1 Amps max.
Contact resistance: 20 mohms max
Insulation resistance: 5000 Mohms min
Dielectric withstanding voltage: 1000 VAC / minute
Mechanical:
Mating durability: 500 cycles min.
Temperature Rating:
Operating temperature: -40° TO +105°

A

6

A

6

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES				ADAM TECH 909 Railway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710			
X ± .10 .XX ± .020 .XXX ± .015		HOLES Ø X ± .10 Ø XX ± .015 Ø XXX ± .010		TITLE BOX HEADER, VERTICAL PCB MOUNT, 2 ROW .100 PITCH, SELECTIVE GOLD			
APPROVALS		DATE					
DRAWN	SS	11/16/04					
CHECKED				SIZE		PART NO.	
APPROVED				X		BHR-XX-VSGA	
REF:		SCALE: NTS		SHEET 1 OF 1		REV: -	

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

BHR-XX-VSGA

SCALE: NTS

SHEET 1 OF 1