



THIS DOCUMENT CONTAINS DATA PROPRIETARY TO PROJECTS UNLIMITED, INC. ANY USE OR REPRODUCTION, IN ANY FORM, WITHOUT PRIOR WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC. IS PROHIBITED.
© 2003, Projects Unlimited Inc.

SPECIFICATIONS

PARAMETERS	VALUES	UNITS
RATED INPUT POWER	1.0	W
MAX INPUT POWER	2.0	W
IMPEDANCE	4±15%	OHM
OUTPUT SPL @ 1.0W/1M (AT 600, 800, 1,000, 1,200 Hz)	80±3	dBA
DISTORTION	5%	—
RESONANT FREQUENCY	500±20%	Hz
FREQUENCY RANGE	500 ~ 20,000	Hz
HOUSING MATERIAL	METAL	—
CONE MATERIAL	MYLAR	—
MAGNET MATERIAL	N35	—
OPERATING TEMPERATURE	-20 ~ +50	°C
WEIGHT	6.5	grams



NOTES:

- ALL DIMENSIONS ARE IN MILLIMETERS.
- SPECIFICATION SUBJECT TO CHANGE OR WITHDRAWAL WITHOUT NOTICE.

FILE NAME
AS2804-72.DWG

REVISIONS

LTR	DESCRIPTION	DATE	APPROVED
—	RELEASED FROM ENGINEERING	11/21/03	
A	REVISED TO NEW TEMPLATE	4/14/04	R. W.

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN
MILLIMETERS, TOLERANCES ARE ±0.5 AND
ANGLES ARE ±3°.

APPROVALS	DATE
DRAWN <i>R. A. C.</i>	11/03
APPROVED <i>E. P.</i>	11/03
DO NOT SCALE DRAWING	



projects®
unlimited

Dayton , Ohio

DYNAMIC SPEAKER
AS2804-72

SIZE
A

DRAWING NO.
AS2804-72

SCALE: N.T.S.

SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[PUI Audio:](#)

[AS2804-72](#)