


Digital Calipers

Roebuck



Calipers have hardened stainless steel frame and measuring jaws, depth rod, thumbroll adjustment and knurled locking screw. 3 button operation: On/Off: Inch/Metric conversion. Zero in any position.

Accuracy  
±0.02mm < 100mm  
±0.03mm > 100 - 200mm  
±0.04mm > 200 - 300mm

489576

| Capacity (mm) | Capacity (in) | Resolution      | External Jaw | Internal Jaw | Order Code | Price Each |
|---------------|---------------|-----------------|--------------|--------------|------------|------------|
| 150           | 6             | 0.01mm/0.0005in | 40mm         | 18mm         | 137-5863   |            |
| 200           | 8             | 0.01mm/0.0005in | 50mm         | 20mm         | 137-5864   |            |
| 300           | 12            | 0.01mm/0.0005in | 60mm         | 20mm         | 137-5865   |            |