

## 4 outlet, Direct plug-in, 670 joule - Protect It! Surge Suppressor

MODEL NUMBER: **TLP4BK**



### Description

The TLP4BK Surge Suppressor from Tripp Lite has 4 side-mounted outlets (including 2 transformer-friendly outlets), a convenient direct plug-in design and diagnostic LEDs. The unit has a surge suppression rating of 670 joules to handle the strongest surges. \$10,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

### Features

- 4 side-mounted outlets allows easier plug connection and removal (including 2 transformer-friendly outlets)
- Direct plug-in design converts two outlets into four by plugging in to any wall outlet
- Surge suppression rating: 670 joules
- EMI/RFI noise filtering
- Diagnostic LEDs indicate protection present & ground present
- \$10,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only) covers connected equipment

### Specifications

General Info	
Product Group	SURGE PROTECTORS
OVERVIEW	
Intended Application	Home/Office
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Circuit Breaker (amps)	15

### Highlights

- 4 side-mounted outlets (including 2 transformer-friendly outlets)
- Direct plug-in design
- 670 joule rating
- Diagnostic LEDs
- \$10,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

### Applications

- Computers, printers/peripherals, home electronics (stereos, TV, DVD player, etc.), satellite systems, appliances, power tools, lighting and more

### Package Includes

- TLP4BK Surge Suppressor
- Instruction manual with warranty information

Outlet Quantity / Type	4 NEMA 5-15R
Number of Outlets	4
Transformer Accommodation	Accommodates 2 transformers
Outlet Orientation	Side-mounted
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Connection Type	NEMA 5-15P
Input Cord Length Details	Direct plug-in
Voltage Compatibility (VAC)	120
<b>LEDS ALARMS &amp; SWITCHES</b>	
Diagnostic LEDs	Built-in LEDs confirm suppressor "protection" (green) and "grounded" (red) status
<b>SURGE / NOISE SUPPRESSION</b>	
AC Suppression Joule Rating	670
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
Clamping Voltage (RMS)	330
UL1449 Let Through Rating	500V
EMI / RFI Filtering	Up to 20 dB
<b>DATALINE SURGE SUPPRESSION</b>	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
<b>PHYSICAL</b>	
Shipping Dimensions (hwd / in.)	9.44 x 5.75 x 2.15
Shipping Dimensions (hwd / cm)	23.98 x 14.61 x 5.46
Shipping Weight (lbs.)	0.38
Shipping Weight (kg)	0.17
Unit Dimensions (hwd / in.)	3.26 x 5.80 x 1.86
Unit Dimensions (hwd / cm)	8.28 x 14.73 x 4.72
Unit Weight (lbs.)	0.36
Unit Weight (kg)	0.16

Material of Construction	Plastic
Housing Color	Black
Receptacle Color	Black
Style	Direct Plug-in
Outlets Measurement (Center to Center)	Distance between transformer outlets = 56mm; Distance between standard outlets = 28mm
<b>CERTIFICATIONS</b>	
UL1449 3rd Edition (AC Suppression)	UL1449 with fail safe circuit
FCC Part 68 (Communications)	Yes
cUL / CSA (Canada)	cUL
Approvals	RoHS
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$10,000 Ultimate Lifetime Insurance

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.