





Perormance level	PL2
Filter type	C
Capacitance	3900pf±20%
Working Voltage	100v
Current Rating	7.5A
Insulation Resistance	>1GΩ

FREQUENCY (MHz)	ATTENUATION (dB)
5	6dB
10	11dB
50	25dB
100	35dB
500	35dB
1000	32dB

				Dat.	Name	 All Dim. in mm Orig. Size DIN A 4	D-Sub, male, straight, 9 Poles, solder pins, dimples and fixing holes	Mo?Mstab/ Scale 1.5:1
			Detail.	8-JUL-02	CV			
			Insp.	09/12/11	JB			
36283	09/12/11	SD	Stand.				TB 09641227240	Blatt/ Page 1 / 1
33241	14/10/05	JMDR	HARTING EURL F-95972 Paris					
31058	8-JUL-02	CV						
Mod.	Dat.	Name						
						Sub.		