






D



C



B



RECOMMENDED MOUNTING HOLE PATTERN
SCALE 4:1

- 1 RECEPTACLE ACCEPTS A .008—.014 THICK I.C.LEAD.
- 2 TUBE LOADED FOR AUTOMATIC INSERTION.
- 3 BECU CONTACT —PLATED WITH TWO .000030 MIN THIK. GOLD STRIPES IN CONTACT AREA WITH TIN ON CONTACT LEGS, BALENCE OF CONTACT NICKEL PLATED.
- 4 PHOS. BRZ CONTACT — PLATED WITH TWO .000015 MIN THK. GOLD STRIPES IN CONTACT AREA WITH TIN ON CONTACT LEGS, BALENCE OF CONTACT NICKEL PLATED.
- 5 GLASS FILLED THERMOPLASTIC, 94V-0, BLACK
- 6 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

A

6	OBSOLETE	3	2.300	23	2.395	48	1—1825376—4
		3	1.900	19	1.995	40	1—1825376—3
		3	1.300	13	1.395	28	1—1825376—2
		3	1.100	11	1.195	24	1—1825376—1
	OBSOLETE	4	2.300	23	2.395	48	1825376—4
		4	1.900	19	1.995	40	1825376—3
		4	1.300	13	1.395	28	1825376—2
6	OBSOLETE	4	1.100	11	1.195	24	1825376—1
CONTACT & FINISH		DIM C	B SPCS	DIM A	POSITION	PART NO.	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B.S.VISWESWARA	22APR05	Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: INCHES		CHK K.WRIGHT	APVD	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-1066		DIP SOCKET ASSY, LADDER, DIPLOMATE, RET. LEAD .600 CL, LEAD FREE	
APPLICATION SPEC 114-1049		SIZE A1		CAGE CODE 00779	DRAWING NO 1825376
MATERIAL SEE TABLE		WEIGHT —		RESTRICTED TO —	
FINISH SEE TABLE		CUSTOMER DRAWING		SCALE 5:1	SHEET 1 OF 1
				REV A1	