



Flanged Block Forks – Vinyl Insulated Butted Seam




Product Number†	UPC (054007-)	Wire Range (AWG)	Stud Size	W	C	L	E	Thickness	Barrel Length	Barrel I.D.	Maximum Insulation Diameter	Terminals per Case
MVU18-6FFBK	01267	22-18	6	0.30	0.25	0.85	0.70	0.030	0.25	0.070	0.145	1000
MVU18-8FFBK	01268	22-18	8	0.30	0.25	0.85	0.70	0.030	0.25	0.070	0.145	1000
MVU18-10FFBK	01269	22-18	10	0.30	0.25	0.85	0.70	0.030	0.25	0.070	0.145	1000
MVU14-6FFBK	01633	16-14	6	0.30	0.25	0.85	0.70	0.030	0.25	0.090	0.170	1000
MVU14-8FFBK	01634	16-14	8	0.30	0.25	0.85	0.70	0.030	0.25	0.090	0.170	1000
MVU14-10FFBK	01635	16-14	10	0.30	0.25	0.85	0.70	0.030	0.25	0.090	0.170	1000
MVU10-6FFBK	02038	12-10	6	0.32	0.29	1.03	0.84	0.040	0.25	0.135	0.250	500
MVU10-8FFBK	02039	12-10	8	0.32	0.29	1.03	0.84	0.040	0.25	0.135	0.250	500
MVU10-10FFBK	02040	12-10	10	0.32	0.29	1.03	0.84	0.040	0.25	0.135	0.250	500




MVU18-6FFBK
Stud Size 6
Wire Range 22-18




MVU18-8FFBK
Stud Size 8
Wire Range 22-18




MVU18-10FFBK
Stud Size 10
Wire Range 22-18




MVU14-6FFBK
Stud Size 6
Wire Range 16-14




MVU14-8FFBK
Stud Size 8
Wire Range 16-14




MVU14-10FFBK
Stud Size 10
Wire Range 16-14



MVU10-6FFBK
Stud Size 6
Wire Range 12-10



MVU10-8FFBK
Stud Size 8
Wire Range 12-10



MVU10-10FFBK
Stud Size 10
Wire Range 12-10

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[MVU18-8FFBK](#) [MVU18-10FFBK](#)