



Search Results

- Evaluate
- FAQ's
- How to Buy
- Bill of Material
  - Favorite Products List
  - Locate Distributor

[Home](#) > [Products Overview](#) > [Search Results](#) >

Current refinements (click to remove) [Search Tips](#) Within Results

**Text Search: 'HSTT50-48-QC'**

Your search criteria matched only one product, shown below

## HSTT50-48-QC



- Shrink ratio of 2:1 insulates a wide range of diameters and irregular shapes
- Cross -linked, UV resistant material improves flame retardancy, chemical, and temperature resistance

For clear, add "C" to end of part number package suffix (Example HSTT05 -48-QC). Contact customer service for additional color information.

Meets Mil Spec AMSDTL-23053/5 Class 1(Colors), Class 2 (Clear)

|  |                                        |                                                      |
|--|----------------------------------------|------------------------------------------------------|
|  | Part Number                            | HSTT5048-QC                                          |
|  | RoHS Compliancy Status                 | Compliant                                            |
|  | Part Description                       | Thin Wall Polyolefin Heat Shrink                     |
|  | Material                               | Flame retardant polyolefin cross-linked except clear |
|  | Color                                  | Clear                                                |
|  | Military Specification                 | AMS-DTL-23053/5 Class 2                              |
|  | Length (ft.)                           | 4                                                    |
|  | Length (m)                             | 1.2                                                  |
|  | Max. Recovered I.D. (In.)              | .250                                                 |
|  | Max. Recovered I.D. (mm)               | 6.4                                                  |
|  | Min. Expanded I.D. (In.)               | .500                                                 |
|  | Min. Expanded I.D. (mm)                | 12.7                                                 |
|  | Nominal Diameter / Size                | .500                                                 |
|  | Nominal Recovered Wall Thickness (In.) | .025                                                 |
|  | Nominal Recovered Wall Thickness (mm)  | .6                                                   |
|  | Pricing Description                    | Heat Shrink Thin, .50"25Pcs/Pk                       |
|  | Shrink Ratio                           | 2:1                                                  |
|  | Temperature Range                      | -67°F to 275°F (-55°C to 135°C)                      |
|  | Min. Order UOM                         | PC                                                   |
|  | Min. Order Qty.                        | 25                                                   |
|  | BOM Qty. (# of Pkgs.)                  | <input type="text" value="0"/>                       |
|  | Add to Favorite Product List           |                                                      |

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.