

Search Results

Evaluate

- FAQ's
- Line Cards
- PDF-Copper Cabli ..
- Performance Data
- PDF-ETL Channel ..
- Selection Guides
- PDF-TX6A 10Gig U ..

Design a Solution

- Specification Sheets
- PDF-TX6A 10Gig U ..
- PDF-TX6A 10Gig U ..

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

Install & Maintain

- Installation Instructions
- PDF-Next Generat ..

Home > Product On-Line Catalog > Search Results >

Current refinements (click to remove) Search Tips

Text Search: 'PUP6A04YL-UG'

Your search criteria matched only one product, shown below

PUP6A04YL-UG



- Exceeds requirements of ANSI/TIA-568-C.2 Category 6A, IEEE 802.3an-2006, and ISO 11801 Class EA channel standards
- Meets requirements of IEEE 802.3af and IEEE 802.3at for PoE applications
- Exceeds requirements of ANSI/TIA-568-C.2 Category 6A and IEC 61156-5 Category 6A component standards
- Patent-pending cable design suppresses alien crosstalk with enhanced internal electrical performance
- Round cable design with reduced cable diameter enables improved cable bundling and optimizes fill capacity
- Cable diameter: 0.30 in. (7.9mm) nominal
- Installation temperature range: 32°F to 140°F (0°C to 60°C)
- Operating temperature range: -4°F to 167°F (-20°C to 75°C)
- Descending length cable markings enable easy identification of remaining cable which reduces installation time and cable scrap

▪ Part Number	PUP6A04YL-UG
▪ RoHS Compliance Status	Compliant
▪ Part Description	Category 6A, plenum (CMP), 4-pair, UTP copper cable. Copper conductors are 23 AWG with FEP insulation. Conductors are twisted in pairs, separated by an integrated pair divider, surrounded by a patent-pending matrix tape and protected by a low-smoke flame-retardant PVC jacket.
▪ Product Type	Copper Cable
▪ Color	Yellow
▪ Cable Color	Yellow
▪ Cable Type	UTP
▪ CE Compliant	No
▪ Flammability Rating	CMP
▪ Jacket Material	Flame-retardant PVC
▪ Performance Level	Category 6A/Class EA
▪ Pricing Description	Copper Cable, Cat 6A, 4-Pair, 23 AWG, UTP, CMP, Yellow, 1000 Feet/305m
▪ Min. Order UOM	FT
▪ Min. Order Qty.	9000
▪ BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
▪ Add to Favorite Product List	<input type="checkbox"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.