

Stufenbohrer

Step Drills



Art. 796

HSS, mit TiAlN (Titan-Aluminium-Nitrid) Beschichtung, mit Spiralnute und Entgratungszone "Kantenbrecher" (DBGM), für gratfreies Bohren und Aufreiben von Blechen, Rohren und Profilen und beidseitiges Entgraten in einem Arbeitsgang.
 Für (Material bis 6 mm Stärke): Baustahl, CrNi-Stahl, NE-Metall.
 Entgraten bis 1,5mm Materialstärke.

HSS, with TiAlN (titanium-aluminium nitride) coating, with spiral flute and "Edge-breaker" zone (DBGM), for drilling and roughening of sheet material, pipes and profiles, and deburring of both sides in one working step. For (material up to 6mm thick): structural steel, CrNi-steel, non-ferrous metal. Deburring of material up to 1.5 mm thick.

CODE	No.	mm				mm	mm	mm	g	EURO	EAN-CODE
07021	412	Bohrstufen 1 mm steigend				5	80	6	27	35,53	070216
		4	5	6	7						
		8	9	10	11						
		12									
07022	420	Bohrstufen 2 mm steigend				4	67	8	50	47,65	070223
		4	6	8	10						
		12	14	16	18						
07023	630	6	8	10	12	4	98	10	155	67,49	070230
		14	16	18	20						
		22	24	26	28						
		30									
07025	636	Bohrstufen 3 mm steigend				3	82	12	188	107,37	070254
		6	9	12	15						
		18	21	24	27						
		30	33	36							

Erläuterung TiAlN-Beschichtung, siehe Seite 117.



Stufenbohrer in Stahlblechkassette

Step Drills in steel-plate cassette



Art. 796-430

HSS, mit TiAlN (Titan-Aluminium-Nitrid) Beschichtung, mit Spiralnute und Entgratungszone "Kantenbrecher" (DBGM), für gratfreies Bohren und Aufreiben von Blechen, Rohren und Profilen und beidseitiges Entgraten in einem Arbeitsgang.

HSS, with TiAlN (titanium-aluminium nitride) coating, with spiral flute and "Edge-breaker" zone (DBGM), for drilling and roughening of sheet material, pipes and profiles, and deburring of both sides in one working step.

Für (Material bis 6 mm Stärke): Baustahl, CrNi-Stahl, NE-Metall.
 Entgraten bis 1,5mm Materialstärke.

For (material up to 6mm thick): structural steel, CrNi-steel, non-ferrous metal. Deburring of material up to 1.5 mm thick.

336-0143

CODE	No.	Inhalt	g	EURO	EAN-CODE
07024	430-2	4-12 / 4-20 / 6-30	670	163,46	070247