





1. RECEPTACLE ACCEPTS A .008-.014 THICK I.C. LEAD.
2. TUBE LOADED.
3. TWO .000030 MIN THK. GOLD STRIPES IN CONTACT AREA WITH TIN-LEAD (93/7) ON CONTACT LEGS, BALANCE OF CONTACT NICKEL PLATED.
4. TWO .000015 MIN THK. GOLD STRIPES IN CONTACT AREA WITH TIN-LEAD (93/7) ON CONTACT LEGS, BALANCE OF CONTACT NICKEL PLATED.



OBSOLETE	TINNED	PHOS.BRZ. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	2-641615-5				
	4	PHOS.BRZ. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	2-641615-4				
	TINNED	PHOS.BRZ. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	2-641615-3				
	3	BE.CU. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	2-641615-2				
	TINNED	BE.CU. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	2-641615-1				
CONTACT FINISH		CONTACT MAT'L	HOUSING MATERIAL		PART NO.			
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN M.CYRUS OK H.WYNKOOP APVD H.WYNKOOP PRODUCT SPEC 108-1066 APPLICATION SPEC 114-1049 WEIGHT -			OSJAND1 17NOV00 17NOV00 NAME SOCKET ASSY, DIP, LADDER, RET LEG, 28 POS, DIPLOMATE™ DL -		
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		Tyco Electronics Corporation Harrisburg, PA 17105				
		0 PLC	± -	SIZE A1				
		1 PLC	± -					
		2 PLC	± -					
		3 PLC	± .005					
		4 PLC	± -	CAGE CODE 00779				
		ANGLES	± 0°-30°					
MATERIAL SEE TABLE		FINISH SEE TABLE		DRAWING NO 641615			RESTRICTED TO -	
CUSTOMER DRAWING				SCALE 5:1			SHEET 1 OF 1	REV Y

0.036±.003 TYP

Ø.009(M)