


Screwdrivers, Nut Drivers and Accessories

Offering a variety of tip types, hex sizes, shaft lengths, and handle designs, Klein has the screwdrivers and nut drivers professionals demand to get the job done with comfort and ease.




For Professionals...
Since 1857™

Introduction

Extra-quality features have made the Klein name famous for hand tools – features that assure greater convenience, comfort and efficiency in use, plus exceptional strength and durability.

All Klein drivers are made of the highest quality tempered steel and carefully heat-treated for maximum strength. Shafts have integral flanges that provide an extra-strong, torque-proof anchor in the handle. Strong, durable black tips are forged and precision ground with square edges to fit screw openings securely. They resist slip-page and provide positive turning action.

Cushion-Grip screwdrivers feature super-comfortable, sure-grip handles on top-quality blades for the professional. All Klein screwdrivers meet or exceed applicable ANSI and MIL specifications.



Using Screwdrivers and Nut Drivers

The size of the screw or nut and the type of opening it has determines which driver to use. Here are a few tips on how to use a driver that can be of benefit, because screwdrivers are the most often misused and abused hand tools of all.

1. Never use a driver to do another tool's job.

Using a driver as a pry bar, scraper, or a chisel can ruin the tool, spoil the work and cause injury.

2. Never push a driver beyond its capacity.

Make a pilot hole for the screw for easier driving. Use square-shank drivers for heavy work.

3. Never expose a driver to excessive heat.

Direct flame can draw the temper from the metal, weakening and possibly warping it, making it unsafe and inefficient to use.

4. Never use a driver at an angle to the screw.

Always keep the shank perpendicular to the screw head. Driving at an angle or using a point that is too small can spoil the screw or slip and damage the work.

5. Never depend on a driver's handle or covered blade to insulate you from electricity.

Plastic and Cushion-Grip handles are intended only to provide a firm, comfortable grip. Insulated blades are intended only as a protective measure against shorting out components. Only use insulated tools that are marked with the official international 1000-volt rating symbol if there is any chance that the tool will make contact with an energized source.

6. Discard damaged or worn drivers.

TORX® is a registered trademark of Acument Intellectual Properties, LLC.

MAGNETIZER

NEW!


Quickly **magnetize** and **demagnetize** screwdriver tips and bits using powerful rare-earth magnets

To magnetize screwdriver:

Insert screwdriver shaft fully into magnetizing slot; avoid rotating shaft while drawing out slowly

To demagnetize screwdriver:

Insert shaft fully into smallest demagnetizing slot that fits; avoid rotating shaft while drawing out slowly



Cat. No.	Overall Length	Overall Height	Overall Width	Weight
MAG2	2-13/64" (56.0 mm)	45/64" (17.9 mm)	1-3/32" (26.2 mm)	1.1 oz (32 g)

Fits these drivers

- #3 Phillips
- 1/4" Keystone (round or square shank)
- 5/16" Cabinet
- #2 Phillips Insulated
- 1/4" Cabinet Insulated
- Most precision screwdrivers




See page 310 for additional information on warnings.



Cushion-Grip Screwdrivers

Meets or exceeds applicable ASME / ANSI specifications

Tip-Ident® quickly identifies the type of screwdriver and tip orientation



MADE IN USA

Color-Coded Cushion-Grip Screwdrivers

Includes core Cushion-Grip screwdriver features plus:

- Color-coded handle ends for quick and easy identification
- TORX® tip drive cuts slippage, saves fasteners and transmits more torque to the work



660



Cat. No.	Tip Type	Shank Type	Shank Length	Color Code	Overall Length	Weight
660	#0 Square-Recess	Round	4" (101.6 mm)	Yellow	7-3/4" (196.9 mm)	0.20 lb (0.09 kg)
661	#1 Square-Recess	Round	4" (101.6 mm)	Green	7-3/4" (196.9 mm)	0.20 lb (0.09 kg)
662	#2 Square-Recess	Round	4" (101.6 mm)	Red	8-1/4" (209.6 mm)	0.30 lb (0.14 kg)
663	#3 Square-Recess	Round	4" (101.6 mm)	Black	8-1/4" (209.6 mm)	0.30 lb (0.14 kg)
665	#1 Square-Recess	Round	8" (203.2 mm)	Green	11-3/4" (298.5 mm)	0.30 lb (0.14 kg)
666	#2 Square-Recess	Round	8" (203.2 mm)	Red	12-1/4" (311.2 mm)	0.40 lb (0.18 kg)
667	#3 Square-Recess	Round	8" (203.2 mm)	Black	12-1/4" (311.2 mm)	0.40 lb (0.18 kg)
668	#1 Square-Recess	Round	1-1/2" (38.1 mm)	Green	3-7/16" (87.3 mm)	0.15 lb (0.07 kg)
19542	T15 TORX®	Round	4" (101.6 mm)	Yellow	8-5/16" (211.1 mm)	0.20 lb (0.09 kg)
19543	T20 TORX®	Round	4" (101.6 mm)	Green	8-5/16" (211.1 mm)	0.25 lb (0.11 kg)
19544	T25 TORX®	Round	4" (101.6 mm)	Blue	8-5/16" (211.1 mm)	0.25 lb (0.11 kg)
19545	T27 TORX®	Round	4" (101.6 mm)	Brown	8-5/16" (211.1 mm)	0.25 lb (0.11 kg)
19546	T30 TORX®	Round	4" (101.6 mm)	Red	8-5/16" (211.1 mm)	0.25 lb (0.11 kg)

TORX® is a registered trademark of Acument Intellectual Properties, LLC.

Cat. No.	Set Contains	Weight
19555	TORX® Cushion-Grip Screwdriver Set 5 Pc	1.2 lb (0.5 kg)

Cat. No.	Description
19542	T15 TORX® Screwdriver Round Shank
19543	T20 TORX® Screwdriver Round Shank
19544	T25 TORX® Screwdriver Round Shank
19545	T27 TORX® Screwdriver Round Shank
19546	T30 TORX® Screwdriver Round Shank

Cat. No.	Set Contains	Weight
85664	4 Piece Square Recess Screwdriver Set	1.5 lb (0.7 kg)

Cat. No.	Description
660	#0 Square Recess Screwdriver 4" Shank
661	#1 Square Recess Screwdriver 4" Shank
662	#2 Square Screwdriver 4" Round Shank
663	#3 Square Recess Screwdriver 4" Shank

Miniature Screwdrivers

Includes core Cushion-Grip screwdriver features



Cat. No.	Tip Type	Shank Type	Shank Length	Overall Length	Weight
604-3	#0 Phillips	Round	3" (76.2 mm)	5-3/4" (146.1 mm)	0.64 oz (18.1 g)
606-2	1/16" (1.59 mm) Keystone	Round	2" (50.8 mm)	4-3/4" (120.7 mm)	0.48 oz (13.6 g)
607-3	3/32" (2.4 mm) Cabinet	Round	3" (76.2 mm)	5-3/4" (146.1 mm)	0.64 oz (18.1 g)
607-4	3/32" (2.4 mm) Cabinet	Round	4" (101.6 mm)	6-3/4" (171.5 mm)	0.64 oz (18.1 g)
608-2	1/8" (3.2 mm) Cabinet	Round	2" (50.8 mm)	4-3/4" (120.7 mm)	0.48 oz (13.6 g)
608-3	1/8" (3.2 mm) Cabinet	Round	3" (76.2 mm)	5-3/4" (146.1 mm)	0.64 oz (18.1 g)
608-4	1/8" (3.2 mm) Cabinet	Round	4" (101.6 mm)	6-3/4" (171.5 mm)	0.80 oz (22.7 g)
608-6	1/8" (3.2 mm) Cabinet	Round	6" (152.4 mm)	8-3/4" (222.3 mm)	0.80 oz (22.7 g)
608-8	1/8" (3.2 mm) Cabinet	Round	8" (203.2 mm)	10-3/4" (273.1 mm)	0.80 oz (22.7 g)
608-10	1/8" (3.2 mm) Cabinet	Round	10" (254.0 mm)	12-3/4" (323.9 mm)	0.80 oz (22.7 g)



608-6

Cat. No.	Set Contains	Weight
85484	Mini Cushion-Grip Screwdriver Set 4 Pc	0.14 lb (0.06 kg)

Cat. No.	Description
604-3	#0 Phillips Mini Screwdriver 3" Shank
606-2	1/16" Keystone Tip Mini Screwdriver 2"
607-3	3/32" Cabinet Tip Mini Screwdriver 3"
608-3	1/8" Cabinet Tip Mini Screwdriver 3"



Cushion-Grip Screwdrivers

Cushion-Grip Screwdrivers

Includes core Cushion-Grip screwdriver features plus:

- Narrow cabinet-tip permits blade access where space is limited
- Precision machined combo-tip designed for combination head screws
- Precision machined Phillips tip provides a more consistent geometric symmetry than conventional Phillips screwdrivers to accurately fit and torque without slippage
- Heavy-duty square shank and hex bolster allows wrench-assisted turning
- Bolster reinforces shank for hard use



Cat. No.	Tip Type	Shank Type	Shank Length	Overall Length	Weight
600-1	5/16" (7.9 mm) Cabinet	Round	1-1/2" (38.1 mm)	3-7/16" (87.3 mm)	0.10 lb (0.05 kg)
601-3	3/16" (4.8 mm) Cabinet	Round	3" (76.2 mm)	6-3/4" (171.5 mm)	0.10 lb (0.05 kg)
601-4	3/16" (4.8 mm) Cabinet	Round	4" (101.6 mm)	7-3/4" (196.9 mm)	0.15 lb (0.07 kg)
601-6	3/16" (4.8 mm) Cabinet	Round	6" (152.4 mm)	9-3/4" (247.7 mm)	0.15 lb (0.07 kg)
601-8	3/16" (4.8 mm) Cabinet	Round	8" (203.2 mm)	11-3/4" (298.5 mm)	0.20 lb (0.09 kg)
601-10	3/16" (4.8 mm) Cabinet	Round	10" (254.0 mm)	13-3/4" (349.3 mm)	0.20 lb (0.09 kg)
7314	#1 Combo	Round	4" (101.6 mm)	8-11/32" (211.9 mm)	0.30 lb (0.14 kg)
7324	#2 Combo	Round	4" (101.6 mm)	8-11/32" (211.9 mm)	0.30 lb (0.14 kg)
603-1	#2 Phillips	Round	1-1/2" (38.1 mm)	3-7/16" (87.3 mm)	0.10 lb (0.05 kg)
603-3	#1 Phillips	Round	3" (76.2 mm)	6-3/4" (171.5 mm)	0.15 lb (0.07 kg)
603-4	#2 Phillips	Round	4" (101.6 mm)	8-1/4" (209.6 mm)	0.25 lb (0.11 kg)
603-6	#3 Phillips	Round	6" (152.4 mm)	11" (279.4 mm)	0.35 lb (0.16 kg)
603-7	#2 Phillips	Round	7" (177.8 mm)	11-5/16" (287.3 mm)	0.30 lb (0.14 kg)
603-10	#2 Phillips	Round	10" (254.0 mm)	14-5/16" (363.5 mm)	0.35 lb (0.16 kg)
Heavy Duty					
605-4	1/4" (6.4 mm) Cabinet	Round	4" (101.6 mm)	8-11/32" (211.9 mm)	0.25 lb (0.11 kg)
605-6	1/4" (6.4 mm) Cabinet	Round	6" (152.4 mm)	10-11/32" (262.7 mm)	0.30 lb (0.14 kg)
605-8	1/4" (6.4 mm) Cabinet	Round	8" (203.2 mm)	12-11/32" (313.5 mm)	0.30 lb (0.14 kg)
605-10	1/4" (6.4 mm) Cabinet	Round	10" (254.0 mm)	14-11/32" (364.3 mm)	0.35 lb (0.16 kg)
Heavy Duty with Bolster					
600-4	1/4" (6.4 mm) Keystone	Square	4" (101.6 mm)	8-11/32" (211.9 mm)	0.25 lb (0.11 kg)
600-6	5/16" (7.9 mm) Keystone	Square	6" (152.4 mm)	10-15/16" (277.8 mm)	0.40 lb (0.18 kg)
600-8	3/8" (9.52 mm) Keystone	Square	8" (203.2 mm)	13-7/16" (341.3 mm)	0.65 lb (0.29 kg)
600-12	1/2" (12.7 mm) Keystone	Square	12" (304.8 mm)	17-7/16" (443.0 mm)	0.80 lb (0.36 kg)
Heavy Duty with Hex Bolster					
602-3	7/32" (5.6 mm) Keystone	Round	3" (76.2 mm)	6-3/4" (171.5 mm)	0.15 lb (0.07 kg)
602-4	1/4" (6.4 mm) Keystone	Round	4" (101.6 mm)	8-11/32" (211.9 mm)	0.25 lb (0.11 kg)
602-6	5/16" (7.9 mm) Keystone	Round	6" (152.4 mm)	10-15/16" (277.8 mm)	0.35 lb (0.16 kg)
602-8	3/8" (9.52 mm) Keystone	Round	8" (203.2 mm)	13-7/16" (341.3 mm)	0.55 lb (0.25 kg)
602-10	3/8" (9.52 mm) Keystone	Round	10" (254.0 mm)	15-7/16" (392.1 mm)	0.60 lb (0.27 kg)
602-12	3/8" (9.52 mm) Keystone	Round	12" (304.8 mm)	17-7/16" (443.0 mm)	0.65 lb (0.29 kg)

Cat. No.	Set Contains	Weight
85078	8 Piece Cushion-Grip Screwdriver Set	1.7 lb (0.8 kg)

Cat. No.	Description
600-4	1/4" Screwdriver HD Square Shank
602-6	5/16" Keystone Tip Screwdriver 6" L
600-1	5/16" Cabinet Tip Screwdriver 1-1/2"
601-3	3/16" Cabinet Tip Screwdriver 3"
603-3	#1 Phillips Screwdriver 3" Round Shank
603-1	#2 Stubby Phillips Screwdriver 1-1/2"
603-4	#2 Phillips Screwdriver 4" Round Shank
603-6	#3 Phillips Screwdriver 6" Round Shank

Cat. No.	Set Contains	Weight
85076	7 Piece Cushion-Grip Screwdriver Set	1.5 lb (0.7 kg)

Cat. No.	Description
600-4	1/4" Screwdriver HD Square Shank
602-6	5/16" Keystone Tip Screwdriver 6" L
601-3	3/16" Cabinet Tip Screwdriver 3"
601-6	3/16" Cabinet Tip Screwdriver 6"
605-4	1/4" Cabinet Tip Screwdriver 4" Shank
603-3	#1 Phillips Screwdriver 3" Round Shank
603-4	#2 Phillips Screwdriver 4" Round Shank

Cat. No.	Set Contains	Weight
85074	6 Piece Cushion-Grip Screwdriver Set	1.5 lb (0.7 kg)

Cat. No.	Description
600-4	1/4" Screwdriver HD Square Shank
600-6	5/16" Keystone Screwdriver 6" SQ Shank
601-3	3/16" Cabinet Tip Screwdriver 3"
603-3	#1 Phillips Screwdriver 3" Round Shank
603-4	#2 Phillips Screwdriver 4" Round Shank
603-6	#3 Phillips Screwdriver 6" Round Shank

Cat. No.	Set Contains	Weight
85075	5 Piece Cushion-Grip Screwdriver Set	1.3 lb (0.6 kg)

Cat. No.	Description
602-6	5/16" Keystone Tip Screwdriver 6" L
600-4	1/4" Screwdriver HD Square Shank
601-6	3/16" Cabinet Tip Screwdriver 6"
605-6	1/4" Cabinet Tip Screwdriver Heavy Duty 6"
603-4	#2 Phillips Screwdriver 4" Round Shank

Cat. No.	Set Contains	Weight
85105	4 Piece Cushion-Grip Screwdriver Set	1.5 lb (0.7 kg)

Cat. No.	Description
600-6	5/16" Keystone Screwdriver 6" SQ Shank
600-4	1/4" Screwdriver HD Square Shank
601-6	3/16" Cabinet Tip Screwdriver 6"
603-4	#2 Phillips Screwdriver 4" Round Shank

Cat. No.	Set Contains	Weight
85071	2 Piece Stubby Screwdriver Set	0.30 lb (0.14 kg)

Cat. No.	Description
600-1	5/16" Cabinet Tip Screwdriver 1-1/2"
603-1	#2 Stubby Phillips Screwdriver 1-1/2"

Cat. No.	Set Contains	Weight
32378	4" Combo Tip Driver Set	1.5 lb (0.7 kg)

Cat. No.	Description
7314	#1 Combo-Tip Driver, 4" Fixed Blade
7324	#2 Combo Tip Driver, 4" Fixed Blade

Cat. No.	Set Contains	Weight
85072	2 Piece 10" Long Blade Screwdriver Set	0.70 lb (0.32 kg)

Cat. No.	Description
603-10	#2 Phillips Screwdriver 10" Round Shank
605-10	1/4" Cabinet Tip Screwdriver 10" Shank



Cushion-Grip Screwdrivers

Demolition Screwdrivers

Includes core Cushion-Grip screwdriver features plus:

- Engineered, manufactured and tested for prying, chiseling and punching
- Plated metal strike cap to protect handle from hammer blows
- Heat treated metal shaft runs complete length of handle to metal strike cap to transfer metal strike force



602-7DD



Cat. No.	Tip Type	Shank Type	Shank Length	Overall Length	Weight
602-4DD	1/4" (6.4 mm) Cabinet	Round	4" (101.6 mm)	9" (228.6 mm)	0.37 lb (0.17 kg)
602-7DD	5/16" (7.9 mm) Keystone	Round	7" (177.8 mm)	12-3/8" (314.3 mm)	0.56 lb (0.25 kg)
6034DD	#2 Phillips	Round	4" (177.8 mm)	9" (228.6 mm)	0.37 lb (0.17 kg)

Cat. No.	Set Contains	Weight
32008	Demolition Driver Set	0.70 lb (0.32 kg)
Cat. No.	Description	
602-4DD	1/4" Keystone Demolition Driver, 4" Shank	
6034DD	#2 Phillips Demolition Driver, 4" Shank	

Electronics Screwdrivers

Includes core Cushion-Grip screwdriver features plus:

- Rotating cap for optimum and precise control



614-6



Cat. No.	Tip Type	Shank Type	Shank Length	Overall Length	Weight
613-3	#0 Phillips	Round	3" (76.2 mm)	6-1/2" (165.1 mm)	0.80 oz (22.7 g)
614-2	1/16" (1.59 mm) Cabinet	Round	2" (50.8 mm)	5-1/2" (139.7 mm)	0.80 oz (22.7 g)
614-3	3/32" (2.4 mm) Cabinet	Round	3" (76.2 mm)	6-1/2" (165.1 mm)	0.80 oz (22.7 g)
614-4	1/8" (3.2 mm) Cabinet	Round	4" (101.6 mm)	7-1/2" (190.5 mm)	0.80 oz (22.7 g)
614-6	1/8" (3.2 mm) Cabinet	Round	6" (152.4 mm)	9-1/2" (241.3 mm)	0.80 oz (22.7 g)

Cat. No.	Set Contains	Weight
85614	5 Piece Electronics Screwdriver Set	0.80 lb (0.36 kg)
Cat. No.	Description	
614-2	1/16" Slotted Electronics Screwdriver, 2" Shank	
614-3	3/32" Slotted Electronics Screwdriver, 3" Shank	
614-4	1/8" Electronics Screwdriver 4" Shank	
614-6	1/8" Electronics Screwdriver 6" Shank	
613-3	#0 Phillips Electronics Screwdriver, 3" Shank	

Coated Screwdrivers

Includes core Cushion-Grip screwdriver features plus:

- Plastic coated for circuit protection only. NOT INSULATED
- Special plastic coating resists cutting, cracking and chipping
- Thin coating permits use in confined areas



620-4

Cat. No.	Tip Type	Shank Type	Shank Length	Overall Length	Weight
620-3	3/16" (4.8 mm) Cabinet	Round	3" (76.2 mm)	6-3/4" (171.5 mm)	0.15 lb (0.07 kg)
620-4	1/4" (6.4 mm) Cabinet	Round	4" (101.6 mm)	8-11/32" (211.9 mm)	0.20 lb (0.09 kg)
620-6	5/16" (7.9 mm) Cabinet	Round	6" (152.4 mm)	10-15/16" (277.8 mm)	0.40 lb (0.18 kg)
620-8	3/8" (9.52 mm) Cabinet	Round	8" (203.2 mm)	13-7/16" (341.3 mm)	0.60 lb (0.27 kg)
621-6	3/16" (4.8 mm) Cabinet	Round	6" (152.4 mm)	9-3/4" (247.7 mm)	0.20 lb (0.09 kg)
621-8	3/16" (4.8 mm) Cabinet	Round	8" (203.2 mm)	11-3/4" (298.5 mm)	0.20 lb (0.09 kg)

2-in-1 Rapi-Driv®


- Interchangeable bit holder allows quick switching between tip styles and works with other standard size bits
- Crank-action handle allows you to spin screws fast with one hand
- Blast finish bit provides firm grip on fasteners to reduce cam out



67100



Cat. No.	Phillips Bits	Slotted Bits	Shank Length	Handle Color	Overall Length	Weight
67100	#2	3/16" (4.8 mm)	6" (152.4 mm)	Black	9-3/4" (247.7 mm)	0.26 lb (0.12 kg)



Cushion-Grip Screwdrivers


Rapi-Driv® Screwdrivers

- Crank-action handle spins screws fast with one hand
- Saves time and effort, especially on long-threaded screws in switch plates, light fixtures, etc.



670-6

Cat. No.	Tip Type	Shank Type	Shank Length	Overall Length	Weight
670-3	3/16" (4.8 mm) Cabinet	Round Rapi-Driv®	4" (101.6 mm)	7-3/4" (196.9 mm)	0.15 lb (0.07 kg)
670-6	3/16" (4.8 mm) Cabinet	Round Rapi-Driv®	6" (152.4 mm)	9-3/4" (247.7 mm)	0.20 lb (0.09 kg)
671-6	1/4" (6.4 mm) Cabinet	Round Rapi-Driv®	6" (152.4 mm)	9-3/4" (247.7 mm)	0.20 lb (0.09 kg)
682-6	#2 Phillips	Round Rapi-Driv®	6" (152.4 mm)	9-3/4" (247.7 mm)	0.25 lb (0.11 kg)
691-6	#1 Square	Round Rapi-Driv®	6" (152 mm)	9-3/4" (248 mm)	0.35 lb (0.16 kg)



7-Piece Multiple-Application Screwdriver Set

- Specialty set for a wide variety of applications

Cat. No.	Set Contains	Weight
85077	Multi Application Screwdriver Set 7 Pc	1.7 lb (0.8 kg)

Cat. No.	Tip Type	Shank Type	Shank Length	Overall Length
600-4	1/4" (6.4 mm) Keystone	Square	4" (101.6 mm)	8-11/32" (211.9 mm)
602-6	5/16" (7.9 mm) Keystone	Round	6" (152.4 mm)	10-15/16" (277.8 mm)
601-6	3/16" (4.8 mm) Cabinet	Round	6" (152.4 mm)	9-3/4" (247.7 mm)
605-6	1/4" (6.4 mm) Cabinet	Round	6" (152.4 mm)	10-11/32" (262.7 mm)
670-6	3/16" (4.8 mm) Cabinet	Round Rapi-Driv®	6" (152.4 mm)	9-3/4" (247.7 mm)
K36	1/4" (6.4 mm) Slotted	Round	6" (152.4 mm)	9-3/4" (247.7 mm)
603-4	#2 Phillips	Round	4" (101.6 mm)	8-1/4" (209.6 mm)



85077

Adjustable Length Screwdrivers

- Removable shank adjusts within 4" to 8" (102-208 mm) range for numerous length combinations
- Blades feature two tips for multiple screwdrivers in one tool
- Proprietary system securely holds blade - as durable as a traditional Klein fixed blade screwdriver
- Press down to extend or lengthen the shank
- Push up to retract or shorten the shank
- Components sold separately



32751



US Patent: 6,561,523

Cat. No.	Type	Tip Size	Shank Length	Overall Length	Weight
32751	Adjustable Length Screwdriver	#2 Phillips, 1/4" (6.4 mm) Slotted	4" to 8" (101.6 to 203.2 mm)	13-3/8" (339.7 mm)	0.70 lb (0.32 kg)
32708	Adjustable Length Screwdriver	#1, #2 Square	4" to 8" (101.6 to 203.2 mm)	13-3/8" (339.7 mm)	0.10 lb (0.05 kg)
32709	Replacement Blade	#1, #2 Square	7-3/4" (196.9 mm)	9" (228.6 mm)	0.10 lb (0.05 kg)
32713	Replacement Blade	#1 Phillips, 3/16" (4.8 mm) Slotted	7-3/4" (196.9 mm)	9" (228.6 mm)	0.10 lb (0.05 kg)
32618	Replacement Blade	#2 Phillips, 1/4" (6.4 mm) Slotted	4" to 8" (101.6 to 203.2 mm)	9-1/8" (231.8 mm)	0.25 lb (0.11 kg)
32619	Screwdriver Handle	—	—	5-3/8" (136.5 mm)	0.20 lb (0.09 kg)

Cat. No.	Set Contains	Weight
32715	Adjustable Length Replacement Blade Set	0.10 lb (0.05 kg)

Cat. No.	Description
32713	Adj. Length Blade, #1 PH, 3/16" Slotted
32618	Adj. Length Blade, #2, 1/4" Slotted
32709	Adj. Length Blade, Sq #1, #2

See page 310 for additional information on warnings.



Specialty Cushion-Grip Screwdrivers

2-in-1 Hex Slide Driver/Nut Driver

- Unique, patented tip switches from 1/4" size to 5/16" size
- Magnetic regardless of which driver is selected
- Twist the thumb nut to lock tip setting
- U.S. Patent 7,654,175 B2

NEW!


65129



Cat. No.	Type	Tip Size	Shank Length	Overall Length	Weight
65129 NEW!	Hex Driver	1/4", 5/16"	6" (152.4 mm)	10-1/4" (260.4 mm)	0.50 lb (0.23 kg)
65131 NEW!	Hex Driver	1/4", 5/16"	1-1/2" (38.1 mm)	3-23/64" (85.3 mm)	0.18 lb (0.08 kg)

2-in-1 Hex Head Screwdriver

- 1/4" and 5/16" six-point hex nut driver
- Powerful magnets for maximum fastener retention
- Solid build quality; feels like a conventional nut driver
- Color coded bands for easy identification
- Wrench-assist to help remove stubborn fasteners



65064



Cat. No.	Type	Tip Size	Shank Length	Overall Length	Weight
65064	Hex Driver	1/4" and 5/16"	3-5/8" (92.1 mm)	8" (203.2 mm)	0.10 lb (0.05 kg)

Screw-Holding Screwdrivers

- Starts and drives screws with one hand when working in hard-to-reach spaces



32215



Cat. No.	Tip Type	Shank Type	Shank Length	Overall Length	Weight
32215	1/4" (6.4 mm) Cabinet	Round	7" (177.8 mm)	11-1/4" (285.8 mm)	0.32 lb (0.15 kg)
32216	#2 Phillips	Round	7" (177.8 mm)	11-1/4" (285.8 mm)	0.32 lb (0.15 kg)

Terminal Block Screwdriver

Includes core Cushion-Grip screwdriver features plus:


- Provides exact fit for terminal block screws
- Tip is up to 19% stronger than competitors and provides 76% higher torque value than the required ASME B107 Standard



612-4



Cat. No.	Tip Type	Shank Type	Shank Length	Overall Length	Weight
612-4	1/8" (3.2 mm) Cabinet	Round	4" (101.6 mm)	7-3/4" (196.9 mm)	0.15 lb (0.07 kg)



Specialty Cushion-Grip Screwdrivers

Wire Bending Screwdrivers

Includes core Cushion-Grip screwdriver features plus:

- Metal stud offers a convenient and easy way to bend, loop and connect solid wire when installing outlets and switches



605-6B



Cat. No.	Bends	Tip Type	Tip Size	Shank Type	Shank Length	Overall Length	Weight
605-4B	AWG Gauges Nos. 10, 12, 14	Cabinet	1/4" (6.4 mm)	Round	4" (101.6 mm)	8-11/32" (211.9 mm)	0.25 lb (0.11 kg)
605-6B	AWG Gauges Nos. 10, 12, 14	Cabinet	1/4" (6.4 mm)	Round	6" (152.4 mm)	10-11/32" (262.7 mm)	0.30 lb (0.14 kg)
603-4B	AWG Gauges Nos. 10, 12, 14	Phillips	#2	Round	4" (101.6 mm)	8-5/16" (211.1 mm)	0.25 lb (0.11 kg)

Multi-Bit Cushion-Grip Screwdrivers/Nut Drivers

15-in-1 Screwdriver/Nut Drivers

- Includes 14 different screwdriver tips plus a 1/4" (6.4 mm) nut driver
- Internal storage for screwdriver bits



INTERNAL STORAGE
in handle



32290



Cat. No.	Description	Nut Driver Sizes	Phillips Bits	Slotted Bits	Square Bits	Hex Bits	Combo Bits	TORX® Bits	Other Bits	Shank Length	Handle Color	Overall Length	Weight
32290	Multi-Bit Screwdriver with Storage 15 Pc	1/4"	#0, #1, #2, #3	4 mm, 6 mm	#1, #2	—	#1, #2	#10, #15, #20, #25	—	4" (101.6 mm)	Black	8-1/2" (215.9 mm)	0.50 lb (0.23 kg)
32291	Tamperproof Multi-Bit Screwdriver 15 Pc	1/4"	—	—	—	Pins: 1/8", 9/64", 5/32", 3/16"	—	Pins: #10, #15, #20, #25, #27, #30	Spanners: #6, #8, #10, #12	4" (101.6 mm)	Black	8-1/2" (215.9 mm)	0.50 lb (0.23 kg)
32292	HVAC Multi-Bit Screwdriver 15 Pc	1/4"	#0, #1, #2, #3	4 mm, 6 mm	#1, #2	—	—	#10, #15, #20, #25	Schrader Valve Insertion, Core Removal	4" (101.6 mm)	Black	8-1/2" (215.9 mm)	0.50 lb (0.23 kg)

Schrader® is a registered trademark of Schrader-Bridgeport International, Inc. TORX® is a registered trademark of Acument Intellectual Properties, LLC.

11-in-1 Combo-Tip Screwdriver/Nut Driver

- Precision machined tip designed for combination head screws



32505



Cat. No.	Nut Driver Sizes	Phillips Bits	Slotted Bits	Square Bits	Combo Bits	Shank Length	Handle Color	Overall Length	Weight
32505	1/4", 5/16" 3/8"	#1, #2	1/4" (6.4 mm), 5/16" (7.9 mm)	#1, #2	#1, #2	4" (101.6 mm)	Yellow/Black	7-1/4" (184.2 mm)	0.50 lb (0.23 kg)



Multi-Bit Cushion-Grip Screwdrivers/Nut Drivers

11-in-1 Screwdriver/Nut Driver with Schrader® Valve Removal/Installation Bit

- Great for HVAC and other industrial applications
- Includes unique style bit for installation/removal of common TR-4 Schrader® valves and aggressive thread extractor tip for backing out broken cores



32527



Cat. No.	Nut Driver Sizes	Phillips Bits	Slotted Bits	Square Bits	Other Bits	Shank Length	Handle Color	Overall Length	Weight
32527	3/8", 5/16", 1/4"	#1, #2	1/4" (6.4 mm), 3/16" (4.8 mm)	#1, #2	Schrader Valve Insertion, Core Removal	3" (76.2 mm)	Yellow/Black	7-3/4" (196.9 mm)	0.44 lb (0.20 kg)

Schrader® is a registered trademark of Schrader International, Inc.


8-in-1 HVAC Slide Driver™ Screwdriver/Nut Driver

NEW!

- Unique, patented head slides back and forth to switch from 1/4" to 5/16" magnetic hex-head screwdriver
- Thumb nut locks tip setting
- Features a specialty bit for installation/removal of common TR-4 Schrader® valves
- Includes 1/4" and 3/8" hollow nut drivers, as well as #2 Phillips, 1/8" (3 mm) and 1/4" (6 mm) slotted screwdriver tips
- Great for HVAC applications including thermostat installation and control work
- U.S. patent 7,654,175 B2



32596



Cat. No.	Nut Driver Sizes	Phillips Bits	Slotted Bits	Other Bits	Shank Length	Handle Color	Overall Length	Weight
32596 NEW!	1/4", 5/16", 3/8"	#2	1/8" (3.2 mm), 1/4" (6.4 mm)	Schrader® Valve Core Removal	3-1/4" (82.6 mm)	Yellow/Black	7-1/2" (190.5 mm)	0.50 lb (0.2 kg)

Schrader® is a registered trademark of Schrader-Bridgeport International, Inc.

4-in-1 Electronics Precision Screwdrivers

- Four different tips in one tool
- Rotating cap for optimum and precise control




32581



Cat. No.	Phillips Bits	Slotted Bits	TORX® Bits	Shank Length	Handle Color	Overall Length	Weight
32581	#0, #00	1/8" (3.2 mm), 3/32" (2.4 mm)	—	2-51/64" (71.0 mm)	Yellow/Black	6-1/2" (165.1 mm)	1.1 oz (31 g)
32585 NEW!	—	—	T7, T8, T10, T15	2-51/64" (71.0 mm)	Yellow/Black	6-1/2" (165.1 mm)	1.1 oz (31 g)

TORX® is a registered trademark of Acument Intellectual Properties, LLC.





Multi-Bit Cushion-Grip Screwdrivers/Nut Drivers

Ratcheting Multi-Bit Screwdriver/Nut Driver

- High torque 3-way ratcheting mechanism, forward, reverse and locked positions for tough applications
- Interchangeable shaft holds six universal tips; converts to three nut driver sizes and one hex driver
- Strong, heat-treated nut drivers for improved torque



32558



Cat. No.	Nut Driver Sizes	Phillips Bits	Slotted Bits	Square Bits	Hex Bits	Shank Length	Handle Color	Overall Length	Weight
32558	1/4", 5/16", 3/8"	#1, #2	1/4" (6.4 mm), 3/16" (4.8 mm)	#1, #2	3/8"	2-61/64" (75.0 mm)	Yellow/Black	7-57/64" (200.4 mm)	0.48 lb (0.22 kg)

6-in-1 Ratcheting Stubby Screwdrivers

- Ratcheting mechanism allows user to work faster with more efficiency



32593



Cat. No.	Nut Driver Sizes	Phillips Bits	Slotted Bits	Square Bits	Shank Length	Handle Color	Overall Length	Weight
32593	1/4", 5/16"	#1, #2	1/4" (6.4 mm), 3/16" (4.8 mm)	—	1-19/64" (32.9 mm)	Yellow/Black	3-1/2" (88.9 mm)	0.10 lb (0.05 kg)
32594	1/4", 5/16"	#2	3/16" (4.8 mm)	#1, #2	1-19/64" (32.9 mm)	Yellow/Black	3-1/2" (88.9 mm)	0.10 lb (0.05 kg)

Heavy-Duty Multi-Bit Screwdriver/Nut Driver

- Superior torque for tough applications
- Interchangeable shaft holds six universal tips; converts to three nut driver sizes and one hex driver
- Strong, heat-treated nut drivers for improved torque



32557



Cat. No.	Nut Driver Sizes	Phillips Bits	Slotted Bits	Square Bits	Hex Bits	Shank Length	Handle Color	Overall Length	Weight
32557	1/4", 5/16", 3/8"	#1, #2	1/4" (6.4 mm), 3/16" (4.8 mm)	#1, #2	3/8"	2-61/64" (75.0 mm)	Yellow/Black	7-57/64" (200.4 mm)	0.48 lb (0.22 kg)



Multi-Bit Cushion-Grip Screwdrivers/Nut Drivers

Multi-Bit Screwdriver/Nut Drivers

- Integrated screwdriver/nut driver shaft holds popular tips and converts nut driver sizes



32476



Cat. No.	Nut Driver Sizes	Phillips Bits	Slotted Bits	Square Bits	TORX® Bits	Shank Length	Handle Color	Overall Length	Weight
32476	5/16"	#1, #2	1/4" (6.4 mm), 3/16" (4.8 mm)	—	—	4" (101.6 mm)	Yellow/Black	7-3/4" (196.9 mm)	0.48 lb (0.22 kg)
32477	5/16", 1/4"	#1, #2	1/4" (6.4 mm), 3/16" (4.8 mm)	#1, #2	T10, T15	4" (101.6 mm)	Yellow/Black	7-3/4" (196.9 mm)	0.50 lb (0.23 kg)
32500	3/8", 5/16", 1/4"	#1, #2	1/4" (6.4 mm), 3/16" (4.8 mm)	#1, #2	T10, T15	3" (76.2 mm)	Yellow/Black	7-1/4" (184.2 mm)	0.50 lb (0.23 kg)

Cat. No. 32476 has 5/16" nut driver only, TORX® is a registered trademark of Acument Intellectual Properties, LLC

Stubby Multi-Bit Screwdriver/Nut Driver

- Compact design features standard 1-1/4" (32 mm) shaft allowing easy access to tight work spaces
- Shaft holds four universal tips and converts to two nut driver sizes




32561



Cat. No.	Nut Driver Sizes	Phillips Bits	Slotted Bits	Square Bits	Shank Length	Handle Color	Overall Length	Weight
32561	1/4", 5/16"	#1, #2	3/16" (4.8 mm), 1/4" (6.4 mm)	—	1-17/64" (32.1 mm)	Yellow/Black	3-13/32" (86.5 mm)	0.16 lb (0.07 kg)
32562	1/4", 5/16"	#2	3/16" (4.8 mm)	#1, #2	1-17/64" (32.1 mm)	Yellow/Black	3-13/32" (86.5 mm)	0.16 lb (0.07 kg)

Extended-Reach Multi-Bit Screwdrivers/Nut Drivers

- Interchangeable shaft holds four universal tips and converts to two nut driver sizes
- Extended shafts and blades provide 39% longer reach
- Small diameter shaft for comfortable grip and quick, easy turning



32559



Cat. No.	Nut Driver Sizes	Phillips Bits	Slotted Bits	Square Bits	Shank Length	Handle Color	Overall Length	Weight
32559	1/4", 5/16"	#1, #2	1/4" (6.4 mm), 3/16" (4.8 mm)	—	4-7/64" (104.4 mm)	Yellow/Black	9-7/64" (231.4 mm)	0.41 lb (0.19 kg)
32560	1/4", 5/16"	#2	1/4" (6.4 mm)	#1, #2	4-7/64" (104.4 mm)	Yellow/Black	9-7/64" (231.4 mm)	0.41 lb (0.19 kg)

Multi-Bit Screwdrivers/Nut Drivers

10-in-1 Folding Screwdriver/Nut Driver

- Conveniently folds up for easy storage or to fit into your pocket
- Each driver arm contains four interchangeable bit styles and two nut drivers
- Unfold each driver arm up to a full 180° for straight on driving power, or at 90° for extra leverage on stubborn fasteners
- The quick release button easily unlocks a fully extended driver arm

10-FOLD™



32535

32434
Schrader®



32535
Standard



32536
TORX®



32537
Tamperproof TORX®



32538
Standard Hex



32539
Metric Hex



Cat. No.	Nut Driver Sizes	Phillips Bits	Slotted Bits	Square Bits	Hex Bits	TORX® Bits	Other Bits	Handle Color	Weight
32534	5/16", 1/4"	#1, #2	1/4" (6.4 mm), 3/16" (4.8 mm)	#1, #2	—	—	Valve Core Removal/ Installation - Extractor	Blue	0.37 lb (0.17 kg)
32535	5/16", 1/4"	#1, #2	1/4" (6.4 mm), 3/16" (4.8 mm)	#1, #2	—	T10, T15	—	Black	0.37 lb (0.17 kg)
32536	5/16", 1/4"	—	—	—	—	T6, T7, T8, T10, T15, T20, T25, T27	—	Green	0.37 lb (0.17 kg)
32537	5/16", 1/4"	—	—	—	—	T7, T8, T9, T10, T15, T20, T25, T27	—	Green	0.37 lb (0.17 kg)
32538	5/16", 1/4"	—	—	—	1/16", 5/64", 3/32", 7/64", 1/8", 9/64", 5/32", 3/16"	—	—	Red	0.37 lb (0.17 kg)
32539	5/16", 1/4"	—	—	—	0.9 mm, 1.3 mm, 1.5 mm, 2 mm, 2.5 mm, 3 mm, 4 mm, 5 mm	—	—	Blue	0.37 lb (0.17 kg)

Schrader® is a registered trademark of Schrader-Bridgeport International, Inc., TORX® is a registered trademark of Acument Intellectual Properties, LLC.

Magnetic Screwdriver Bit Sets

Non-Ratcheting Magnetic Screwdriver with 32-Piece Tamperproof Bit Set

- Sturdy bit and screw holding magnet allows for screws to fit securely in place for easy use
- Durable PVC black block allows for easy storage of standard 1/4" bits
- Includes complete tamperproof bit set in block



32510



TAMPERPROOF BIT SET INCLUDED
WITH SET, ALSO SOLD SEPARATELY
32525



STANDARD BIT SET
SOLD SEPARATELY
32526

Cat. No.	Nut Driver Sizes	Phillips Bits	Slotted Bits	Square Bits	Hex Bits	TORX® Bits	Other Bits	Shank Length	Handle Color	Overall Length	Weight
32510	1/4"	—	—	—	3/32", 7/64", 1/8", 9/64", 5/32", 3/16", 2 mm, 2.5 mm, 3 mm, 4 mm, 5 mm	—	Spanner: 4, 6, 8, 10; Tri-Wing®: 1, 2; TORQ-SET®: 6, 8, 10	3-1/2" (88.9 mm)	Yellow/ Black	8" (203.2 mm)	0.71 lb (0.32 kg)
32-Piece Bit Sets											
Cat. No.	Nut Driver Sizes	Phillips Bits	Slotted Bits	Square Bits	Hex Bits	TORX® Bits	Other Bits	Shank Length	Handle Color	Overall Length	Weight
32526	—	#0, #1, #2, #3	3-4, 5-6, 6-8, 8-10, 10-12, 12-14 Screw Sizes	#1, #2, #3	2mm, 3/32", 7/64", 1/8", 9/64", 4mm, 3/16"	T6, T7, T8, T10, T15, T20, T25	Clutch: 5/32" (4 mm), 3/16" (4.8 mm)	—	—	1" (25.4 mm)	0.43 lb (0.20 kg)
32525	—	—	—	—	5/64" (2 mm), 3/32" (2.4 mm), 7/64" (2.8 mm), 1/8" (3.2 mm), 9/64" (3.6 mm), 5/32" (4.0 mm), 3/16" (4.8 mm), 2 mm, 2.5 mm, 3 mm, 4 mm, 5 mm	T7, T8, T10, T15, T20, T25, T27, T30, T40	Spanner: 4, 6, 8, 10; Tri-Wing®: 1, 2, 3, 4	—	—	1" (25.4 mm)	0.43 lb (0.20 kg)

TORX® is a registered trademark of Acument Intellectual Properties, LLC. TORQ-SET® and Tri-Wing® are registered trademarks of Phillips Screw Co.



Multi-Bit Screwdriver/Nut Driver Replacement Parts and Bits

Replacement Parts for Multi-Bit Screwdriver/Nut Drivers

- Precision-machined tips for exact fit into fastener



32398



32396



32397



32484



32478



32784



32781



13105

Cat. No.	Tip Type	For Use With	Package Quantity
32392	—	Heavy Duty (32557) and Ratcheting (32558)	1 Piece
32394	—	Heavy Duty (32557) and Ratcheting (32558)	2 Piece
32395	—	Extended Reach Drivers (32559 and 32560)	1 Piece
32396	—	Stubby Drivers (32561 and 32562)	1 Piece
32397	#2 Phillips; #1 Square	Heavy Duty (32557) and Ratcheting (32558)	2 Bits
32398	#1 Phillips; 1/4" (6.4 mm) Slotted	Heavy Duty (32557), Ratcheting (32558) and Stubby (32561)	2 Bits
32399	#2 Square; 3/16" (4.8 mm) Slotted	Heavy Duty (32557) and Ratcheting (32558)	2 Bits
32400	#1, #2 Phillips	Extended Reach (32559)	2 Bits
32401	3/16" (4.8 mm), 1/4" 6.4 mm) Slotted	Extended Reach (32559)	2 Bits
32410	#2 Square; #2 Phillips	Stubby Driver (32560)	2 Bits
32411	#1 Square; 1/4" (6.4 mm) Slotted	Stubby Driver (32560)	2 Bits
32412	#2 Phillips; 3/16" (4.8 mm) Slotted	Stubby Driver (32561)	2 Bits
32478	#1 Phillips; 3/16" (4.8 mm) Slotted	5-in-1 (32476)	1 Bit
32479	#2 Phillips; 9/32" (7.1 mm) Slotted	5-in-1 (32476)	1 Bit
32482	#1 Phillips; 3/16" (4.8 mm) Slotted	10-in-1, 11-in-1 and 10-Fold™	2 Bits
32483	#2 Phillips; 1/4" (6.4 mm) Slotted	10-in-1, 11-in-1 and 10-Fold™	2 Bits
32484	#1, #2 Square	10-in-1, 11-in-1 and 10-Fold™	2 Bits
67101	#2 Phillips; 3/16" (4.8 mm) Slotted	2-in-1 Rapi-Drive®, 10-in-1, 11-in-1 and 10-Fold	2 Bits
32540	TT7, TT8 TORX®	10-in-1, 11-in-1 and 10-Fold™ Multi-bit Drivers	2 Bits
32541	TT9, TT10 TORX®	10-in-1, 11-in-1 and 10-Fold™ Multi-bit Drivers	2 Bits
32542	TT15, TT20 TORX®	10-in-1, 11-in-1 and 10-Fold™ Multi-bit Drivers	2 Bits
32543	TT25, TT27 TORX®	10-in-1, 11-in-1 and 10-Fold™ Multi-bit Drivers	2 Bits
32544	T6, T7 TORX®	10-in-1, 11-in-1 and 10-Fold™ Multi-bit Drivers	2 Bits
32485	T10 and T15 TORX®	10-in-1, 11-in-1 and 10-Fold™	2 Bits
32545	T8, T10 TORX®	10-in-1, 11-in-1 and 10-Fold™ Multi-bit Drivers	2 Bits
32546	T25, T27 TORX®	10-in-1, 11-in-1 and 10-Fold™ Multi-bit Drivers	2 Bits
32547	3/32", 7/64" Hex	10-in-1, 11-in-1 and 10-Fold™ Multi-bit Drivers	2 Bits
32548	5/32", 3/16" Hex	10-in-1, 11-in-1 and 10-Fold™ Multi-bit Drivers	2 Bits
32549	1/6", 5/64" Hex	10-in-1, 11-in-1 and 10-Fold™ Multi-bit Drivers	2 Bits
32550	1/8", 9/64" Hex	10-in-1, 11-in-1 and 10-Fold™ Multi-bit Drivers	2 Bits
32551	0.9 mm, 1.3 mm Hex	10-in-1, 11-in-1 and 10-Fold™ Multi-bit Drivers	2 Bits
32552	1.5 mm, 2.0 mm Hex	10-in-1, 11-in-1 and 10-Fold™ Multi-bit Drivers	2 Bits
32553	2.5 mm, 3.0 mm Hex	10-in-1, 11-in-1 and 10-Fold™ Multi-bit Drivers	2 Bits
32554	4.0 mm, 5.0 mm Hex	10-in-1, 11-in-1 and 10-Fold™ Multi-bit Drivers	2 Bits
32752	#1, #2 Combo	Combo-Tip Multi-Tool (32505)	2 Bits
32528	Schrader® Valve Core Tool	11-in-1 Schrader (32527)	1 Bit
32770	#1, #2 Phillips	15-in-1 Screwdrivers (32290, 32291, 32292)	1 Bit
32771	#0, #3 Phillips	15-in-1 Screwdrivers (32290, 32291, 32292)	1 Bit
32772	#1, #2 Square	15-in-1 Screwdrivers (32290, 32291, 32292)	1 Bit
32773	T10, T15 TORX®	15-in-1 Screwdrivers (32290, 32291, 32292)	1 Bit
32774	T20, T25 TORX®	15-in-1 Screwdrivers (32290, 32291, 32292)	1 Bit
32775	4 mm, 6 mm Slotted	15-in-1 Screwdrivers (32290, 32291, 32292)	1 Bit
32776	#1, #2 Combo	15-in-1 Screwdrivers (32290, 32291, 32292)	1 Bit
32777	6, 8 Spanner	15-in-1 Screwdrivers (32290, 32291, 32292)	1 Bit
32778	10, 12 Spanner	15-in-1 Screwdrivers (32290, 32291, 32292)	1 Bit
32779	1/8, 9/64 Hex Pin	15-in-1 Screwdrivers (32290, 32291, 32292)	1 Bit
32780	5/32, 3/16 Hex Pin	15-in-1 Screwdrivers (32290, 32291, 32292)	1 Bit
32781	10, 15 Tamperproof	15-in-1 Tamperproof Screwdriver (32291)	1 Bit
32782	20, 25 Tamperproof	15-in-1 Tamperproof Screwdriver (32291)	1 Bit
32783	27, 30 Tamperproof	15-in-1 Tamperproof Screwdriver (32291)	1 Bit
32784	Schrader® Valve Core Tool	15-in-1 HVAC Screwdriver (32292)	1 Bit
13391	#0 Phillips; 3/32" (2.4 mm) Slotted	4-in-1 Electronics Screwdriver (32581, 32585)	2 Bits
13392	#00 Phillips; 1/8" (3.2 mm) Slotted	4-in-1 Electronics Screwdriver (32581, 32585)	2 Bits
13104	T7, T10 Tamperproof TORX®	4-in-1 Electronics Screwdrivers (32581, 32585)	2 Bits
13105	T8, T15 TORX®	4-in-1 Electronics Screwdrivers (32581, 32585)	2 Bits
13231	Schrader® Valve Core Tool; 1/8" (3.2 mm) Slotted	HVAC 8-in-1 Slide Driver™ Screwdriver/Nut Driver (32596)	1 Bit



Meets or exceeds applicable
ASME / ANSI and MIL specifications

Plastic-Handle Screwdrivers

Nickel-chrome, precision-forged
and polished blades with black tips

Tough amber plastic handle

Smooth Comfordome® handles
fit the palm of the hand comfortably.

Chrome-plated shank helps
prevent corrosion

Internal flanges provide solid,
twist-resistant shaft anchor.

**MADE IN
USA**

Plastic-Handle Screwdrivers

Includes core Plastic-Handle Screwdriver features plus:

- Precision-machined Phillips tips provide a more consistent geometric symmetry to ensure accurate fit and torque without slippage
- Small-diameter cabinet-tip shanks for use in recessed holes or tight places and is well-suited for electrical and telecommunications work
- 35% larger than comparable screwdriver handles, the oversized Bull Driver handles deliver up to 50% extra power to perform tough jobs with minimal effort



Cat. No.	Tip Type	Shank Type	Shank Length	Overall Length	Weight
P18	#1 Phillips	Round	8" (203.2 mm)	11-1/2" (292.1 mm)	0.15 lb (0.07 kg)
P28	#2 Phillips	Round	8" (203.2 mm)	11-5/8" (295.3 mm)	0.20 lb (0.09 kg)
P212	#2 Phillips	Round	12" (304.8 mm)	15-5/8" (396.9 mm)	0.25 lb (0.11 kg)
P202	#2 Phillips	Round	20" (508.0 mm)	24-1/2" (622.3 mm)	0.55 lb (0.25 kg)
A000	3/32" (2.4 mm) Keystone	Round	1-1/2" (38.1 mm)	2-7/8" (73.0 mm)	0.32 oz (9.1 g)
A216-3	1/8" (3.2 mm) Cabinet	Round	3" (76.2 mm)	6" (152.4 mm)	0.80 oz (22.7 g)
A216-4	1/8" (3.2 mm) Cabinet	Round	4" (101.6 mm)	7" (177.8 mm)	0.80 oz (22.7 g)
A216-6	1/8" (3.2 mm) Cabinet	Round	6" (152.4 mm)	9" (228.6 mm)	0.80 oz (22.7 g)
A216-8	1/8" (3.2 mm) Cabinet	Round	8" (203.2 mm)	11" (279.4 mm)	0.80 oz (22.7 g)
A216-10	1/8" (3.2 mm) Cabinet	Round	10" (254.0 mm)	13" (330.2 mm)	0.80 oz (22.7 g)
A316-4	3/16" (4.8 mm) Cabinet	Round	4" (101.6 mm)	7-5/8" (193.7 mm)	0.10 lb (0.05 kg)
A316-6	3/16" (4.8 mm) Cabinet	Round	6" (152.4 mm)	9-5/8" (244.5 mm)	0.10 lb (0.05 kg)
A316-8	3/16" (4.8 mm) Cabinet	Round	8" (203.2 mm)	11-5/8" (295.27 mm)	0.15 lb (0.07 kg)
A316-10	3/16" (4.8 mm) Cabinet	Round	10" (254.0 mm)	13-5/8" (346.1 mm)	0.20 lb (0.09 kg)
70155	3/16" (4.8 mm) Cabinet	Round	20" (508.0 mm)	24-1/2" (622.3 mm)	0.45 lb (0.20 kg)

Bull Driver™ Plastic Handle Screwdrivers

BD284	1/4" (6.4 mm) Keystone	Square	4" (101.6 mm)	8-1/2" (215.9 mm)	0.25 lb (0.11 kg)
BD286	1/4" (6.35 mm) Keystone	Square	6" (152.4 mm)	10-1/2" (266.7 mm)	0.30 lb (0.14 kg)
BD306	5/16" (7.9 mm) Keystone	Square	6" (152.4 mm)	11-3/16" (284.2 mm)	0.35 lb (0.16 kg)
BD308	5/16" (7.9 mm) Keystone	Square	8" (203.2 mm)	13-3/16" (335.0 mm)	0.40 lb (0.18 kg)
BD410	3/8" (9.52 mm) Keystone	Square	10" (254.0 mm)	15-3/16" (385.8 mm)	0.60 lb (0.27 kg)
BD412	3/8" (9.52 mm) Keystone	Square	12" (304.8 mm)	17-3/16" (436.6 mm)	0.75 lb (0.34 kg)
BD144	1/4" (6.4 mm) Keystone	Round	4" (101.6 mm)	8-1/2" (215.9 mm)	0.25 lb (0.11 kg)
BD146	1/4" (6.4 mm) Keystone	Round	6" (152.4 mm)	10-1/2" (266.7 mm)	0.25 lb (0.11 kg)
BD156	5/16" (7.9 mm) Keystone	Round	6" (152.4 mm)	11-3/16" (284.2 mm)	0.35 lb (0.16 kg)
BD408	3/8" (9.52 mm) Keystone	Round	8" (203.2 mm)	13-3/16" (335.0 mm)	0.50 lb (0.23 kg)
BD510	3/8" (9.52 mm) Keystone	Round	10" (254 mm)	15-3/16" (385.76 mm)	0.55 lb (0.25 kg)
BD512	3/8" (9.5 mm) Keystone	Round	12" (305 mm)	17-3/16" (437 mm)	0.60 lb (0.27 kg)
BD111	#1 Phillips	Round	3" (76.2 mm)	6-5/8" (168.3 mm)	0.10 lb (0.05 kg)
BD122	#2 Phillips	Round	4" (101.6 mm)	8-1/2" (215.9 mm)	0.20 lb (0.09 kg)
BD133	#3 Phillips	Round	6" (152.4 mm)	11-3/16" (284.2 mm)	0.35 lb (0.16 kg)

Cat. No.	Set Contains	Weight
85276	7 Piece Combination Screwdriver Set	1.1 lb (0.5 kg)

Cat. No. Description

BD284	Keystone Tip Screwdriver 4" Square Shank
BD306	5/16" Keystone Screwdriver 6" Shank
A216-3	1/8" Cabinet Tip Screwdriver 3" Shank
A216-4	Cabinet Tip Screwdriver 4" Round Shank
A216-6	Cabinet Tip Screwdriver 6" Round Shank
BD111	Profiled #1 Phillips Screwdriver 3"
BD122	Profiled #2 Phillips Screwdriver 4"

See page 310 for additional information on warnings.



Plastic-Handle Screwdrivers

Pocket-Clip Screwdrivers

Includes core Plastic-Handle Screwdriver features plus:

- Specially designed for delicate instrument work



A116-3



Cat. No.	Tip Type	Shank Type	Shank Length	Overall Length	Weight
A130-2	1/8" (3.2 mm) Keystone	Round	2" (50.8 mm)	3-7/8" (98.4 mm)	0.80 oz (22.7 g)
A130-3	1/8" (3.2 mm) Keystone	Round	3" (76.2 mm)	4-7/8" (123.8 mm)	0.64 oz (18.1 g)
A116-2	3/32" (2.4 mm) Keystone	Round	2" (50.8 mm)	4-7/16" (112.7 mm)	0.80 oz (22.7 g)
A116-3	3/32" (2.4 mm) Keystone	Round	3" (76.2 mm)	5-7/16" (138.1 mm)	0.48 oz (13.6 g)
A131-2	1/8" (3.2 mm) Keystone	Round	2" (50.8 mm)	4-7/16" (112.7 mm)	0.80 oz (22.7 g)
P12	#0 Phillips	Round	2-1/2" (63.5 mm)	5" (127.0 mm)	0.80 oz (22.7 g)

Magnetic Plastic-Handle Screwdriver

- Powerful magnet built into its shank to hold interchangeable bits and also screws
- Comfortable handle for easier driving
- Interchangeable bits store inside handle for quick access
- Wide selection of bits for different screw types



70035

Cat. No.	Phillips Bits	Slotted Bits	Shank Length	Handle Color	Overall Length	Weight
70035	#1, #2	3/16" (4.8 mm), 9/32" (7.1 mm)	3-3/4" (95.3 mm)	Black and Clear	3-7/16"	0.25 lb (0.11 kg)

Slotted Plastic-Handle Screw-Holding Screwdrivers

- Positive gripping action holds, starts, and drives slotted screws in awkward, hard-to-reach places
- Split-blade screw-holding driver wedges into screw slot
- Not designed for torquing or tightening



K36


Cat. No.	Overall Length	Shank Type	Tip Type	Weight
K23	5-1/4" (133.4 mm)	Round	3/16" (4.8 mm) Slotted	0.80 oz (22.7 g)
K28	10-1/4" (260.4 mm)	Round	3/16" (4.8 mm) Slotted	0.10 lb (0.05 kg)
K34	7-3/4" (196.9 mm)	Round	1/4" (6.4 mm) Slotted	0.10 lb (0.05 kg)
K36	9-3/4" (247.7 mm)	Round	1/4" (6.4 mm) Slotted	0.15 lb (0.07 kg)
K38	11-3/4" (298.5 mm)	Round	1/4" (6.4 mm) Slotted	0.20 lb (0.09 kg)
K44	8-1/4" (209.6 mm)	Round	5/16" (7.9 mm) Slotted	0.25 lb (0.11 kg)
K46	10-1/4" (260.4 mm)	Round	5/16" (7.9 mm) Slotted	0.25 lb (0.11 kg)
K48	12-1/4" (311.2 mm)	Round	5/16" (7.9 mm) Slotted	0.30 lb (0.14 kg)



Cat. No.	Set Contains	Weight
SK234	Slotted Holding Screwdriver Set 3 Pc	0.40 lb (0.18 kg)
Cat. No.	Description	
K23	3/16" Screw Holding Screwdriver 3"	
K34	Slotted Screw Holding Screwdriver 4"	
K46	Slotted Holding Screwdriver 10-1/4" L	

Precision blade for use with small precision screws. Blade thickness of 0.028" expanding to 0.045".
 ‡ Blade thickness of 0.043" expanding to 0.085". K21 and K23 have pocket clips.





Screw-Holding Screwdrivers

Phillips-Tip Screw-Holding Screwdrivers

- Positive gripping action holds and starts Phillips screws in awkward, hard-to-reach places
- Blade separates to hold the fastener
- Not designed for torquing or tightening



Cat. No.	Overall Length	Shank Type	Tip Type	Weight
K14	5" (127.0 mm)	Round	Phillips	0.80 oz (22.7 g)
K16	7" (177.8 mm)	Round	Phillips	0.80 oz (22.7 g)
K19	9" (228.6 mm)	Round	Phillips	0.80 oz (22.7 g)



K16

Impact and Torque Drivers

Reversible Impact-Driver Set

- Rugged, hand-impact driver turns rusted, frozen, or other stubborn screws
- Can also be used with 3/8" square-drive impact sockets
- Internal, spring-loaded, helical design transforms the impact of a hammer blow to up to 200 ft.-lbs. of shock torque
- Easily reverses for tightening or loosening screws
- Constructed of high-grade alloy steel that has been heat-treated for added strength
- Reclosable, seal-tight vinyl pouch with hang-up grommet



70229
BITS FOR IMPACT
DRIVER SET



70220



Cat. No.	Phillips Bits	Nut Driver Sizes	Slotted Bits	Included	Weight
70220	#2 and #4	5/16"	5/16" (7.9 mm) and 1/2" (12.7 mm)	3/8" (9.5 mm) Square Drive fitting Adapter	2.2 lb (1.0 kg)

Torque Screwdriver Set

- Compact, easy to use set includes the Torque Screwdriver, a 6-piece bit set and a rugged case with foam inserts for a tight, organized fit
- Increased usability and readability plus a wider torque range (5-40 in. lbs)
- Tri-lobular design with a textured finish for better grip
- Lightweight, aluminum frame
- N.I.S.T. traceable calibration certificate
- Set includes six 3-1/2" (89 mm) power drivers and a 1/4" nut driver



Cat. No.	Included	Weight
57032	Phillips: #1 and #2; Slotted: 3/16" (4.8 mm) and 1/4" (6.4 mm); Square: #1 and #2 and 1/4" Nut Driver	1.0 lb (0.5 kg)



57032



Heavy-Duty Cushion-Grip Nut Drivers

Through-handle full-hollow shaft

design for torquing hex nuts onto threaded rod of any length




Wrench-assist
feature for
added torque



**Rare-earth
magnetic tip**
holds nut in
place while
fastening



**Color-coded
ends and tips**
for easy size
identification



6 sizes 1/4", 5/16", 3/8",
7/16", 1/2" and 9/16" sizes

**MADE IN
USA**
GLOBAL
COMPONENTS

Heavy-Duty Nut Drivers



635-1/4



635-5/16



635-3/8



635-7/16



635-1/2



635-9/16



Cat. No.	Nut Driver Sizes	Shaft Length	Color Code	Overall Length	Weight
635-1/4	1/4"	4" (101.6 mm)	Red	9" (228.6 mm)	0.30 lb (0.14 kg)
635-5/16	5/16"	4" (101.6 mm)	Yellow	9" (228.6 mm)	0.30 lb (0.14 kg)
635-3/8	3/8"	4" (101.6 mm)	Blue	9" (228.6 mm)	0.30 lb (0.14 kg)
635-7/16	7/16"	4" (101.6 mm)	Brown	9-25/64" (238.5 mm)	0.40 lb (0.18 kg)
635-1/2	1/2"	4" (101.6 mm)	Red	9-25/64" (238.5 mm)	0.50 lb (0.23 kg)
635-9/16	9/16"	4" (101.6 mm)	Orange	9-25/64" (238.5 mm)	0.50 lb (0.23 kg)


Cat. No.	Set Contains	Weight
635-6	6 Piece Heavy-Duty Nut Driver Set	2.5 lb (1.1 kg)
Cat. No.	Description	
635-1/4	1/4" Heavy-Duty Nut Driver	
635-5/16	5/16" Heavy-Duty Nut Driver	
635-3/8	3/8" Heavy-Duty Nut Driver	
635-7/16	7/16" Heavy-Duty Nut Driver	
635-1/2	1/2" Heavy-Duty Nut Driver	
635-9/16	9/16" Heavy-Duty Nut Driver	

Cat. No.	Set Contains	Weight
635-4	4 Piece Heavy-Duty Nut Driver Set	1.4 lb (0.6 kg)
Cat. No.	Description	
635-1/4	1/4" Heavy-Duty Nut Driver	
635-5/16	5/16" Heavy-Duty Nut Driver	
635-3/8	3/8" Heavy-Duty Nut Driver	
635-7/16	7/16" Heavy-Duty Nut Driver	



Cushion-Grip Nut Drivers

Meets or exceeds applicable ASME / ANSI and MIL specifications



Handle end is also color coded for easy identification



Tip-Ident® quickly identifies nut driver and size



Magnetic-Tip Hollow-Shaft Nut Drivers

Includes core Cushion-Grip Nut Driver features plus:

- Exclusive hollow shaft* design with Rare Earth magnetic tip features unobstructed pass-through, even on long bolts



630-3/8M

Cat. No.	Nut Driver Sizes	Shaft Length	Color Code	Overall Length	Weight
610-1/4M	1/4"	1-1/2" (38.1 mm)	Red	3-1/2" (88.9 mm)	0.10 lb (0.05 kg)
610-5/16M	5/16"	1-1/2" (38.1 mm)	Yellow	3-1/2" (88.9 mm)	0.10 lb (0.05 kg)
610-3/8M	3/8"	1-1/2" (38.1 mm)	Blue	3-1/2" (88.9 mm)	0.10 lb (0.05 kg)
630-3/16M	3/16"	3" (76.2 mm)	Black	6-3/4" (171.5 mm)	0.20 lb (0.09 kg)
630-1/4M	1/4"	3" (76.2 mm)	Red	6-3/4" (171.5 mm)	0.20 lb (0.09 kg)
630-5/16M	5/16"	3" (76.2 mm)	Yellow	6-3/4" (171.5 mm)	0.20 lb (0.09 kg)
630-11/32M	11/32"	3" (76.2 mm)	Green	6-3/4" (171.5 mm)	0.20 lb (0.09 kg)
630-3/8M	3/8"	3" (76.2 mm)	Blue	6-3/4" (171.5 mm)	0.20 lb (0.09 kg)
630-7/16M	7/16"	3" (76.2 mm)	Brown	7-5/16" (185.7 mm)	0.25 lb (0.11 kg)
630-1/2M	1/2"	3" (76.2 mm)	Red	7-5/16" (185.7 mm)	0.25 lb (0.11 kg)
646-3/16M	3/16"	6" (152.4 mm)	Black	9-3/4" (247.7 mm)	0.25 lb (0.11 kg)
646-1/4M	1/4"	6" (152.4 mm)	Red	9-3/4" (247.7 mm)	0.25 lb (0.11 kg)
646-5/16M	5/16"	6" (152.4 mm)	Yellow	9-3/4" (247.7 mm)	0.25 lb (0.11 kg)
646-11/32M	11/32"	6" (152.4 mm)	Green	9-3/4" (247.7 mm)	0.25 lb (0.11 kg)
646-3/8M	3/8"	6" (152.4 mm)	Blue	9-3/4" (247.7 mm)	0.30 lb (0.14 kg)
646-7/16M	7/16"	6" (152.4 mm)	Brown	10-5/16" (261.9 mm)	0.35 lb (0.16 kg)
646-1/2M	1/2"	6" (152.4 mm)	Red	10-5/16" (261.9 mm)	0.35 lb (0.16 kg)
618-1/4M	1/4"	18" (457.2 mm)	Red	21-3/4" (552.5 mm)	0.50 lb (0.23 kg)
618-5/16M	5/16"	18" (457.2 mm)	Yellow	21-3/4" (552.5 mm)	0.50 lb (0.23 kg)

*3/16" magnetic nut driver does not have a hollow shaft.

Cat. No.	Set Contains	Weight
631M	Magnetic Nut Driver Set 3" Shaft, 7 Pc	1.5 lb (0.7 kg)

Cat. No.	Description
630-3/16M	3/16" Magnetic Tip Nut Driver 3" Shaft
630-1/4M	1/4" Magnetic Tip Nut Driver 3" Shaft
630-5/16M	5/16" Nut Driver with Hollow Shaft
630-11/32M	11/32" Magnetic Nut Driver 3" Shaft
630-3/8M	3/8" Magnetic Tip Nut Driver 3" Shaft
630-7/16M	7/16" Magnetic Tip Nut Driver 3" Shaft
630-1/2M	1/2" Magnetic Tip Nut Driver 3" Shank

Cat. No.	Set Contains	Weight
647M	Magnetic Nut Driver Set 6" Shafts, 7 Pc	1.5 lb (0.7 kg)

Cat. No.	Description
646-3/16M	3/16" Magnetic Tip Nut Driver 6" Shaft
646-1/4M	1/4" Magnetic Tip Nut Driver 6" Shaft
646-5/16M	5/16" Magnetic Nut Driver Cushion-Grip
646-11/32M	11/32" Magnetic Nut Driver 6" Shaft
646-3/8M	3/8" Magnetic Tip Nut Driver 6" Shaft
646-7/16M	7/16" Magnetic Tip Nut Driver 6" Shaft
646-1/2M	1/2" Magnetic Tip Nut Driver 6" Shaft

Cat. No.	Set Contains	Weight
630M	Magnetic Nut Driver Set 3" Shank 2 Pc	0.40 lb (0.18 kg)

Cat. No.	Description
630-1/4M	1/4" Magnetic Tip Nut Driver 3" Shaft
630-5/16M	5/16" Nut Driver with Hollow Shaft

Cat. No.	Set Contains	Weight
646M	Nut Driver Set 6" Shafts, Magnetic 2 Pc	0.50 lb (0.23 kg)

Cat. No.	Description
646-1/4M	1/4" Magnetic Tip Nut Driver 6" Shaft
646-5/16M	5/16" Magnetic Nut Driver Cushion-Grip

Cat. No.	Set Contains	Weight
610M	Stubby Nut Driver Set 1-1/2" Shafts Magnetic 2 Pc	0.20 lb (0.09 kg)

Cat. No.	Description
610-1/4M	Magnetic Nut Driver 1-1/2" Hollow Shaft
610-5/16M	5/16" Magnetic Nut Driver 1-1/2" Shaft



Cushion-Grip Nut Drivers

Hollow-Shaft Nut Drivers

Includes core Cushion-Grip Nut Driver features plus:

- 3" (76 mm) length for most long bolt and stud applications
- 6" (152 mm) length reaches into deep recesses and fits over extra-long bolts and studs
- Exclusive hollow shaft* design with Rare Earth magnetic tip features unobstructed pass-through, even on long bolts

Refer to the insulated section for insulated nut drivers.



Cat. No.	Nut Driver Sizes	Shaft Length	Color Code	Overall Length	Weight
610-1/4	1/4"	1-1/2" (38.1 mm)	Red	3-1/2" (88.9 mm)	0.10 lb (0.05 kg)
610-5/16	5/16"	1-1/2" (38.1 mm)	Yellow	3-1/2" (88.9 mm)	0.10 lb (0.05 kg)
630-3/16	3/16"	3" (76.2 mm)	Black	6-3/4" (171.5 mm)	0.20 lb (0.09 kg)
630-1/4	1/4"	3" (76.2 mm)	Red	6-3/4" (171.5 mm)	0.20 lb (0.09 kg)
630-5/16	5/16"	3" (76.2 mm)	Yellow	6-3/4" (171.5 mm)	0.20 lb (0.09 kg)
630-11/32	11/32"	3" (76.2 mm)	Green	6-3/4" (171.5 mm)	0.20 lb (0.09 kg)
630-3/8	3/8"	3" (76.2 mm)	Blue	6-3/4" (171.5 mm)	0.20 lb (0.09 kg)
630-7/16	7/16"	3" (76.2 mm)	Brown	7-5/16" (185.7 mm)	0.25 lb (0.11 kg)
630-1/2	1/2"	3" (76.2 mm)	Red	7-5/16" (185.7 mm)	0.25 lb (0.11 kg)
630-9/16	9/16"	4" (101.6 mm)	Orange	9-3/8" (238.1 mm)	0.35 lb (0.16 kg)
630-5/8	5/8"	4" (101.6 mm)	Yellow	9-3/8" (238.1 mm)	0.35 lb (0.16 kg)
646-3/16	3/16"	6" (152.4 mm)	Black	9-3/4" (247.7 mm)	0.25 lb (0.11 kg)
646-1/4	1/4"	6" (152.4 mm)	Red	9-3/4" (247.7 mm)	0.25 lb (0.11 kg)
646-5/16	5/16"	6" (152.4 mm)	Yellow	9-3/4" (247.7 mm)	0.25 lb (0.11 kg)
646-11/32	11/32"	6" (152.4 mm)	Green	9-3/4" (247.7 mm)	0.25 lb (0.11 kg)
646-3/8	3/8"	6" (152.4 mm)	Blue	9-3/4" (247.7 mm)	0.30 lb (0.14 kg)
646-7/16	7/16"	6" (152.4 mm)	Brown	10-5/16" (261.9 mm)	0.35 lb (0.16 kg)
646-1/2	1/2"	6" (152.4 mm)	Red	10-5/16" (261.9 mm)	0.35 lb (0.16 kg)
646-9/16	9/16"	6" (152.4 mm)	Orange	11-3/8" (288.9 mm)	0.40 lb (0.18 kg)
646-5/8	5/8"	6" (152.4 mm)	Yellow	11-3/8" (288.9 mm)	0.40 lb (0.18 kg)
Metric					
630-4MM	4 mm	3" (76.2 mm)	Red	6-3/4" (171.5 mm)	0.20 lb (0.09 kg)
630-4.5MM	4.5 mm	3" (76.2 mm)	Yellow	6-3/4" (171.5 mm)	0.20 lb (0.09 kg)
630-5MM	5 mm	3" (76.2 mm)	Black	6-3/4" (171.5 mm)	0.20 lb (0.09 kg)
630-6MM	6 mm	3" (76.2 mm)	Red	6-3/4" (171.5 mm)	0.20 lb (0.09 kg)
630-7MM	7 mm	3" (76.2 mm)	Orange	6-3/4" (171.5 mm)	0.20 lb (0.09 kg)
630-8MM	8 mm	3" (76.2 mm)	Yellow	6-3/4" (171.5 mm)	0.20 lb (0.09 kg)
630-10MM	10 mm	3" (76.2 mm)	Blue	6-3/4" (171.5 mm)	0.20 lb (0.09 kg)
630-11MM	11 mm	3" (76.2 mm)	Brown	7-5/16" (185.7 mm)	0.20 lb (0.09 kg)

*3/16" magnetic nut driver does not have a hollow shaft.



630-11MM

Cat. No.	Set Contains	Weight
631	Nut Driver Set 3" Shafts, 7 Pc	1.5 lb (0.7 kg)

Cat. No. Description

630-3/16	3/16" Hollow Shaft Nut Driver 3" Shaft
630-1/4	1/4" Nut Driver 3" Shaft Cushioned
630-5/16	5/16" Nut Driver Cushion-Grip 3" Shaft
630-11/32	11/32" Nut Driver 3" Hollow Shaft
630-3/8	3/8" Hollow Shaft Nut Driver 3" Shaft
630-7/16	7/16" Hollow Nut Driver 3" Cushioned
630-1/2	1/2" Nut Driver 3" Shaft Cushion-Grip

Cat. No.	Set Contains	Weight
647	Nut Driver Set 6" Shafts, 7 Pc	1.7 lb (0.8 kg)

Cat. No. Description

646-3/16	3/16" Nut Driver 6" Shaft
646-1/4	1/4" Hollow Shaft Nut Driver 6" Shaft
646-5/16	5/16" Hollow Shaft Nut Driver 6" Shaft
646-11/32	11/32" Nut Driver 6" Hollow Shaft
646-3/8	3/8" Hollow Shaft Nut Driver 6" Shaft
646-7/16	7/16" Nut Driver 6" Hollow Shaft
646-1/2	1/2" Nut Driver 6" Hollow Shaft

Cat. No.	Set Contains	Weight
65160	7 Piece Metric Nut Driver Set 3" Shafts	1.5 lb (0.7 kg)

Cat. No. Description

630-5MM	5 mm Cushion Grip Nut Driver 3" Shaft
630-5.5MM	5.5 mm Cushion-Grip Hollow-Shank Nut Driver
630-6MM	6 mm Cushion-Grip Nut Driver, 3" Hollow Shaft
630-7MM	7 mm Cushion Grip Nut Driver 3" Shaft
630-8MM	8 mm Cushion-Grip Nut Driver, 3" Hollow Shaft
630-9MM	9 mm Cushion-Grip Nut Driver, 3" Hollow Shaft
630-10MM	10 mm Cushion Grip Nut Driver 3" Shaft

Cat. No.	Set Contains	Weight
633	Nut Driver Set, 4 Pc	1.3 lb (0.6 kg)

Cat. No. Description


630-1/4	1/4" Nut Driver 3" Shaft Cushioned
630-5/16	5/16" Nut Driver Cushion-Grip 3" Shaft
630-3/8	3/8" Hollow Shaft Nut Driver 3" Shaft
630-9/16	9/16" Hollow Shaft Nut Driver 4" Shaft

Cat. No.	Set Contains	Weight
610	Stubby Nut Driver Set 1-1/2" Shafts 2 Pc	0.20 lb (0.09 kg)

Cat. No. Description

610-1/4	1/4" Stubby Nut Driver 1-1/2" Shaft
610-5/16	5/16" Stubby Nut Driver Cushion Grip





Cushion-Grip Nut Drivers

Coated Hollow-Shaft Nut Drivers

Includes core Cushion-Grip Nut Driver features plus:

- Entire shaft plastic coated for circuit protection only. NOT INSULATED
- Special plastic coating resists cutting, cracking and chipping
- Thin coating permits use in confined areas



640-1/2

WARNING: NOT insulated. Coating is intended for protection of circuits only.

Cat. No.	Nut Driver Sizes	Shaft Length	Color Code	Overall Length	Weight
640-3/16	3/16"	3" (76.2 mm)	Black	6-3/4" (171.5 mm)	0.25 lb (0.11 kg)
640-1/4	1/4"	3" (76.2 mm)	Red	6-3/4" (171.5 mm)	0.25 lb (0.11 kg)
640-5/16	5/16"	3" (76.2 mm)	Yellow	6-3/4" (171.5 mm)	0.25 lb (0.11 kg)
640-3/8	3/8"	3" (76.2 mm)	Blue	6-3/4" (171.5 mm)	0.25 lb (0.11 kg)
640-7/16	7/16"	3" (76.2 mm)	Brown	7-5/16" (185.7 mm)	0.30 lb (0.14 kg)
640-1/2	1/2"	3" (76.2 mm)	Red	7-5/16" (185.7 mm)	0.25 lb (0.11 kg)
640-9/16	9/16"	4" (101.6 mm)	Orange	9-3/8" (238.1 mm)	0.40 lb (0.18 kg)
640-5/8	5/8"	4" (101.6 mm)	Yellow	9-3/8" (238.1 mm)	0.40 lb (0.18 kg)

*3/16" magnetic nut driver does not have a hollow shaft.

Cushion-Grip Multi-Nut Drivers

Heavy-Duty Multi-Nut Drivers

- Multiple sizes in one convenient tool
- Heavy-duty handle and shaft exceed the torque performance of regular nut drivers
- Wrench-assist feature for added torque




32800

Cat. No.	Description	Nut Driver Sizes	Shaft Length	Overall Length	Weight
32800	6-in-1 Multi-Nut Driver Heavy Duty	3/16", 1/4", 5/16", 3/8", 7/16", 9/16"	4" (101.6 mm)	9-1/2" (241.3 mm)	1.2 lb (0.5 kg)
32801	5-in-1 Multi-Nut Driver Heavy Duty	3/16", 1/4", 5/16", 3/8", 9/16"	4" (101.6 mm)	9-7/64" (231.4 mm)	1.0 lb (0.5 kg)



Plastic-Handle Nut Drivers

Meets or exceeds applicable ASME / ANSI and MIL specifications.



MADE IN
USA

Hollow-Shaft Nut Drivers

Includes core Plastic-Handle Nut Driver features plus:

- Standard length works for most applications
- Fits over long bolts and studs
- Cat. Nos. SS8, SS10 and SS12 have smaller shaft length for work in close quarters



S11



Cat. No.	Nut Driver Sizes	Shaft Length	Handle Color	Overall Length	Weight
SS8	1/4"	1-1/2" (38.1 mm)	Red	3-3/4" (95.3 mm)	0.15 lb (0.07 kg)
SS10	5/16"	1-1/2" (38.1 mm)	Amber	3-3/4" (95.3 mm)	0.15 lb (0.07 kg)
SS12	3/8"	1-1/2" (38.1 mm)	Blue	3-3/4" (95.3 mm)	0.15 lb (0.07 kg)
S5	5/32"	3" (76.2 mm)	Amber	6-1/2" (165.1 mm)	0.10 lb (0.05 kg)
S6	3/16"	3" (76.2 mm)	Black	6-5/8" (168.3 mm)	0.10 lb (0.05 kg)
S7	7/32"	3" (76.2 mm)	Brown	6-5/8" (168.3 mm)	0.10 lb (0.05 kg)
S8	1/4"	3" (76.2 mm)	Red	6-5/8" (168.3 mm)	0.15 lb (0.07 kg)
S9	9/32"	3" (76.2 mm)	Orange	6-5/8" (168.3 mm)	0.15 lb (0.07 kg)
S10	5/16"	3" (76.2 mm)	Amber	6-5/8" (168.3 mm)	0.15 lb (0.07 kg)
S11	11/32"	3" (76.2 mm)	Green	6-5/8" (168.3 mm)	0.15 lb (0.07 kg)
S12	3/8"	3" (76.2 mm)	Blue	6-5/8" (168.3 mm)	0.15 lb (0.07 kg)
S14	7/16"	3" (76.2 mm)	Brown	7" (177.8 mm)	0.20 lb (0.09 kg)
S16	1/2"	3" (76.2 mm)	Red	7" (177.8 mm)	0.20 lb (0.09 kg)
S18	9/16"	4" (101.6 mm)	Red	8-1/2" (215.9 mm)	0.30 lb (0.14 kg)
S20	5/8"	4" (101.6 mm)	Red	8-1/2" (215.9 mm)	0.30 lb (0.14 kg)
S66	3/16"	6" (152.4 mm)	Black	9-5/8" (244.5 mm)	0.15 lb (0.07 kg)
S86	1/4"	6" (152.4 mm)	Red	9-5/8" (244.5 mm)	0.15 lb (0.07 kg)
S106	5/16"	6" (152.4 mm)	Amber	9-5/8" (244.5 mm)	0.15 lb (0.07 kg)
S116	11/32"	6" (152.4 mm)	Green	9-5/8" (244.5 mm)	0.15 lb (0.07 kg)
S126	3/8"	6" (152.4 mm)	Blue	9-5/8" (244.5 mm)	0.15 lb (0.07 kg)
S146	7/16"	6" (152.4 mm)	Brown	10" (254.0 mm)	0.20 lb (0.09 kg)
S166	1/2"	6" (152.4 mm)	Red	10" (254.0 mm)	0.20 lb (0.09 kg)

Cat. No.	Set Contains	Weight
K7	Nut Driver Set 3" Shanks, 7 Pc	1.2 lb (0.5 kg)

Cat. No.	Description
S6	3/16" Hollow Shank Nut Driver 3" Shank
S8	1/4" Hollow Shank Nut Driver 3" Shank
S10	5/16" Nut Driver 3" Hollow Shaft
S11	11/32" Nut Driver, Plastic Grip 3" L
S12	3/8" Hollow Shaft Nut Driver 3" Shaft
S14	7/16" Hollow Shank Nut Driver 3" Shank
S16	1/2" Nut Driver 3" Hollow Shank

Cat. No.	Set Contains	Weight
89904	7 Piece Nut Driver Set 6" Shanks	1.2 lb (0.5 kg)

Cat. No.	Description
S66	3/16" Individual Nut Driver 6" Shank
S86	1/4" Individual Nut Driver 6" Shank
S106	5/16" Individual Nut Driver 6" Shaft
S116	11/32" Individual Nut Driver 6" Shaft
S126	3/8" Individual Nut Driver 6" Shaft
S146	7/16" Individual Nut Driver 6" Shank
S166	1/2" Individual Nut Driver 6" Shank

Set Cat. No. K7 includes a vinyl pouch which hangs up or rolls up



Plastic Handle, Hollow-Shaft Nut Drivers

Super-Long Nut Drivers - 18" (457 mm) Shafts

Includes core Plastic-Handle Nut Driver features plus:

- Ideal for reaching into walls and other hard-to-reach places where added length is necessary
- Cat. No. S1018 has a non-magnetic tip; Cat. Nos. S818M and S1018M have magnetic tips



S1018



Cat. No.	Nut Driver Sizes	Shaft Length	Handle Color	Overall Length	Weight
S1018	5/16"	18" (457.2 mm)	Amber	21-5/8" (549.27 mm)	0.25 lb (0.11 kg)
S818M	1/4"	18" (457.2 mm)	Red	21-5/8" (549.3 mm)	0.25 lb (0.11 kg)
S1018M	5/16"	18" (457.2 mm)	Amber	21-5/8" (549.3 mm)	0.25 lb (0.11 kg)

Metric Nut Drivers

Includes core Plastic-Handle Nut Driver features plus:

- Standard length works for most applications
- Fits over long bolts and studs



70209

Cat. No.	Nut Driver Sizes	Shaft Length	Handle Color	Overall Length	Weight
70204	4 mm	3" (76.2 mm)	Black	6-5/8" (168.3 mm)	0.10 lb (0.05 kg)
70245	4.5 mm	3" (76.2 mm)	Black	6-5/8" (168.3 mm)	0.10 lb (0.05 kg)
70205	5 mm	3" (76.2 mm)	Black	6-5/8" (168.3 mm)	0.15 lb (0.07 kg)
70255	5.5 mm	3" (76.2 mm)	Black	6-5/8" (168.3 mm)	0.15 lb (0.07 kg)
70206	6 mm	3" (76.2 mm)	Black	6-5/8" (168.3 mm)	0.15 lb (0.07 kg)
70207	7 mm	3" (76.2 mm)	Black	6-5/8" (168.3 mm)	0.15 lb (0.07 kg)
70208	8 mm	3" (76.2 mm)	Black	6-5/8" (168.3 mm)	0.15 lb (0.07 kg)
70209	9 mm	3" (76.2 mm)	Black	6-5/8" (168.3 mm)	0.15 lb (0.07 kg)
70210	10 mm	3" (76.2 mm)	Black	7" (177.8 mm)	0.15 lb (0.07 kg)
70211	11 mm	3" (76.2 mm)	Black	7" (177.8 mm)	0.20 lb (0.09 kg)

Cat. No.	Set Contains	Weight
70200	Metric Nut Driver Set 3" Shafts 10 Pc	1.9 lb (0.8 kg)

Cat. No.	Description
70204	4 mm Metric Nut Driver 3" Shaft
70245	4.5 mm Metric Nut Driver 3" Shaft
70205	5 mm Metric Nut Driver 3" Shaft
70255	5.5 mm Metric Nut Driver 3" Shaft
70206	6 mm Metric Nut Driver 3" Shaft
70207	7 mm Metric Nut Driver 3" Shaft
70208	8 mm Metric Nut Driver 3" Shaft
70209	9 mm Metric Nut Driver 3" Shaft
70210	10 mm Metric Nut Driver 3" Shaft
70211	11 mm Metric Nut Driver 3" Shaft

Set includes white enameled metal stand with identification labels for easy selection of tool

Plastic Handle Nut Drivers

Magnetic Nut Drivers - Solid Shafts

Includes core Plastic-Handle Nut Driver features plus:

- Powerful nut-holding magnet built into solid shaft



S818M



Cat. No.	Nut Driver Sizes	Shaft Length	Handle Color	Overall Length	Weight
S8M	1/4"	3" (76.2 mm)	Red	6-5/8" (168.3 mm)	0.15 lb (0.07 kg)
S10M	5/16"	3" (76.2 mm)	Amber	6-5/8" (168.3 mm)	0.15 lb (0.07 kg)
S86M	1/4"	6" (152.4 mm)	Yellow	9-5/8" (244.5 mm)	0.15 lb (0.07 kg)
S106M	5/16"	6" (152.4 mm)	Amber	9-5/8" (244.5 mm)	0.15 lb (0.07 kg)
S126M	3/8"	6" (152.4 mm)	Blue	9-5/8" (244.5 mm)	0.15 lb (0.07 kg)

Tapping Tools

Cushion-Grip Multi-Bit Tap Tool Driver

- Increases job speed by combining taps and drivers in one tool
- Six common tap sizes (6-32, 8-32, 10-32, 10-24, 12-24, 1/4-20)
- Each tap size rethreads to next larger size if threads are stripped



32517


32518
REPLACEMENT TAP

Cat. No.	Nut Driver Sizes	Phillips Bits	Slotted Bits	Other Bits	Shank Length	Handle Color	Overall Length	Weight
32517	1/4", 5/16", 3/8"	#1, #2	1/4" (6.4 mm), 3/16" (4.8 mm)	Taps: 6-32, 8-32, 10-32, 10-24, 12-24, 1/4-20	4" (101.6 mm)	Yellow/Black	7-3/4" (196.9 mm)	0.50 lb (0.23 kg)

Cushion-Grip 6-in-1 Tap Tool

- Quickly forms new threads, re-forms burred threads, and cleans out plaster obstructions
- Each tap size rethreads to next larger size if threads are stripped



626


628-20 (10-24, 12-24, 1/4-20)
626-32 (6-32, 8-32, 10-32)
REPLACEMENT TAPS

Cat. No.	Tap Sizes	Overall Length	Weight
626	6-in-1 Tap 6-32, 8-32, 10-32, 10-24, 12-24, 1/4-20	7-3/4" (196.9 mm)	0.25 lb (0.11 kg)

6-in-1 Tapping Tool

- Quickly forms new threads, re-forms burred threads, and cleans out plaster obstructions
- Each tap size rethreads to next larger size if threads are stripped
- Two high-carbon steel taps are secured in reversible holder



627-20


628-20 (10-24, 12-24, 1/4-20)
626-32 (6-32, 8-32, 10-32)
REPLACEMENT TAPS

Cat. No.	Tap Sizes	Overall Length	Weight
627-20	6-32, 8-32, 10-32, 10-24, 12-24, 1/4-20	7-5/8" (193.7 mm)	0.35 lb (0.16 kg)

Triple Taps

- Quickly forms new threads, re-forms burred threads, and cleans out plaster obstructions
- Each tap size rethreads to next larger size if threads are stripped




625-24


626-24 (6-32, 8-32, 10-24)
626-32 (6-32, 8-32, 10-32)
REPLACEMENT TAPS

Cat. No.	Tap Sizes	Overall Length	Weight
625-24	6-32, 8-32, 10-24	7-1/8" (181.0 mm)	0.20 lb (0.09 kg)
625-32	6-32, 8-32, 10-32	7-1/8" (181.0 mm)	0.20 lb (0.09 kg)





Scratch Awls

Cushion-Grip Scratch Awl

- Professional, heavy-duty, hard-pointed awl
- Scribes metal, starts screw holes, performs a variety of piercing and punching jobs
- Rigid, chrome-plated, heat-treated, tempered-steel shank has full reinforcing bolster at handle for extra strength and impact reinforcement
- Cat. No. 650DD has plated metal strike cap to protect handle from hammer blows and is engineered, manufactured and tested for prying, chiseling and punching



Cat. No.
650 only



650DD

Cat. No.	Shank Length	Overall Length	Weight
650	3-1/2" (88.9 mm)	7-7/8" (200.0 mm)	0.25 lb (0.11 kg)
650DD	3-1/2" (88.9 mm)	7-7/8" (200.0 mm)	0.30 lb (0.14 kg)

Steel Scratch Awl

- One-piece forged-steel blade and bolstered shank
- Heat-treated for long life
- Well-balanced for top efficiency during use
- Black finish for rust resistance



66385

Cat. No.	Overall Length	Shank Length	Weight
66385	7" (177.8 mm)	3-1/2" (88.9 mm)	0.30 lb (0.14 kg)

Conduit Reamers

Conduit-Fitting and Reaming Screwdriver

- Hooded-blade design keeps tip from slipping out of screws, especially when tightening hard-to-reach conduit fittings. Thicker hood is designed for rugged use
- Reams both the inside and outside of the conduit at the same time
- 5/16" (8 mm) screwdriver tip with 2-1/2" (64 mm) long shank
- Longer Cushion-Grip handle provides comfort and more torque for reaming
- Replaceable reaming blade is now held in place with a 1/6" (1.5 mm) set screw



85191

Cat. No.	Conduit Size	Overall Length	Weight
85191	1/2" (12.7 mm), 3/4" (19.1 mm), 1" (25.4 mm)	7-1/2" (190.5 mm)	0.50 lb (0.23 kg)



19353
CONDUIT REAMER
REPLACEMENT BLADE, 2pk

Conduit Reamer

- Locks onto screwdrivers; reams and smooths thin-wall conduit
- Reams ID and OD at the same time
- Two set-screws for round- and square-shank screwdrivers
- Fits up to 3/8" (10 mm) keystone-tip screwdrivers
- NOT for use on power tools



19352



19353
CONDUIT REAMER
REPLACEMENT BLADE, 2pk

Cat. No.	Conduit Size	Overall Length	Weight
19352	1/2" (12.7 mm), 3/4" (19.1 mm), 1" (25.4 mm)	6-3/4" (171.5 mm)	0.20 lb (0.09 kg)

Power Conduit Reamer

IMPACT RATED!

- Ream conduit and install fittings in a fraction of the time
- Designed to fit into power drill chucks and quick release adapters; impact ready
- Includes precision engineered replaceable reaming blade
- Replacement blades are available and the only approved blade for use in this tool
- Replacement bits are available but any standard 1/4" hex bit will work

Precision engineered
replaceable reaming blade



1/4" hex
quick connect



85091

4x Stronger
Bit Retention



19353
CONDUIT REAMER
REPLACEMENT BLADE, 2pk



NOTE: Read and follow safety instructions in power tool owner's manual.

Cat. No.	Conduit Size	Overall Length	Weight
85091	1/2" (12.7 mm), 3/4" (19.1 mm), 1" (25.4 mm)	5-3/4" (146.1 mm)	0.33 lb (0.15 kg)

See page 310 for additional information on warnings.




Power Driver Bits

Power Drivers

- Manufactured in the U.S.A. to ensure proper fit in every application, each power driver is precision machined, heat treated and finished to the gold standards Klein Tools puts into every screwdriver blade. Proprietary processes create the longest life power driver bit in the industry. Tight fitting tips reduce wear and deliver the premium performance you expect from a Klein.
- Precision machined for better fit, more torque and less wear
- Custom heat treated for long life

Klein Lasts Longer Before Cam Out



Cat. No.	Overall Length	Bit Type	Package Quantity	Weight
PH115	1" (25.4 mm)	#1 Phillips	5	0.10 oz (2.8 g)
PH1355	3-1/2" (88.9 mm)	#1 Phillips	5	0.50 oz (14.2 g)
PH162	6" (152.4 mm)	#1 Phillips	2	0.9 oz (26 g)
PH2115	1" (25.4 mm)	#2 Phillips	15	0.10 oz (2.8 g)
PH2355	3-1/2" (88.9 mm)	#2 Phillips	5	0.50 oz (14.2 g)
PH262	6" (152.4 mm)	#2 Phillips	2	0.9 oz (26 g)
PH315	1" (25.4 mm)	#3 Phillips	5	0.10 oz (2.8 g)
PH3355	3-1/2" (88.9 mm)	#3 Phillips	5	0.50 oz (14.2 g)
PH362	6" (152.4 mm)	#3 Phillips	2	0.9 oz (26 g)
SL31615	1" (25.4 mm)	3/16" (4.8 mm) Slotted	5	0.10 oz (2.8 g)
SL316355	3-1/2" (88.9 mm)	3/16" (4.8 mm) Slotted	5	0.50 oz (14.2 g)
SL1415	1" (25.4 mm)	1/4" (6.4 mm) Slotted	5	0.10 oz (2.8 g)
SL14355	3-1/2" (88.9 mm)	1/4" (6.4 mm) Slotted	5	0.50 oz (14.2 g)

Power Driver Sets				
Cat. No.	Overall Length	Bit Type	Package Quantity	Weight
32234	3-1/2" (88.9 mm)	#1 and #2 Phillips, #1 and #2 Square, 3/16" Slotted	5	0.10 lb (0.05 kg)
32235	6" (152.4 mm)	Phillips #1 and #3	2	0.10 lb (0.05 kg)

Power Nut Drivers

- Available in several sizes, these hollow shaft magnetic nut drivers are designed for long bolts, studs or threaded rod jobs.
- Rare Earth magnetic head holds nuts and bolts to aid in hard to reach installations.
- The 5" and 10" models feature a wrench assist end, designed for high torque loosening found in many jobs.
- Power Nut Driver Set contains 1/4", 5/16" and 3/8" nut drivers (Cat. No. 32759)



Hollow magnetic* shafts for nut running



PND7165



32759




PND71610

Cat. No.	Overall Length	Shaft Length	Hollow Depth	Nut Driver Sizes	Weight
32759	6-5/16" (160.3 mm)	2" (50.8 mm)	1-7/8" (47.6 mm)	1/4", 5/16", 3/8"	0.10 lb (0.05 kg)
PND7165	6-5/16" (160.3 mm)	5" (127.0 mm)	3-11/16" (93.7 mm)	7/16"	0.16 lb (0.07 kg)
PND125	6-19/64" (159.9 mm)	5" (127.0 mm)	3-23/32" (94.5 mm)	1/2"	0.19 lb (0.09 kg)
PND9165	6+21/64" (160.7 mm)	5" (127.0 mm)	3-5/8" (92.1 mm)	9/16"	0.23 lb (0.10 kg)
PND71610	11-5/16" (287.3 mm)	10" (254.0 mm)	8-13/16" (223.8 mm)	7/16"	0.25 lb (0.11 kg)
PND1210	11-19/64" (286.9 mm)	10" (254.0 mm)	8-23/32" (221.5 mm)	1/2"	0.31 lb (0.14 kg)
PND91610	11-5/16" (287.3 mm)	10" (254.0 mm)	8-5/8" (219.1 mm)	9/16"	0.35 lb (0.16 kg)

NOTE: Read and follow safety instructions in power tool owner's manual.





Power Driver Bits

Magnetic Hex Drivers

- For driving sheet metal screws
- Strong rare earth magnets for maximum holding
- 1/4" (6.4 mm) hex shank with quick release groove




86602

Cat. No.	Description	Overall Length	Weight
86600	1/4" Magnetic Hex Drivers, 3-pack	1-3/4" (44.5 mm)	0.12 lb (0.05 kg)
86601	5/16" Magnetic Hex Drivers, 3-pack	1-3/4" (44.5 mm)	0.14 lb (0.06 kg)
86602	3/8" Magnetic Hex Drivers, 3-pack	1-3/4" (44.5 mm)	0.16 lb (0.07 kg)
8660010	1/4" Magnetic Hex Drivers, 10-pack	1-3/4" (44.5 mm)	0.43 lb (0.20 kg)
8660110	5/16" Magnetic Hex Drivers, 10-pack	1-3/4" (44.5 mm)	0.49 lb (0.22 kg)
8660210	3/8" Magnetic Hex Drivers, 10-pack	1-3/4" (44.5 mm)	0.57 lb (0.26 kg)

Drill/Tap/Deburr Set

- For aluminum, brass, copper, plastic, and up to 10 gauge metal
- 1/4" hex for easier application with quick connect
- Set of six tap sizes plus two extra of the smallest taps
- For use on up to 10 gauge metal
- Made of high speed steel for added durability

IMPACT RATED!



32217

Cat. No.	Tap Sizes	Overall Length	Weight
32217	6-32 (2), 8-32 (2), 10-24, 10-32, 12-24, 1/4-20	4" (101.6 mm)	1.5 lb (0.7 kg)
Cat. No.	Tap Sizes	Weight	
32237	6-32	0.25 lb (0.11 kg)	
32238	8-32	0.25 lb (0.11 kg)	
32239	10-32	0.25 lb (0.11 kg)	
32240	10-24	0.25 lb (0.11 kg)	
32241	12-24	0.25 lb (0.11 kg)	
32242	1/4-20	0.25 lb (0.11 kg)	

NOTE: Read and follow safety instructions in power tool owner's manual.

See page 310 for additional information on warnings.

