

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire. Propriete de c FCI. Droits de reproduction FCI.





All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER
55308-XXX





PLATING OPTION
3= 0.76 µm GOLD
5= 1.27 µm GOLD

HOLD DOWN OPTION
1= OUTSIDE
2= INSIDE

TERMINAL LOADING
1 = FULLY LOADED 6 POS
2 = ONLY POS 2.3.4.5 LOADED
3 = ONLY POS 1.2.5.6 LOADED



RECOMMENDED PIPET
SCALE 2



NOTES:


- 1 - MATERIAL: HOUSING: HIGH TEMP. PLASTIC, COLOR BLACK. TERMINAL: PHOSPHOR BRONZE.
- 2 - PLATING: CONTACT AREA: SEE TABLE. SOLDER TAIL: 90/10 SnPb 2 µm MIN. NO RAW EDGES EXCEPT SOLDER TAIL TIPS.
- 3 - PACKAGING IN TAPE & REEL SEE TA858.
- 4 - DIMENSION MEASURED FROM "B" TO THE TOP OF PRODUCT
- 5 - RECOMMENDED VACCUM PIPET

A FCI www.fciconnect.com			surface - ✓ ISO 1302		tolerance ±0.13 ±2 °		projection 		mm 	
Dr	D LEGRAND	02.05.23	Product family MODULAR JACK			size		Scale		
Eng	F TISSERAND	02.05.23	Spec ref			A3		5:2		
Chr	F TISSERAND	02.05.23	Material SEE NOTES			ECN		F20562		
Appr	F TISSERAND	02.05.23								
title	HORIZONTAL L.P. SMT					dwg no		55308		Rev.
	6 POSITIONS									
catalog no					SEE TABLE		CUSTOMER COPY		sheet 1 of 2	


ltr	ecn no	dr	date
D	F20300	DLE	02.04.23
E	F20520	DLE	02.09.06
F	F20562	BLE	02.10.16
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

MAXIMUM COPLANARITY 0.1 mm
MEASURED BY MEANS OF
SMARTSCOPE TYPE EQUIPMENT
AT DEFINED POINTS

MEASUREMENT POINTS
ON HOLD DOWN (2x)



MEASUREMENT POINTS
ON SOLDER TAILS (6x)






Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire. Propriete de c FCI. Droits de reproduction FCI.

A
FCI

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.


D

RECOMMENDED PCB FOOT PRINT
FOR 6 POSITIONS OUTSIDE



RECOMMENDED PANEL CUTOUT

RECOMMENDED PCB FOOT PRINT
FOR 6 POSITIONS INSIDE



A FCI www.fciconnect.com			surface - ✓ ISO 1302		tolerance ±0.13 ±2°		projection 		mm ← →	
Dr	D LEGRAND	02.05.23	Product family MODULAR JACK			size		Scale		
Eng	F TISSERAND	02.05.23	Spec ref			A3		5:1		
Chr	F TISSERAND	02.05.23	Material			SEE NOTES		ECN F20562		
Appr	F TISSERAND	02.05.23								
title HORIZONTAL L.P. SMT 6 POSITIONS					dwg no 55308					Rev. F
catalog no					SEE TABLE		CUSTOMER COPY			sheet 2 of 2