




FEATURES:

- Shielded cable to reduce noise.
- WE-310 and dual Bantam Plugs are molded to the cable for optimum durability

MATERIALS:

Plugs – Nickel plated brass

Cable – 2 Conductor shielded twisted pair, PVC jacket and insulation

RATINGS:

Operating Temperature: -20°C to +80°C

Operating Voltage: 300 VRMS Max.

Current: 3.36 Amperes @ 25°C Max.

ORDERING INFORMATION: Model 6328-96

Standard Length 96 Inches (2134 mm)

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).
All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies. Made in USA