



155 Series Twist-Lock In-Line Holders for 3AG/AB Fuses



Dimensions



Product Characteristics

Compatible Fuses	For low voltage 3AG/AB or SFE Fuse Applications
Electrical	Intended for use at 32 volts or less with fuses rated up to 20 amperes when the proper spring is installed for fuse size.
Molded Parts	Black Thermoplastic (UL94 V-2). Body halves have a .14" diameter hole for insulated wire.
Ambient Temperature	-40°C to +75°C.
Contact Rivet	Brass. Nickel plating. Designed to accommodate #14 AWG stranded wire.
Assembled	Supplied with 19" loop of #14 AWG red vinyl insulated wire, SFE fuse (listed) with a spring in different lengths depending of the fuse size.
Unassembled	For assembly to #14 AWG wire.
Options	150 215 is similar to 155 120A except no fuse is supplied. It is intended for use with 3AG fuses rated up to 20 amperes.
In-Line Fuseholder	Supplied with a spring in different lengths depending of the fuse size.

* Please refer to Fuseology section for information on proper fuseholder re-rating.

** Fuseholders with specific wire sizes and lengths are available on special order.

Additional Information



Datasheet



Resources




Samples

Ordering Information


Unassembled			Assembled			Packaging
Ordering Number	Catalog Number	For Fuse Size	Ordering Number	Catalog Number	Fuse Installed	
-	155 100	All below	01550100Z*	-	-	Bulk Pack (100 Pcs)
01550104ZXU	155 104U	¼" × 5/8"	01550104ZXA	155 104A	SFE 4	Bulk Pack (100 Pcs - Assembled) (100 Pcs- Unassembled)
01550106ZXU	155 106U	¼" × ¾"	01550106ZXA	155 106A	SFE 6	Bulk Pack (100 Pcs - Assembled) (100 Pcs- Unassembled)
01550109ZXU	155 109U	¼" × 7/8"	01550109ZXA	155 109A	SFE 9	Bulk Pack (100 Pcs - Assembled) (100 Pcs- Unassembled)
01550114ZXU	155 114U	¼" × 1 1/16"	01550114ZXA	155 114A	SFE 14	Bulk Pack (100 Pcs - Assembled) (100 Pcs- Unassembled)
01550120ZXU	155 120U	¼" × 1 ¼"	01550120ZXA	155 120A	SFE 20	Bulk Pack (100 Pcs - Assembled) (100 Pcs- Unassembled)
-	-	¼" × 1 1/16" ¼" × 1 ¼"	01500215Z	-	-	Bulk Pack (100 Pcs)

* Supplied with 8" loop of #14 AWG red vinyl insulated wire and two springs in different lengths to accommodate SFE sized fuses. (Fuse not included)

155 Series Heavy-Duty Bayonet Knob In-Line Holders for 3AG/AB Fuses



Dimensions



Product Characteristics

Compatible Fuses	For Low voltage 3AG/AB or SFE Fuse Applications
Electrical	Intended for use at 32 volts or less with fuses rated up to 20 amperes when the proper spring is installed for full size.
Molded Parts	Body and knob are Black Thermoset (UL94 V-0). Both body and knob have a .20" diameter hole for insulated wire.
Knob	Bayonet-lock type metal insert.
Ambient Temperature	-40°C to +125°C.
Contact Rivet	Brass. Tin plated. Designed to accommodate #14 AWG stranded wire.
Assembled	Supplied with 19" loop of #14 AWG red vinyl insulated wire, SFE fuse (listed) with a spring in different lengths depending of the fuse size.
Unassembled	For assembly to #14 AWG wire.
Options	150 079 is similar to 155 020A except no fuse is supplied. It is intended for use with 3AG fuses rated up to 20 amperes.
In-Line Fuseholder	Supplied with a spring in different lengths depending of the fuse size.

* Please refer to Fuseology section for information on proper fuseholder re-rating.

** Fuseholders with specific wire sizes and lengths are available on special order.

Additional Information



Datasheet



Resources



Samples

Ordering Information

Unassembled			Assembled			Packaging
Ordering Number	Catalog Number	For Fuse Size	Ordering Number	Catalog Number	Fuse Installed	
01550004ZXU	155 004U	¼" × 5/8"	01550004ZXA	155 004A	SFE 4	Bulk Pack (100 Pcs)
01550006ZXU	155 006U	¼" × ¾"	01550006ZXA	155 006A	SFE 6	Bulk Pack (100 Pcs)
01550009ZXU	155 009U	¼" × 7/8"	01550009ZXA	155 009A	SFE 9	Bulk Pack (100 Pcs)
01550014ZXU	155 014U	¼" × 1 1/16"	01550014ZXA	155 014A	SFE 14	Bulk Pack (100 Pcs)
01550020ZXU	155 020U	¼" × 1 ¼"	01550020ZXA	155 020A	SFE 20	Bulk Pack (100 Pcs)
-	-	¼" × 1 ¼"	01500079Z	-	-	Bulk Pack (100 Pcs)
-	-	¼" × 1 ¼"	01500145HXB*	-	-	Bulk Pack (100 Pcs)
-	-	¼" × 7/8"	01500145Z**	-	-	Bulk Pack (100 Pcs)
		¼" × 1 1/16"				
		¼" × 1 ¼"				

* Supplied with 15" loop of #14 AWG red vinyl insulated wire

** and three springs in different lengths to accommodate SFE sized fuses.


150 Series In-Line Holders for 2AG or 5×20mm Fuses



Agency Approval

Agency	Agency File Number
	E14721

Dimensions [mm]



Product Characteristics

Compatible Fuses	2AG or 5×20mm
Electrical	This fuseholder, part number 150274, is intended for use with 2AG and 5 × 20mm fuses. Maximum current ratings are 5 amperes at 350V for the 2AG size fuses and 10 amperes at 350V for the 5 × 20mm size fuses.**
Body	Black Nylon, UL94 V-0
Terminals	Brass
Wire	16 Awg size; Nominal o.d. 0.104"; color Red
Lead Pull Test	Will withstand 10 lb. pull.
Ambient Temperature	-40°C to +80°C.

NOTES:

* Ensure that proper fuse re-rating is factored in fuseholder selection.

** If use above 32V, power must be turn off when changing the fuse.

Ordering Information

Ordering Number	Packaging
01500274Z	Bulk Pack (1000 Pcs)
01500274LXN	Bulk Pack (100 Pcs)
*01500274ZXU	Bulk Pack (5000 Pcs)

NOTES:

* For unassembled Fuseholder, UL certification does not apply.

Additional Information



Datasheet



Resources



Samples