

## Honeywell Sensing and Control

Search



## narrow your search

## Products

- Controls Monitoring and Lighting (286)
- Machine Safety (1727)
- Sensors (6165)
- Switches (9781)
- Wireless (45)

## Technology

- Control and Instrumentation (890)
- Electromechanical (9307)
- Magnetic (541)
- Platinum thin film (56)
- Thick Film (1372)
- More...

## new products

## New Wireless Products

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



Wireless Web Site  
WGLA and WPMM  
XYR6000™

[find out more](#)

## white papers

- Wireless Switches Offer Unlimited Benefit
- Basic Switches Are Not Created Equal
- Applying Precision Switches
- Sensors for Medical Devices
- New Ways to Measure Torque
- Choosing Safety Switches
- Specifying Hour Meters

## Need help?

[Click here to contact us](#)

## GSXC42C

( Home : Products : Machine Safety » MICRO SWITCH™ Safety Switches » Electromechanical » GSX )



Actual product appearance may vary.

GSX Series, Explosion-Proof Safety Switch, 20 mm housing, 2NC/1NO top roller plunger

[Sales & Service](#)[Distributor Inventory](#)[Overview](#) [Specs](#) [Documentation](#) [Application Notes](#)

## Product Specifications

Product Type	Safety Limit Switch
Actuator	Top Roller Plunger
Switch Type	2NC/1NO Positive Break, Slow Acting, BBM
Contact Material	Silver
Termination Type	20 mm Housing
Ampere Rating	10 A (Thermal)
Housing Material	Zinc die-cast
Housing Type	20 mm Housing
Series Name	GSX
Sealing	IP67; NEMA 1, 3, 4, 12, 13
Agency Approvals and Standards	cULus, ATEX, IEC Ex
Expected Mechanical Life	1 Million
Operating Temperature	-40 °C to 70 °C [-40 °F to 158 °F]
Availability	Global
UNSPSC Code	302119
UNSPSC Commodity	302119 Switches and Controls and Relays
Comment	Div. 1, Class I, Groups B, C, & D; Div. 1, Class II, Groups, E, F, & G; II 2 G, Ex d IIC T6; II 2 D, Ex d tD A21 T85C

## contacts

Customer Service  
Technical Support  
Global Sales & Service  
View Site Demo  
Site Comments?

## meet dr. larry

VIDEO - Dr. Larry Goldstein explains our newest and best technologies.



Meet Dr. Larry

## my links

Login to iCOM  
Login to Rep/AD Portal  
Login to Digital University

## News Center

Honeywell Introduces  
TruStability® NSC Series,  
Uncompensated / Unamplified  
Board Mount Pressure Sensors

HONEYWELL EXPANDS ITS  
LIMITLESS™ PLATFORM WITH  
THE LAUNCH OF ITS  
GLOBALLY AVAILABLE  
INDUSTRIAL WIRELESS  
RECEIVER

HONEYWELL EXTENDS ITS  
TRUSTABILITY® PRESSURE  
SENSOR PRODUCT LINE WITH  
A SINGLE SIDE LIQUID MEDIA  
OPTION

HONEYWELL ADDS NEW 100°  
AND 180° ARC  
CONFIGURATIONS TO ITS  
SMART POSITION SENSOR  
PORTFOLIO

HONEYWELL INTRODUCES  
ITS HAWK™ RESOLVERS 1-  
INCH SERIES, FULLY HOUSED  
CONFIGURATION

HONEYWELL INTRODUCES  
MICROPOWER OMNIPOLAR  
DIGITAL HALL-EFFECT  
SENSOR ICS WITH LOW  
SUPPLY VOLTAGE AND ULTRA  
LOW TYPICAL CURRENT

**MICRO SWITCH**  
Anniversary site