


Item no.: 769-612  
Product description: Plug WITH CAGE CLAMP®CONNECTION FOR FREE CONNECTION PIN SPACING 5 MM / 0.197 IN 12 POLE



Produkt kann von Bild abweichen / product may differ

Packing unit 25 pieces

RoHS compliant

|                                  |                          |
|----------------------------------|--------------------------|
| Product group                    | 18 (X-COM-SYSTEM)        |
| Pin spacing from                 | 5 mm                     |
| Pin spacing from                 | 0.197 in                 |
| pole count                       | 12                       |
| Cross section [mm <sup>2</sup> ] | 0.08 - 4 mm <sup>2</sup> |
| Cross section [AWG]              | 28 - 12 AWG              |
| Measured voltage EN              | 500 V                    |
| Measured shock voltage           | 6 kV                     |
| Pollution degree                 | 3                        |
| Current intensity EN             | 32 A                     |
| Weight                           | 35.169 g                 |
| Color                            | gray                     |
| Wiring type                      | Front-entry              |
| No. of connection Points         | 12                       |
| No. of potentials                | 12                       |
| Height                           | 18.3 mm                  |
| Height                           | 0.72 in                  |
| Width                            | 63.6 mm                  |
| Width                            | 2.504 in                 |

|                   |          |
|-------------------|----------|
| Depth             | 40.2 mm  |
| Depth             | 1.583 in |
| Strip length from | 8 mm     |
| Strip length to   | 9 mm     |
| Strip length      | 0.33 in  |



| Item no. | Admission office | Approval no.      | Voltage [V] | Current [A] | Cross section [ mm² ] |
|----------|------------------|-------------------|-------------|-------------|-----------------------|
| 769-612  | ABS              | 05-HG476175/3-PDA | 500         | 32          | 4                     |
| 769-612  | CSA              | 154112-1101144    | 300         | 20          | 28-12                 |
| 769-612  | KEMA             | 2077750.01        | 500         | 32          | 4                     |
| 769-612  | UR               | E45171            | 600         | 20          | 16-12                 |
| 769-612  | UR               | E45172            | 300         | 20          | 28-12                 |

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected