





Dimensions in mm



Test Specification according to Standard UL 248-1,14

Electrical Characteristic

Rated Current	1.0 In	1.35 In	2 In
In	Min.	Max.	Max.
100mA-30A	4 h	3600 S	120 S

Rated Current	Breaking capacity	Rated Voltage	MFG52/-P-PA-PR		
100mA	@125V/AC 10KA @250V/AC 35A	125V/250V			
125mA		125V/250V			
160mA		125V/250V			
200mA		125V/250V			
250mA		125V/250V			
300mA		125V/250V			
315mA		125V/250V			
400mA		125V/250V			
500mA		125V/250V			
600mA		125V/250V			
630mA		125V/250V			
700mA		125V/250V			
800mA		125V/250V			
1A		125V/250V			
1.25A	@125V/AC 10KA @250V/AC 100A	125V/250V			
1.5A		125V/250V			
1.6A		125V/250V			
2A		125V/250V			
2.5A		125V/250V			
3A		125V/250V			
3.15A		125V/250V			
3.5A		125V/250V			
4A		125V/250V			
5A		125V/250V			
6A	@125V/AC 10KA @250V/AC 200A	125V/250V			
6.3A		125V/250V			
7A		125V/250V			
8A		125V/250V			
* 10A		125V/250V			
12A	@32V/AC 1000A	32V			
13A		32V			
15A		32V			
16A		32V			
20A		32V			
25A		32V			
30A		32V			

GOLDSUN ELECTRONICS CO., LTD.

JAMECO NO. 103908		GOLDSUN NO. MFG52A1.000N	
Description FUSE,FAST ACTING, 250V 1A 5mmx20mm			Rev. 1
UNIT: mm	SCALE:	SHEET 1 OF 1	CAS No: ERN No: