



SPECIFICATION

1. Rated Voltage 9 VDC
2. Operating Voltage 7~12 VDC
3. Max. Rated Current 30mA/9VDC
4. Min. Sound Pressure Level 85dB/10cm
5. Resonant Frequency 2300±300Hz
6. Response Time 50ms
6. Case Material PBT
7. Operating Temperature -20~+70℃
8. Store Temperature -30~+80℃
9. Weight 2g

				KEPO KEPO ELECTRONIC CO., LTD. http://www.kepo.com.tw			
				Magnetic Buzzer			
				KPX-1209A			
No.	DESCRIPTION	APPROVED	DATE				
TOLERANCES UNLESS NOTED OTHERWISE X .X XX . XXX + 90° FORMED -2° FIRST ANGLE PROJECTION		APPROVALS		DATE			
		DRAWN			UNIT	DWG NO.	
		CHECKED			mm	KP3.840.690	
		APPROVED		05.02.26	SCALE	NOT TO SCALE	VER 1.1