




Home	Products	Enquiry Form	Contact Us	The Company	Quality
----------------------	--------------------------	------------------------------	----------------------------	-----------------------------	-------------------------

Standard Brass Ended

Our standard range of BS89/IEC51 class 1 or class 0.5 shunts can be current rated from 5A to 10000A with 50mV to 300mV output.


Technical Specification

Operating Temperature:	-20°C TO +40°C
Permissible Overload:	
Continuous	1.2 x rated current
5 seconds	5 x rated current up to 2kA
10 seconds	2 x rated current for 2kA-5kA
Shunt Leads:	Millivolt leads can be supplied upon request (standard length = 760mm)
Order example:	A brass ended shunt with 1000A rated current and 100mV output, class 1 is: SHB1000A100-CLASS1




Dimensions (mm)


Current (A)	A									B	C	D	E	F
	Type	50mV	60mV	75mV	100mV	150mV	200mV	250mV	300mV					
5-35	1	95	95	95	114	114	172	172	167	22	10	11	-	7
40-200	1	95	95	95	114	114	172	172	267	32	12	13	-	10
225-440	1	95	95	95	114	121	172	172	267	32	20	25	-	10
450-1700	2	95	95	95	114	121	172	172	267	67	25	25	41	10
1800-3400	3	95	95	95	114	121	172	-	-	111	38	81	57	10
3500-5000	3	95	95	95	114	121	-	-	-	140	38	114	90	12
5500-7000	4	83	83	96	-	-	-	-	-	230	38	114	90	12
7500-10000	5	83	83	96	-	-	-	-	-	320	38	114	90	12




Type 1




Type 2




Type 3



Type 4




Type 5



[Sales Enquiry](#)



[Home](#)



[Main Shunt Page](#)

Contact sales: sales@hobut.co.uk