

Lamp Cord Type SPT

60°C 300 Volts UL/CSA



TYPE SPT-1

CATALOG NUMBER	NO. OF COND.	AWG SIZE	COND. STRAND	NOM. INSULATION THICKNESS		NOMINAL O.D.		CURRENT AMPS ⁽¹⁾	APPROX. NET WEIGHT LBS/M ^(S)	JACKET COLOR CHART
				INCHES	mm	INCHES	mm			
02301	2	18	41/34	0.030	0.76	0.107 X 0.210	2.72 X 5.330	10	22	A
02304	2	18	41/34	0.030	0.76	0.107 X 0.210	2.72 X 5.330	10	22	D
02305	2	18	41/34	0.030	0.76	0.107 X 0.210	2.72 X 5.330	10	22	C
02306	2	18	41/34	0.030	0.76	0.107 X 0.210	2.72 X 5.330	10	22	B

TYPE SPT-2

CATALOG NUMBER	NO. OF COND.	AWG SIZE	COND. STRAND	NOM. INSULATION THICKNESS		NOMINAL O.D.		CURRENT AMPS ⁽¹⁾	APPROX. NET WEIGHT LBS/M ^(S)	JACKET COLOR CHART
				INCHES	mm	INCHES	mm			
02303	2	16	65/34	0.045	1.14	0.155 X 0.295	3.94 X 7.490	13	37	A

⁽¹⁾ Ampacities based on NEC table 400.5(A).

^(S) Actual shipping weight may vary.

Product Construction:

Conductor:

- 18 and 16 AWG fully annealed bare or tinned copper per ASTM B-174

Insulation:

- Premium-grade, color-coded PVC
- Temperature range: -20°C to +60°C
- Color code: See chart below

Jacket Marking:

- (SIZE) SPT-1 (or STP-2) 60°C E# (UL) --- CSA LL# FT-2 300V

Applications:

- Small appliances
- Lamps
- Radios
- Jukeboxes

Industry Approvals:

- UL Listed
- CSA Certified
- RoHS Compliant

Packaging:

- 250' (76.2 m) spools
- Other put-ups available on special order

JACKET COLOR CODE CHART

A	Black or White or Brown
B	Clear Silver (tinned copper)
C	Clear Gold
D	Clear