



FEATURES:

- Retractable Sheath Banana Plug provided for use with older test equipment.

MATERIALS:

Conn: 1st End-Retractable sheath banana plug:

Spring: Beryllium Copper per QQ-C-533,

Cond. H.T.Nickel plated per QQ-N-290, Class 2, 200/300 microinches.

Plug Body: Brass Rod, per ASTM B16-85,

Temper HO2. Nickel plated per QQ-N-290,

Class 2, 200/300 microinches.

Tip: Nylon. Color matches color of wire.

Compression Spring: Stainless Steel 302.

Insulation: Nylon molded to plug body and wire.

Color matches color of wire.

Wire: 20 AWG stranding 41 x 36 T.C., PVC insulated, 2.21 (.087) O.D. Color: One Black and one Red.

Molded Breakout: PVC molded to breakout leads

and cable. Color: Black

Cable: Shielded coaxial RG58C/U, 4.95 (.195) O.D.

Color: Black. Marking: "POMONA 5343-C-XX". Conn: 2nd End-BNC Male Connector Body and fittings: Tarnish resistant. Center Contact: Gold plated per requirements of MIL-C-39012.

Strain Relief Boot: PVC molded to BNC plug and cable.

Color: Black

RATINGS:

Environmental: Operating Temperature: +50°C.

(+122°F.) Max.

Operating Voltage: Shield-Earth: 30VAC/60VDC,

Inner Conductor-Shield: 500 VRMS Max.

Nominal Impedance: 50 Ohms

ORDERING INFORMATION:

Model 5343-C-XX
 XX=cable length, standard length: 12" (305), 24" (610), 36" (914), 48" (1219), 60" (1524) Ordering Example: 5343-C-60 (1524)

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[5343-C-36](#) [5343-C-60](#)