






8 7 6 5 4 3 2 1
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	04/15/04	MCCORMICK



SPECIFICATIONS:
- UL94V-0 COMPLIANT (CONTACT HOUSING)

MATERIALS
- TOP & BOTTOM SHELL: STEEL – TIN/LEAD FINISH
- CONTACTS: COPPER ALLOY
- CONTACT PLATING: SELECTIVE GOLD PLATING

ELECTRICAL RATING:
- VOLTAGE: 30 VAC (R.M.S.)

ENVIRONMENTAL
- OPERATING TEMPERATURE RANGE: -55 °C TO +85 °C,
UNLESS LIMITED BY CABLE OR OVERRMOLD (-40 °C TO +60 °C
STORAGE; +0 °C TO +40 °C OPERATING).

APPLICATION NOTES
- APPLICABLE CABLE DIAMETER: ϕ .134 TO ϕ .209

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:
X \pm .1
XX \pm .05
XXX \pm .005
CABLE LENGTH TOLERANCE
<300' \pm 5% >300' \pm 2%

APPROVALS	DATE
DRAWN BY C.MCCORMICK	04/08/2004
CHECKED BY D.PARHAM	04/13/2004
APPROVED BY R.CARRICK	04/13/2004

CONFIGURATION DETAILS OF
UNDIMENSIONED FEATURES
MAY VARY

SIZE	FSCM NO.	DWG. NO.	REV
A	43321	CNUSB-B-OD1	A
SCALE: 2:1	CAD FILE: CNUSB-B-OD1.SLDDRW	SHEET 1 OF 1	



45 BEECHWOOD DRIVE
NORTH ANDOVER, MA
01845

PRODUCT DESCRIPTION

USB PLUG - SERIES B w/o HOOD

DRAWING TITLE

OUTLINE DRAWING