

HG 2300 EM

Powerful hot air gun for use with "Professional" hot air accessory attachments.

Features

- Fully electronic temperature and airflow control
- High-performance, long-life brushless motor
- Barrel shape for optimum stationary use

Settings

- Continuously adjustable air flow and temperature

Maintenance

- Easy-to-change heating element
- Easy-to change mains power cord



Semplice
sostituzione della
resistenza



A regolazione
continua



Cavo di
allacciamento alla
rete facilmente
sostituibile



HG 2300 EM
Adatto per ugelli
"Professional"
avvitabili

HG 2300 EM

Prod. No.

Length / dia. (at knock guard)

Voltage

Output

Temperature

Temperature control

Airflow rate

350413

375 mm / 100 mm

230 V / 50 Hz

(other voltages also available)

2300 W

25 - 600° C

continuous

600 l / min. max.

Air pressure	3000 Pa
Air flow regulation	continuously variable
delivery nozzle	suitable for screw-on "Professional" attachments (30 mm dia.)
Motor life	approx. 5000 hrs.
Heater life	approx. 800 hrs.
Mains power cord	H07 RN-F 2 x 1 length 2.5 m
Weight	850 g
	Subject to technical modifications