

 [Live Product Chat](#)



✓ Active

 [Add to Part List](#)

[View 3D PDF](#)

 Always EU RoHS/ELV Compliant (Statement of Compliance)

- Barrier Strip
- Barrier Style = Double Row, Dual Barrier
- Block Style = Flat
- 9.53 mm Centerline
- Vertical Mount Angle

[View all Features](#) | [Find Similar Products](#)

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

- [9.50MM \(.374\) DBL ROW BARRIER STRIP W/O WASHER \(PDF, English\)](#)

- [BUCHANAN TERMINAL BLOCKS CATALOG - BARRIER STRIPS](#)
(PDF, English)

- None Available

- None Available

- None Available

- 2D Drawing (DXF, Version G12)
- 3D Model (IGES, Version G12)
- 3D Model (STEP, Version G12)

List all Documents

- Product Line Information

- Tooling

- [Product Type](#) = Barrier Strip
- [Mount Angle](#) = Vertical
- Number of Positions = 4
- Screw Material = Steel
- Screw Size = 6-32 x 1/4
- Mounting Ears = With
- Comment = Other options available upon request, consult our Product Information Center.

- Screw Plating = Nickel
- Mounting Style = Open End Position

- [Top Hardware](#) = Wire Clamp Combo Head
- Number of Levels = Single
- End Barriers = Without
- Current Rating (Amps.) = 20
- Mounting Insert = Without

- Barrier Style = Double Row, Dual Barrier
- Block Style = Flat
- Centerline (in [mm]) = 0.375 [9.53]
- Number of Rows = Dual
- Length (mm [in]) = 55.20 [2.170]
- Block Material = Thermoplastic
- Block Color = Black
- Wire Range (mm [AWG]) = 0.30-3.00² [22-12]

- Mounting Options = End Mounting Ears

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

- Brand = Buchanan