





JKL PART NUMBER	Color	Volts V	Amps mA	Luminous Intensity (mcd)	Peak Wave Length (nm) or Color Temperature (°k)	Viewing Angle (deg).
Z-T55-NW	Neutral White	36V DC	20 MAX.	1200 TYP.	4400°k	60
Z-T55-R	Red	36V DC	20 MAX.	1000 TYP..	622nm	30
Z-T55-G	Green	36V DC	20 MAX.	4250 TYP.	468nm	20

NOTE: LED LAMP REPLACEMENT FOR SM3620L

			METRIC  THIRD ANGLE PROJECTION		DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- REF. 2 PL +/- REF. ANGLE +/- 0		JKL COMPONENTS CORPORATION TITLE LILIPUT T5.5 TELEPHONE SLIDE BASE LED							
C	CHANGE MOL TOLERANCE FROM ±1 TO ±2	3/29/11	DRAWN BY	APP'VD BY	DATE	SIZE	FSCM NO.	DRAWING NO.	Z-T55					
B	ADD NOTE FOR + SIDE MARK	3/29/11	L. WENGSTROM	L.R.	8/19/13	A	55335							
A	ADD SYMBOLS ON CHART	2/22/11												
	RELEASE & CANCEL PL-1010-01	1/13/11												
REV. NO.	DESCRIPTION/ECO NUMBER	APP'VD DATE	- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED			SCALE	NONE	RELEASED DATE	1/13/11	REVISION DATE	8/19/13	REV. NO.	C	SHEET 1 OF 1