


NOTES:

- ① MAT'L: COPPER (STOCK TKN. .79)
PLATING: ELECTRO TIN (.0003 MIN)
TIN-PLATED BRASS FUNNEL FERRULE
- ②
- ③ NYLON INSULATION (COLOR CODED BU



STUD SIZES: (+.005)

- | | | |
|----|---|------|
| 02 | = | .094 |
| 04 | = | .119 |
| 06 | = | .146 |
| 08 | = | .173 |
| 10 | = | .198 |
| 14 | = | .265 |
| 56 | = | .328 |
| 38 | = | .390 |

"UL" LISTING #E32244
"CSA" LISTING #18689

WIRE SIZE: 16 - 14 AWG 2.5 MM²

ALL DIMENSIONS = $\frac{\text{INCHES}}{\text{MM}}$

(MWID)=DENOTES MAXIMUM WIRE INSULATION DIAMETER

[illegible]