

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300500105](#)
Status: **Active**
Overview: [Brad Industrial Ethernet Solutions](#)
Description: Brad RJ-Lnxx RJ-45 Single-Ended Cordset, 8 Poles, Male to Pigtail, Straight, Shielded Cable, 1.0m (3.28') Length , 26 AWG

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Cordsets
Series	130050
Connector End A	RJ-45 (standard)
Connector End B	Pigtail
IP Rating	IP67
Material - Contact	Copper Alloy
Overview	Brad Industrial Ethernet Solutions
Performance Category	5e
Product Name	Brad, RJ-Lnxx
Protocol	N/A
Region	America, Asia, Europe
Type	Single Ended
UPC	78678850644

Physical

Cable Diameter	7.37mm (.290")
Cable Length	1.0m (3.28')
Color - Cable Jacket	Black
Coupling Style	N/A
Gender	Male-Pigtail
Keyway	None
LED Indicator	No
Material - Cable Jacket	PUR
Material - Connector Body	PVC
Material - Coupling Nut	N/A
Material - Plating Mating	N/A
Orientation	Straight to Pigtail
Poles	8
Temperature Range - Operating	-20°C to +80°C
Wire Size AWG	26
Wire/Cable Type	Shielded-Twisted Pair

Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	30V

Material Info

Engineering Number	ENP1305M010
--------------------	-------------

Reference - Drawing Numbers

Sales Drawing	SD-130050-013
---------------	---------------



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130050](#) Series