

Sura Magnets AB

Hamragatan 2

S-614 31 Söderköping

Sverige/Sweden

Telefon +46 (0) 121 353 10

Fax +46 (0) 121 353 15

E-mail info@suramagnets.seInternet www.suramagnets.se


Partnumber: NA35-2-014-4

Material : Neodym 35

Dimensions

D	H
14 mm	8 mm

Magnetisation: Axially magnetized



Grade	Remanence (T)		Coercivity BHc (kA/m)		Coercivity Ihc (kA/m)	Energi product BH max (kJ/m3)		Max Work temp
	Min	Typ	Min	Typ		Min	Typ	
N35	1,17	1,21	860	915,4	>=955	262,7	278,6	<=80°