

Conductor - VS-DSIV-M12FSD-RJ45-933-B/ 0,5 - 1657180

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Assembled PROFINET cable, type B, CAT5e, shielded, star quad, AWG 22 stranded (7-wire), RAL 6018 (yellow-green), panel feed-through, M12, 4 pos., D-coded on RJ45 connector, length: 0.5 m



Key commercial data

Packing unit	1 pc
Weight per Piece (excluding packing)	77.0 GRM
Custom tariff number	85444210
Country of origin	Poland

Technical data

Product type	Data cable preassembled
Cable length	0.5 m
Number of positions	4

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27060306
eCl@ss 5.0	27260701
eCl@ss 5.1	27060307
eCl@ss 6.0	27061801
eCl@ss 7.0	27061801

ETIM

ETIM 3.0	EC000830
ETIM 4.0	EC000830

Conductor - VS-DSIV-M12FSD-RJ45-933-B/ 0,5 - 1657180

Classifications

ETIM


ETIM 5.0	EC000830
----------	----------

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501


Drawings

Dimensioned drawing




Mounting panel with feed-through hole

Dimensioned drawing




Mounting panel with thread

Schematic diagram



Pin assignment M12 socket, 4-pos., D-coded, female side


Cable cross section




PROFINET PVC stranded CAT5e [93B]

Conductor - VS-DSIV-M12FSD-RJ45-933-B/ 0,5 - 1657180

Dimensioned drawing




Circuit diagram



M12 flush-type connector

Schematic diagram



Connector pin assignment plug RJ45