

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1212020006](#)
Status: **Active**
Overview: mPm DIN Valve Connectors
Description: mPm DIN Valve Connector, Form B-11mm, External Thread, 2 Pole Plus Ground Terminal, 250V AC/DC, Transparent, Nitrile Gasket

Documents:

[Drawing \(PDF\)](#) [Packaging Specification PK-121202-C22-001 \(PDF\)](#)
[Product Specification PS-121201-001-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification STR-1251-001 \(PDF\)](#)

General

Product Family Field Attachable / Accessories
Series [121202](#)
Form B - 11mm
IP Rating IP65, IP67
Material - Contact Brass
Overview [mPm DIN Valve Connectors](#)
Product Name mPm
Type Field Attachable Connector
UPC 883906916237

Physical

Cable Diameter N/A
Coupling Type External Thread
Diagnostics / LEDs No
Diagnostics Port No
Gender N/A
Keyway None
Material - Connector Body Polyamide
Material - Coupling Nut N/A
Material - Plating Mating Silver
Net Weight 10.000/g
Orientation 90° Angle
Pitch - Mating Interface 11.00mm
Poles 2
Temperature Range - Operating -40°C to +90°C
Wire Size AWG N/A

Electrical

Current - Maximum per Contact 16.0A
Voltage - Maximum 250V AC/DC

Material Info

Engineering Number C22200T0R

Reference - Drawing Numbers

Packaging Specification PK-121202-C22-001
Product Specification PS-121201-001-001, STR-1251-001
Sales Drawing SD-121202-001



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[121202](#) Series