


STANDARD ZIF CABLE - SAME SIDE



CABLE WIDTH = (# OF CONDUCTORS + 1)(PITCH)
 SPAN = (# OF CONDUCTORS - 1)(PITCH)
 MATING THICKNESS = .012" (.305mm)
 INSULATION = .002" Thick Polyester with Flame Retardent Adhesive
 COPPER = TIN PLATED
 TEMPERATURE RATING = -55°C TO 105°C
 DIELECTRIC STRENGTH = 2500 VOLTS/MIL
 UL FLAME RATING = VW-1
 INSULATION RESISTANCE = 10^3 MEGOHM MIN

PITCH	MARGIN	EXPOSED COPPER	STIFFENER LENGTH	COPPER THICKNESS	COPPER WIDTH	UL #	CURRENT RATING
.0197" (.500mm)	.014" (.356mm)	.140" (3.556mm)	.237" (6mm)	.003" (.076mm)	.011" (.280mm)	20890	.50 AMPS
.0246" (.625mm)	.017" (.422mm)	.140" (3.556mm)	.237" (6mm)	.003" (.076mm)	.016" (.406mm)	20890	.50 AMPS
.025" (.635mm)	.020" (.495mm)	.140" (3.556mm)	.237" (6mm)	.003" (.076mm)	.011" (.280mm)	20890	.50 AMPS
.0315" (.800mm)	.023" (.572mm)	.140" (3.556mm)	.237" (6mm)	.003" (.076mm)	.019" (.483mm)	20566	.80 AMPS
.0394" (1.00mm)	.026" (.660mm)	.140" (3.556mm)	.237" (6mm)	.003" (.076mm)	.026" (.660mm)	20566	1.5 AMPS
.0492" (1.25mm)	.033" (.845mm)	.170" (4.318mm)	.294" (7.5mm)	.003" (.076mm)	.0315" (.800mm)	20566 & 2643	2.0 AMPS
.050" (1.27mm)	.034" (.864mm)	.170" (4.318mm)	.294" (7.5mm)	.003" (.076mm)	.0315" (.800mm)	20566 & 2643	2.0 AMPS
.100" (2.54mm)	.075" (1.905mm)	.240" (6.096mm)	.394" (10mm)	.003" (.076mm)	.050" (1.27mm)	2643	3.0 AMPS
.100" (2.54mm)	.069" (1.753mm)	.240" (6.096mm)	.394" (10mm)	.003" (.076mm)	.062" (1.575mm)	2643	3.0 AMPS

* STANDARDS CAN BE CUSTOM ADJUSTED PER REQUEST

UL # CLARIFICATION CHART

20890 = .008" MIN SPACING BETWEEN CONDUCTORS,
 VOLTAGE RATING = 90VOLTS
 20566 = .010" MIN SPACING BETWEEN CONDUCTORS
 VOLTAGE RATING = 90 VOLTS
 2643 = .016" MIN SPACING BETWEEN CONDUCTORS
 VOLTAGE RATING = 300 VOLTS

PROPRIETARY INFORMATION NOTICE

This document and the designs, specifications, and engineering information disclosed herein are the property of Parlex Corp., and are not to be disseminated or reproduced without expressed written consent. This document is loaned in confidence and then only for consideration of the matter disclosed hereon. In accepting loan of this document, the recipient agrees to keep it and the matter disclosed hereon in confidence and not to use or permit their use in any way detrimental to Parlex Corp.

DIMENSION		STANDARD TOLERANCES
CABLE LENGTH	0-3"	±.050" (1.27mm)
	3"-6"	±.060" (1.524mm)
	6"-12"	±.070" (1.778mm)
	12"-18"	±.110" (2.794mm)
	18"-24"	±.120" (3.048mm)
	24"-36"	±.150" (3.810mm)
	OVER 36"	±1% OF LENGTH
EXPOSED COND. LENGTH		±.030" (.76MM)
STIFFENER LENGTH		±.050" (1.27MM)
PITCH		±.005" (.127MM)
SPAN		±.005" (.127MM)
MARGIN		±.005" (.127MM)
CABLE WIDTH		±.005" (.127MM)

P ARLEX CORPORATION
 ONE PARLEX PLACE
 METHUEN, MA 01844

LAMINATED CABLE DIVISION

SPECIFICATION DRAWING FOR STANDARD ZIF CABLE - SAME SIDE

SIZE	FSCM	PS-2562		Rev.
B	18377			B
SCALE	NA			SHEET 1 OF 1