



International Components Corporation

Quality Components since 1970

PIEZO SOUNDER WITH BUILT-IN CIRCUIT



ROHS COMPLIANT

PART NUMBER:

BPS9234S-24-C

SPECIFICATIONS:

RATED VOLTAGE:	24 VDC
OPERATING VOLTAGE:	6 ~ 28 VDC
MAX CURRENT:	150 mA
SOUND OUTPUT LEVEL:	115dB @ 1M
TERMINAL TYPE:	SCREW
RESONANT FREQUENCY:	2800 Hz
OPERATING TEMPERATURE:	-20 TO +70 °C
TONE MODE:	CONT., SIREN or
FRAME DIAMETER:	92 x 92 mm
FRAME DEPTH:	34.0 mm
MOUNTING DIMENSIONS:	72.0 mm

DIMENSIONS:

