








SECTION B-B



NOTES:

- 1) HOUSING MATERIAL: GLASS FILLED HIGH TEMP THERMOPLASTIC, COLOR: BLACK
- 2) TERMINAL MATERIAL: PHOSPHOR BRONZE
- 3) SEE SHT 2 FOR CKT SIZE, PART NUMBERS AND OVERALL DIMENSIONS, SEE SHT 3 FOR VOIDS.
- 4) FOR ILLUSTRATION, 6 CKT ASSY SHOWN.
- 5) REFER TO PRODUCT SPEC PS-79107
- 6) PACKAGING PER PK-70873-0180
- 7) CKTS NUMBERED FROM LEFT TO RIGHT WHEN PART IS VIEWED FROM TOP WITH RECESS ON THE RIGHT AS SHOWN.
- 8) SOLDER TAIL TO BE MEASURED BY PITCH GAUGE.



PLATING OPTION:

- 4) - 30u"/0.76um MIN GOLD PLATE IN SELECTED AREA
75u"/1.90um MIN TIN PLATE IN SELECTED AREA
BOTH OVER 50u"/1.25um MIN NICKEL OVERALL
- 5) - 15u"/0.38um MIN GOLD PLATE IN SELECTED AREA
75u"/1.90um MIN TIN PLATE IN SELECTED AREA
BOTH OVER 50u"/1.25um MIN NICKEL OVERALL
- 6) - 2u"/0.05um MIN GOLD PLATE IN SELECTED AREA
40u"/1.02um MIN TIN PLATE IN SELECTED AREA
BOTH OVER 40u"/1.02um MIN NICKEL OVERALL

ADD CONTACT PT DIM		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION	
EC NO: S2011-0137		DESCRIPTION		mm		MM ONLY		NTS		METRIC		DATE	
2010/08/17		DRWN:SKANG		4 PLACES		DRAWN BY		DATE		TITLE		1989/05/15	
2011/01/08		CHKD:ATSEE		3 PLACES		CHECKED BY		DATE		2MM DUAL ROW		1989/05/15	
2011/01/10		APPR:MLONG		2 PLACES		APPROVED BY		DATE		VERTICAL RECEPTACLE T/H		1989/05/15	
				1 PLACE		WAZ		1989/05/15		MOLEX INCORPORATED			
						MATERIAL NO.		DOCUMENT NO.		SDA-79107-****		SHEET NO.	
						SEE TABLE						1 OF 3	
						THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							

	10	9	8	7	6	5	4	3	2	1																																																																																																																																																																																																																																																																																																																																																																																																																	
F	<table><tr><td rowspan="3">CKT SIZE</td><td rowspan="3">DIM 'A'</td><td rowspan="3">DIM 'B'</td><td colspan="6">P.C.TAIL DIMENSION 'C' = 3.00</td><td colspan="6">P.C.TAIL DIMENSION 'C' = 1.91</td></tr><tr><td colspan="2">PLATING OPTION 5</td><td colspan="2">PLATING OPTION 4</td><td colspan="2">PLATING OPTION 6</td><td colspan="2">PLATING OPTION 5</td><td colspan="2">PLATING OPTION 4</td><td colspan="2">PLATING OPTION 6</td></tr><tr><td colspan="2">ITEM NO.</td><td colspan="2">ITEM NO.</td><td colspan="2">ITEM NO.</td><td colspan="2">ITEM NO.</td><td colspan="2">ITEM NO.</td><td colspan="2">ITEM NO.</td></tr><tr><td>04</td><td>(4.19)</td><td>(2.00)</td><td></td><td>79107-7001</td><td></td><td>79107-7051</td><td>X</td><td>79107-7126</td><td></td><td>79107-7201</td><td></td><td>79107-7251</td><td>X</td><td>79107-7326</td></tr><tr><td>06</td><td>(6.19)</td><td>(4.00)</td><td></td><td>79107-7002</td><td></td><td>79107-7052</td><td>X</td><td>79107-7127</td><td></td><td>79107-7202</td><td></td><td>79107-7252</td><td>X</td><td>79107-7327</td></tr><tr><td>08</td><td>(8.19)</td><td>(6.00)</td><td></td><td>79107-7003</td><td></td><td>79107-7053</td><td>X</td><td>79107-7128</td><td></td><td>79107-7203</td><td></td><td>79107-7253</td><td>X</td><td>79107-7328</td></tr><tr><td>10</td><td>(10.19)</td><td>(8.00)</td><td></td><td>79107-7004</td><td></td><td>79107-7054</td><td>X</td><td>79107-7129</td><td></td><td>79107-7204</td><td></td><td>79107-7254</td><td>X</td><td>79107-7329</td></tr><tr><td>12</td><td>(12.19)</td><td>(10.00)</td><td></td><td>79107-7005</td><td></td><td>79107-7055</td><td></td><td>79107-7130</td><td></td><td>79107-7205</td><td></td><td>79107-7255</td><td></td><td>79107-7330</td></tr><tr><td>14</td><td>(14.19)</td><td>(12.00)</td><td></td><td>79107-7006</td><td></td><td>79107-7056</td><td>X</td><td>79107-7131</td><td></td><td>79107-7206</td><td></td><td>79107-7256</td><td>X</td><td>79107-7331</td></tr><tr><td>16</td><td>(16.19)</td><td>(14.00)</td><td></td><td>79107-7007</td><td></td><td>79107-7057</td><td>X</td><td>79107-7132</td><td></td><td>79107-7207</td><td></td><td>79107-7257</td><td>X</td><td>79107-7332</td></tr><tr><td>18</td><td>(18.19)</td><td>(16.00)</td><td></td><td>79107-7008</td><td></td><td>79107-7058</td><td>X</td><td>79107-7133</td><td></td><td>79107-7208</td><td></td><td>79107-7258</td><td>X</td><td>79107-7333</td></tr><tr><td>20</td><td>(20.19)</td><td>(18.00)</td><td></td><td>79107-7009</td><td></td><td>79107-7059</td><td>X</td><td>79107-7134</td><td></td><td>79107-7209</td><td></td><td>79107-7259</td><td>X</td><td>79107-7334</td></tr><tr><td>22</td><td>(22.19)</td><td>(20.00)</td><td></td><td>79107-7010</td><td></td><td>79107-7060</td><td>X</td><td>79107-7135</td><td></td><td>79107-7210</td><td></td><td>79107-7260</td><td>X</td><td>79107-7335</td></tr><tr><td>24</td><td>(24.19)</td><td>(22.00)</td><td></td><td>79107-7011</td><td></td><td>79107-7061</td><td>X</td><td>79107-7136</td><td></td><td>79107-7211</td><td></td><td>79107-7261</td><td>X</td><td>79107-7336</td></tr><tr><td>26</td><td>(26.19)</td><td>(24.00)</td><td></td><td>79107-7012</td><td></td><td>79107-7062</td><td>X</td><td>79107-7137</td><td></td><td>79107-7212</td><td></td><td>79107-7262</td><td>X</td><td>79107-7337</td></tr><tr><td>28</td><td>(28.19)</td><td>(26.00)</td><td></td><td>79107-7013</td><td></td><td>79107-7063</td><td>X</td><td>79107-7138</td><td></td><td>79107-7213</td><td></td><td>79107-7263</td><td>X</td><td>79107-7338</td></tr><tr><td>30</td><td>(30.19)</td><td>(28.00)</td><td></td><td>79107-7014</td><td></td><td>79107-7064</td><td>X</td><td>79107-7139</td><td></td><td>79107-7214</td><td></td><td>79107-7264</td><td>X</td><td>79107-7339</td></tr><tr><td>32</td><td>(32.19)</td><td>(30.00)</td><td></td><td>79107-7015</td><td></td><td>79107-7065</td><td>X</td><td>79107-7140</td><td></td><td>79107-7215</td><td></td><td>79107-7265</td><td>X</td><td>79107-7340</td></tr><tr><td>34</td><td>(34.19)</td><td>(32.00)</td><td></td><td>79107-7016</td><td></td><td>79107-7066</td><td>X</td><td>79107-7141</td><td></td><td>79107-7216</td><td></td><td>79107-7266</td><td>X</td><td>79107-7341</td></tr><tr><td>36</td><td>(36.19)</td><td>(34.00)</td><td></td><td>79107-7017</td><td></td><td>79107-7067</td><td>X</td><td>79107-7142</td><td></td><td>79107-7217</td><td></td><td>79107-7267</td><td>X</td><td>79107-7342</td></tr><tr><td>38</td><td>(38.19)</td><td>(36.00)</td><td></td><td>79107-7018</td><td></td><td>79107-7068</td><td>X</td><td>79107-7143</td><td></td><td>79107-7218</td><td></td><td>79107-7268</td><td>X</td><td>79107-7343</td></tr><tr><td>40</td><td>(40.19)</td><td>(38.00)</td><td></td><td>79107-7019</td><td></td><td>79107-7069</td><td>X</td><td>79107-7144</td><td></td><td>79107-7219</td><td></td><td>79107-7269</td><td>X</td><td>79107-7344</td></tr><tr><td>42</td><td>(42.19)</td><td>(40.00)</td><td></td><td>79107-7020</td><td></td><td>79107-7070</td><td>X</td><td>79107-7145</td><td></td><td>79107-7220</td><td></td><td>79107-7270</td><td>X</td><td>79107-7345</td></tr><tr><td>44</td><td>(44.19)</td><td>(42.00)</td><td></td><td>79107-7021</td><td></td><td>79107-7071</td><td>X</td><td>79107-7146</td><td></td><td>79107-7221</td><td></td><td>79107-7271</td><td>X</td><td>79107-7346</td></tr><tr><td>46</td><td>(46.19)</td><td>(44.00)</td><td></td><td>79107-7022</td><td></td><td>79107-7072</td><td>X</td><td>79107-7147</td><td></td><td>79107-7222</td><td></td><td>79107-7272</td><td>X</td><td>79107-7347</td></tr><tr><td>48</td><td>(48.19)</td><td>(46.00)</td><td></td><td>79107-7023</td><td></td><td>79107-7073</td><td>X</td><td>79107-7148</td><td></td><td>79107-7223</td><td></td><td>79107-7273</td><td>X</td><td>79107-7348</td></tr><tr><td>50</td><td>(50.19)</td><td>(48.00)</td><td></td><td>79107-7024</td><td></td><td>79107-7074</td><td>X</td><td>79107-7149</td><td></td><td>79107-7224</td><td></td><td>79107-7274</td><td>X</td><td>79107-7349</td></tr></table>											CKT SIZE	DIM 'A'	DIM 'B'	P.C.TAIL DIMENSION 'C' = 3.00						P.C.TAIL DIMENSION 'C' = 1.91						PLATING OPTION 5		PLATING OPTION 4		PLATING OPTION 6		PLATING OPTION 5		PLATING OPTION 4		PLATING OPTION 6		ITEM NO.		ITEM NO.		ITEM NO.		ITEM NO.		ITEM NO.		ITEM NO.		04	(4.19)	(2.00)		79107-7001		79107-7051	X	79107-7126		79107-7201		79107-7251	X	79107-7326	06	(6.19)	(4.00)		79107-7002		79107-7052	X	79107-7127		79107-7202		79107-7252	X	79107-7327	08	(8.19)	(6.00)		79107-7003		79107-7053	X	79107-7128		79107-7203		79107-7253	X	79107-7328	10	(10.19)	(8.00)		79107-7004		79107-7054	X	79107-7129		79107-7204		79107-7254	X	79107-7329	12	(12.19)	(10.00)		79107-7005		79107-7055		79107-7130		79107-7205		79107-7255		79107-7330	14	(14.19)	(12.00)		79107-7006		79107-7056	X	79107-7131		79107-7206		79107-7256	X	79107-7331	16	(16.19)	(14.00)		79107-7007		79107-7057	X	79107-7132		79107-7207		79107-7257	X	79107-7332	18	(18.19)	(16.00)		79107-7008		79107-7058	X	79107-7133		79107-7208		79107-7258	X	79107-7333	20	(20.19)	(18.00)		79107-7009		79107-7059	X	79107-7134		79107-7209		79107-7259	X	79107-7334	22	(22.19)	(20.00)		79107-7010		79107-7060	X	79107-7135		79107-7210		79107-7260	X	79107-7335	24	(24.19)	(22.00)		79107-7011		79107-7061	X	79107-7136		79107-7211		79107-7261	X	79107-7336	26	(26.19)	(24.00)		79107-7012		79107-7062	X	79107-7137		79107-7212		79107-7262	X	79107-7337	28	(28.19)	(26.00)		79107-7013		79107-7063	X	79107-7138		79107-7213		79107-7263	X	79107-7338	30	(30.19)	(28.00)		79107-7014		79107-7064	X	79107-7139		79107-7214		79107-7264	X	79107-7339	32	(32.19)	(30.00)		79107-7015		79107-7065	X	79107-7140		79107-7215		79107-7265	X	79107-7340	34	(34.19)	(32.00)		79107-7016		79107-7066	X	79107-7141		79107-7216		79107-7266	X	79107-7341	36	(36.19)	(34.00)		79107-7017		79107-7067	X	79107-7142		79107-7217		79107-7267	X	79107-7342	38	(38.19)	(36.00)		79107-7018		79107-7068	X	79107-7143		79107-7218		79107-7268	X	79107-7343	40	(40.19)	(38.00)		79107-7019		79107-7069	X	79107-7144		79107-7219		79107-7269	X	79107-7344	42	(42.19)	(40.00)		79107-7020		79107-7070	X	79107-7145		79107-7220		79107-7270	X	79107-7345	44	(44.19)	(42.00)		79107-7021		79107-7071	X	79107-7146		79107-7221		79107-7271	X	79107-7346	46	(46.19)	(44.00)		79107-7022		79107-7072	X	79107-7147		79107-7222		79107-7272	X	79107-7347	48	(48.19)	(46.00)		79107-7023		79107-7073	X	79107-7148		79107-7223		79107-7273	X	79107-7348	50	(50.19)	(48.00)		79107-7024		79107-7074	X	79107-7149		79107-7224		79107-7274	X	79107-7349	F
CKT SIZE	DIM 'A'	DIM 'B'	P.C.TAIL DIMENSION 'C' = 3.00						P.C.TAIL DIMENSION 'C' = 1.91																																																																																																																																																																																																																																																																																																																																																																																																																		
			PLATING OPTION 5		PLATING OPTION 4		PLATING OPTION 6		PLATING OPTION 5		PLATING OPTION 4				PLATING OPTION 6																																																																																																																																																																																																																																																																																																																																																																																																												
			ITEM NO.		ITEM NO.		ITEM NO.		ITEM NO.		ITEM NO.		ITEM NO.																																																																																																																																																																																																																																																																																																																																																																																																														
04	(4.19)	(2.00)		79107-7001		79107-7051	X	79107-7126		79107-7201		79107-7251	X	79107-7326																																																																																																																																																																																																																																																																																																																																																																																																													
06	(6.19)	(4.00)		79107-7002		79107-7052	X	79107-7127		79107-7202		79107-7252	X	79107-7327																																																																																																																																																																																																																																																																																																																																																																																																													
08	(8.19)	(6.00)		79107-7003		79107-7053	X	79107-7128		79107-7203		79107-7253	X	79107-7328																																																																																																																																																																																																																																																																																																																																																																																																													
10	(10.19)	(8.00)		79107-7004		79107-7054	X	79107-7129		79107-7204		79107-7254	X	79107-7329																																																																																																																																																																																																																																																																																																																																																																																																													
12	(12.19)	(10.00)		79107-7005		79107-7055		79107-7130		79107-7205		79107-7255		79107-7330																																																																																																																																																																																																																																																																																																																																																																																																													
14	(14.19)	(12.00)		79107-7006		79107-7056	X	79107-7131		79107-7206		79107-7256	X	79107-7331																																																																																																																																																																																																																																																																																																																																																																																																													
16	(16.19)	(14.00)		79107-7007		79107-7057	X	79107-7132		79107-7207		79107-7257	X	79107-7332																																																																																																																																																																																																																																																																																																																																																																																																													
18	(18.19)	(16.00)		79107-7008		79107-7058	X	79107-7133		79107-7208		79107-7258	X	79107-7333																																																																																																																																																																																																																																																																																																																																																																																																													
20	(20.19)	(18.00)		79107-7009		79107-7059	X	79107-7134		79107-7209		79107-7259	X	79107-7334																																																																																																																																																																																																																																																																																																																																																																																																													
22	(22.19)	(20.00)		79107-7010		79107-7060	X	79107-7135		79107-7210		79107-7260	X	79107-7335																																																																																																																																																																																																																																																																																																																																																																																																													
24	(24.19)	(22.00)		79107-7011		79107-7061	X	79107-7136		79107-7211		79107-7261	X	79107-7336																																																																																																																																																																																																																																																																																																																																																																																																													
26	(26.19)	(24.00)		79107-7012		79107-7062	X	79107-7137		79107-7212		79107-7262	X	79107-7337																																																																																																																																																																																																																																																																																																																																																																																																													
28	(28.19)	(26.00)		79107-7013		79107-7063	X	79107-7138		79107-7213		79107-7263	X	79107-7338																																																																																																																																																																																																																																																																																																																																																																																																													
30	(30.19)	(28.00)		79107-7014		79107-7064	X	79107-7139		79107-7214		79107-7264	X	79107-7339																																																																																																																																																																																																																																																																																																																																																																																																													
32	(32.19)	(30.00)		79107-7015		79107-7065	X	79107-7140		79107-7215		79107-7265	X	79107-7340																																																																																																																																																																																																																																																																																																																																																																																																													
34	(34.19)	(32.00)		79107-7016		79107-7066	X	79107-7141		79107-7216		79107-7266	X	79107-7341																																																																																																																																																																																																																																																																																																																																																																																																													
36	(36.19)	(34.00)		79107-7017		79107-7067	X	79107-7142		79107-7217		79107-7267	X	79107-7342																																																																																																																																																																																																																																																																																																																																																																																																													
38	(38.19)	(36.00)		79107-7018		79107-7068	X	79107-7143		79107-7218		79107-7268	X	79107-7343																																																																																																																																																																																																																																																																																																																																																																																																													
40	(40.19)	(38.00)		79107-7019		79107-7069	X	79107-7144		79107-7219		79107-7269	X	79107-7344																																																																																																																																																																																																																																																																																																																																																																																																													
42	(42.19)	(40.00)		79107-7020		79107-7070	X	79107-7145		79107-7220		79107-7270	X	79107-7345																																																																																																																																																																																																																																																																																																																																																																																																													
44	(44.19)	(42.00)		79107-7021		79107-7071	X	79107-7146		79107-7221		79107-7271	X	79107-7346																																																																																																																																																																																																																																																																																																																																																																																																													
46	(46.19)	(44.00)		79107-7022		79107-7072	X	79107-7147		79107-7222		79107-7272	X	79107-7347																																																																																																																																																																																																																																																																																																																																																																																																													
48	(48.19)	(46.00)		79107-7023		79107-7073	X	79107-7148		79107-7223		79107-7273	X	79107-7348																																																																																																																																																																																																																																																																																																																																																																																																													
50	(50.19)	(48.00)		79107-7024		79107-7074	X	79107-7149		79107-7224		79107-7274	X	79107-7349																																																																																																																																																																																																																																																																																																																																																																																																													
E												E																																																																																																																																																																																																																																																																																																																																																																																																															
D												D																																																																																																																																																																																																																																																																																																																																																																																																															
C	*X* - DENOTES THE ITEM IS NOT AVAILABLE CURRENTLY.											C																																																																																																																																																																																																																																																																																																																																																																																																															
B												B																																																																																																																																																																																																																																																																																																																																																																																																															
A	<table><tr><td rowspan="5">ADD CONTACT PT DIM EC NO: S2011-0137 DRWN:SKANG CHKD:ATSEE APPR:MLONG 2010/08/17 2011/01/08 2011/01/10</td><td rowspan="5">QUALITY SYMBOLS ▽_F=0 ▽_F=0 ▽_F=0</td><td rowspan="5">DESCRIPTION REV</td><td colspan="2">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2">DIMENSION STYLE MM ONLY</td><td>SCALE NTS</td><td>DESIGN UNITS METRIC</td><td colspan="2">THIRD ANGLE PROJECTION</td></tr><tr><td></td><td></td><td>mm</td><td>INCH</td><td>DRAWN BY AAB</td><td>DATE 1989/05/15</td><td colspan="2" rowspan="2">2MM DUAL ROW VERTICAL RECEPTACLE T/H</td></tr><tr><td></td><td></td><td></td><td></td><td>CHECKED BY MJM</td><td>DATE 1989/05/15</td></tr><tr><td></td><td></td><td></td><td></td><td></td><td></td><td>APPROVED BY WAZ</td><td>DATE 1989/05/15</td><td colspan="2">MOLEX INCORPORATED</td></tr><tr><td></td><td></td><td></td><td></td><td></td><td></td><td>MATERIAL NO.</td><td>DOCUMENT NO.</td><td colspan="2">SDA-79107-****</td></tr><tr><td></td><td></td><td></td><td></td><td></td><td></td><td>SIZE A3</td><td colspan="5">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td></tr><tr><td></td><td></td><td></td><td></td><td></td><td></td><td colspan="2">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td colspan="2">SHEET NO. 2 OF 3</td><td colspan="2"></td></tr></table>											ADD CONTACT PT DIM EC NO: S2011-0137 DRWN:SKANG CHKD:ATSEE APPR:MLONG 2010/08/17 2011/01/08 2011/01/10	QUALITY SYMBOLS ▽ _F =0 ▽ _F =0 ▽ _F =0	DESCRIPTION REV	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION				mm	INCH	DRAWN BY AAB	DATE 1989/05/15	2MM DUAL ROW VERTICAL RECEPTACLE T/H						CHECKED BY MJM	DATE 1989/05/15							APPROVED BY WAZ	DATE 1989/05/15	MOLEX INCORPORATED								MATERIAL NO.	DOCUMENT NO.	SDA-79107-****								SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SHEET NO. 2 OF 3				A																																																																																																																																																																																																																																																																																																																																										
ADD CONTACT PT DIM EC NO: S2011-0137 DRWN:SKANG CHKD:ATSEE APPR:MLONG 2010/08/17 2011/01/08 2011/01/10	QUALITY SYMBOLS ▽ _F =0 ▽ _F =0 ▽ _F =0	DESCRIPTION REV	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION																																																																																																																																																																																																																																																																																																																																																																																																																		
					mm	INCH	DRAWN BY AAB	DATE 1989/05/15	2MM DUAL ROW VERTICAL RECEPTACLE T/H																																																																																																																																																																																																																																																																																																																																																																																																																		
							CHECKED BY MJM	DATE 1989/05/15																																																																																																																																																																																																																																																																																																																																																																																																																			
									APPROVED BY WAZ	DATE 1989/05/15	MOLEX INCORPORATED																																																																																																																																																																																																																																																																																																																																																																																																																
									MATERIAL NO.	DOCUMENT NO.	SDA-79107-****																																																																																																																																																																																																																																																																																																																																																																																																																
						SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																																																																																																																																																																																																																																																																																																																																																																																																				
						DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SHEET NO. 2 OF 3																																																																																																																																																																																																																																																																																																																																																																																																																			
fb_frame_A3_P_AM_T Rev. F 2009/06/18	9	8	7	6	5	4	3	2	1																																																																																																																																																																																																																																																																																																																																																																																																																		

MOLDED VOID OPTION

ASSEMBLIES WITHOUT PEGS

CKT. SIZE	ASSEMBLY	VOID LOCATION(S) SEE SHEET 1 FOR CONVENTION		PLATING OPTION	DIM. "A"	DIM. "B"	P.C. TAIL DIM. "C"
	ITEM NO.	ROW	CKT. NO.(s)				
24	79107-5101	ROW B	6	5	(24.19)	(22.00)	(3.00)
10	79107-5102	ROW A	5	5	(10.19)	(8.00)	(3.00)
26	79107-5103	ROW B	5	5	(26.19)	(24.00)	(3.00)
20	79107-5104	ROW A	7	5	(20.19)	(18.00)	(1.91)
24	79107-5105	ROW B	10	5	(24.19)	(22.00)	(1.91)
20	79107-5106	ROW A	7	5	(20.19)	(18.00)	(3.00)
24	79107-5107	ROW B	10	5	(24.19)	(22.00)	(3.00)

"X" - DENOTES THE ITEM IS NOT AVAILABLE CURRENTLY.

NOTES

- TERMINALS WILL BE PRESENT IN VOIDED LOCATIONS HOWEVER, PIN WINDOWS WILL BE CLOSED.
- VOIDS CANNOT BE PRESENT IN BOTH ROWS ON A CONNECTOR.

ADD CONTACT PT DIM EC NO: S2011-0137 DRWN:SKANG CHKD:ATSEE APPR:MLONG 2010/08/17 2011/01/08 2011/01/10	QUALITY SYMBOLS FA=0 FG=0 FP=0 DESCRIPTION REV	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			
				mm	INCH	DRAWN BY	DATE	TITLE 2MM DUAL ROW VERTICAL RECEPTACLE T/H			
		4 PLACES	± ---	± ---	AAB	1989/05/15					
		3 PLACES	± ---	± ---	CHECKED BY	DATE	MOLEX MOLEX INCORPORATED				
		2 PLACES	± 0.25	± ---	MJM	1989/05/15					
1 PLACE	± ---	± ---	APPROVED BY	DATE	DOCUMENT NO. SDA-79107-****						
ANGULAR ±1/2°		WAZ	1989/05/15								
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO.		SEE TABLE		SHEET NO.					
				SIZE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					
H2				A3							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[79107-7261](#)