



MBU 1


Industrial Connectors: Measuring and Testing Equipment: Sockets: 2 mm system

Product description

Description 2 mm diameter bright metal miniature socket. Brass nickel-plated socket body, tin-plated copper beryllium contact (spring-loaded), with solder connection. Suitable for installation in equipment chassis and switch panels up to a maximum wall thickness of 8 mm.

Type	MBU 1
Order No.	930 312-000
System	2 mm system

Drawing



Technical data

Type of contact	socket (spring-loaded)
Type of termination	solder
Rated voltage	DC 60 V
Rated current	6 A
Contact resistance	6 mOhm
Mounting	screw

Material

Contact material	copper beryllium
Contact surface material	tin-plated
Housing material	PF2400

Environmental conditions

Temperature range	-20 °C to +60 °C
--------------------------	------------------

Inflammability class

Housing	94 V-0
----------------	--------