





NOTES:  
1.MATERIAL:  
HOOD:THERMALPLATIC UL94V0;  
BODY:GLASSFIBER REINFORCED THERMALPLASTIC UL94V0;  
CONTACTS:PHOSPHOR BRONZE;  
PLATING:GOLD OVER 2um NICKEL ON WORKING AREA.  
2.MECHANICAL REQUIREMENT:  
INSERTION FORCE(EACH CONTACT):<=1N;  
WITHDRAWAL FORCE (EACH CONTACT):>=0.19N;  
DURABILITY:>=100CYCLES.  
3.ELECTRICAL REQUIREMENT:  
INITIAL CONTACT RESISTANCE:<=20MILLIOHM;  
INSULATION RESISTANCE AFTER TEST:>=10000MEGAOHM;  
WITHSTANDING VOLTAGE:>1000Vrms;  
OPERATING VOLTAGE:250VAC;  
OPERATING CURRENT:1.3A AT 70 DEGREE.  
4.IF LEAD FREE P/N, GS-14-920 SHOULD BE  
APPLIED.  
5.THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES  
AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN  
GS-22-008.



| PLATING CODE&GOLD THICKNESS |               | E9 Au:1u               |   |   | Z4 or Z6 Au:0.8u |   |                                     |
|-----------------------------|---------------|------------------------|---|---|------------------|---|-------------------------------------|
| PART NUMBER                 |               |                        |   |   |                  |   |                                     |
| 5                           | HPTE1597      | -                      | - | - | 1AB000490003(LF) | - | PLASTIC CABLE CLAMP                 |
|                             | HPTE1586      | -                      | - | - | BPS1B04D0CZ6(LF) | - | CABLE CLAMP Ø7.2                    |
| 4                           | HPTE1585/A    | -                      | - | - | 1AB000490023(LF) | - | CABLE CLAMP Ø12.5                   |
|                             | HPTE1585      | -                      | - | - | BPS1B04D0CZ6(LF) | - | CROSSHEEDED SCREW                   |
| 3                           | BPBS1B04P4    | -                      | - | - | 1AB000490009(LF) | - | OR SLOTTED SCREW                    |
|                             | BPCD3P2--(LF) | -                      | - | - | BPS1B04D3CZ6(LF) | - | CABLE HOOD                          |
| 2                           | BPCD2P2--(LF) | -                      | - | - |                  | - | CONTACT FOR AWG24(IDENTIFICATION=3) |
|                             | BPCD0P2--(LF) | -                      | - | - |                  | - | CONTACT FOR AWG26(IDENTIFICATION=2) |
| 1                           | BPBS1B04P9    | -                      | - | - |                  | - | CONTACT FOR AWG30(IDENTIFICATION=0) |
|                             | BPBS1B04P8    | -                      | - | - |                  | - | BODY FOR AWG30(COLOR=WHITE)         |
|                             | BPBS1B04P1    | -                      | - | - |                  | - | BODY FOR AWG26(COLOR=BLACK)         |
|                             |               | -                      | - | - |                  | - | BODY FOR AWG24(COLOR=GREY)          |
| ITEM                        | CATALOG N°    | QTY. FOR COMPLETE ASSY |   |   | DESCRIPTION      |   | DRAWING                             |

| mat'l. code |                |       |          | tolerances unless otherwise specified |             | CUSTOMER COPY |                    |
|-------------|----------------|-------|----------|---------------------------------------|-------------|---------------|--------------------|
| ltr         | ecn no         | dr    | date     | linear                                | .X ± 0.5    | projection    | title              |
| A           | F03021         | DLE   | 01/29/03 |                                       | .XX ± 0.30  |               | ASSY 2X2           |
| B           | F04-0107       | DLE   | 01/21/04 |                                       |             |               | CAPOT & CON.       |
| C           | N05-0006       | YS    | 01/11/05 | angles                                | ± 2°        |               | VXX27633           |
| D           | N05-0223       | AILEI | 09/05/05 | dr                                    | D LEGRAND   | MM            | product family DIN |
|             |                |       |          | engr                                  | F TISSERAND |               | code               |
|             |                |       |          | chr                                   | JF NOTTEAU  | scale 1:1     | size dwg no        |
|             |                |       |          | appd                                  | F. TI       |               | VJW12162           |
| sheet index | revision sheet | D     | 1        |                                       |             |               | sheet 1 of 1       |