


# HEX NYLON TAPPED SPACERS

561-L4.25, 561-L4.375, 561-L4.50, 561-L4.75, 561-L41.0, 561-L6.25, 561-L6.375, 561-L6.50, 561-L6.75, 561-L61.0, 561-L8.25, 561-L8.375, 561-L8.50, 561-L8.75, 561-L81.0, 561-L4.875, 561-L6.875, 561-L8.875, 561-L4.625, 561-L6.625, 561-L8.625, 561-14HTSP023, 561-L61.5

Date Last Revised: 1/7/13

DIMENSIONS: in(mm.)



| MOUSER STOCK NO. | Description | L             | A             | Tapped |
|------------------|-------------|---------------|---------------|--------|
| 561-L4.25        | HTSP 1      | 0.250 (±.015) | 0.250 (±.015) | 4-40   |
| 561-L4.375       | HTSP 2      | 0.375 (±.015) | 0.250 (±.015) | 4-40   |
| 561-L4.50        | HTSP 3      | 0.500 (±.015) | 0.250 (±.015) | 4-40   |
| 561-L4.75        | HTSP 4      | 0.750 (±.015) | 0.250 (±.015) | 4-40   |
| 561-L41.0        | HTSP 5      | 1.000 (±.015) | 0.250 (±.015) | 4-40   |
| 561-L6.25        | HTSP 6      | 0.250 (±.015) | 0.250 (±.015) | 6-32   |
| 561-L6.375       | HTSP 7      | 0.375 (±.015) | 0.250 (±.015) | 6-32   |
| 561-L6.50        | HTSP 8      | 0.500 (±.015) | 0.250 (±.015) | 6-32   |
| 561-L6.75        | HTSP 9      | 0.750 (±.015) | 0.250 (±.015) | 6-32   |
| 561-L61.0        | HTSP 10     | 1.000 (±.015) | 0.250 (±.015) | 6-32   |
| 561-L8.25        | HTSP 11     | 0.250 (±.015) | 0.250 (±.015) | 8-32   |
| 561-L8.375       | HTSP 12     | 0.375 (±.015) | 0.250 (±.015) | 8-32   |
| 561-L8.50        | HTSP 13     | 0.500 (±.015) | 0.250 (±.015) | 8-32   |
| 561-L8.75        | HTSP 14     | 0.750 (±.015) | 0.250 (±.015) | 8-32   |
| 561-L81.0        | HTSP 15     | 1.000 (±.015) | 0.250 (±.015) | 8-32   |
| 561-L4.875       | HTSP 16     | 0.875 (±.015) | 0.250 (±.015) | 4-40   |
| 561-L6.875       | HTSP 17     | 0.875 (±.015) | 0.250 (±.015) | 6-32   |
| 561-L8.875       | HTSP 18     | 0.875 (±.015) | 0.250 (±.015) | 8-32   |
| 561-L4.625       | HTSP 19     | 0.625 (±.015) | 0.250 (±.015) | 4-40   |
| 561-L6.625       | HTSP 20     | 0.625 (±.015) | 0.250 (±.015) | 6-32   |
| 561-L8.625       | HTSP 21     | 0.625 (±.015) | 0.250 (±.015) | 8-32   |
| 561-14HTSP023    | HTSP 23     | 1.250 (±.015) | 0.250 (±.015) | 6-32   |
| 561-L61.5        | HTSP 36     | 1.500 (±.015) | 0.250 (±.015) | 6-32   |
| RoHS Compliant   |             |               |               |        |

Available from Mouser Electronics  
1-800-346-6873 / [www.mouser.com](http://www.mouser.com)

EPD-200914