

Cover plate - HC-D 25-AP-OG - 1774966

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Cover plate, for HEAVYCON wall-cutouts, cutout 24 x 74 mm, for type D25



The illustration shows version HC-B
24-AP in orange



Key commercial data

Packing unit	1 pc
GTIN	 4 017918 037932
Weight per Piece (excluding packing)	14.92 GRM
Custom tariff number	85472000
Country of origin	Germany

Technical data

Dimensions

Length	103 mm
Height	45 mm
Hole diameter	4.5 mm
Width	2 mm
Drill hole distance, horizontal	86 mm
Drill hole distance, vertical	17.5 mm
Internal cutout dimension	24 x 74 mm

General

Note	For wall cutouts of type D25
Material	PA
Inflammability class according to UL 94	HB

Cover plate - HC-D 25-AP-OG - 1774966

Technical data

General

Color	orange
Design	D25

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209

ETIM

ETIM 3.0	EC002309
ETIM 4.0	EC000886
ETIM 5.0	EC002314

UNSPSC

UNSPSC 6.01	30211817
UNSPSC 7.0901	39121416
UNSPSC 11	39121408
UNSPSC 12.01	39121408
UNSPSC 13.2	39121408

Approvals

Approvals

Approvals

GOST

Ex Approvals

Approvals submitted

Cover plate - HC-D 25-AP-OG - 1774966

Approvals

Approval details

GOST 

Drawings

