

Technical Specifications



**CI5164 /
CI5168**



**CI7904 /
CI7912**

Cat. No.	Trade Size	
	E.M.T.	Rigid
E.M.T. / Rigid Couplings (Zinc Alloy)		
CI5164	1/2	1/2
CI5166	3/4	3/4
CI5168	1	1
Concrete-tight		
Cat. No.	Trade Size	
3-piece Couplings (Machined steel)		
CI7904	1/2	
CI7906	3/4	
CI7908	1	
CI7910	1-1/4	
CI7912	1-1/2	
EK-406	2	

Rigid Conduit

Locknuts

IBERVILLE®

Technical Specifications



**CI1704 /
CI1748**



**CI1704-AL /
CI1732-AL**



**CI1703-PL /
CI1706-PL**



**CI1704-SL /
CI1732-SL**



**LN-201 /
LN-210**

Cat. No.					Trade Size
Steel	Aluminum	Nylon	Sealing	Zinc	
Locknuts					
—	—	CI1703-PL	—	—	3/8
CI1704	CI1704-AL	CI1704-PL	CI1704-SL	LN-201	1/2
CI1706	CI1706-AL	CI1706-PL	CI1706-SL	LN-202	3/4
CI1708	CI1708-AL	—	CI1708-SL	LN-203	1
CI1710	CI1710-AL	—	CI1710-SL	LN-204	1-1/4
CI1712	CI1712-AL	—	CI1712-SL	LN-205	1-1/2
CI1716	CI1716-AL	—	CI1716-SL	LN-206	2
CI1720	CI1720-AL	—	CI1720-SL	LN-207	2-1/2
CI1724	CI1724-AL	—	CI1724-SL	LN-208	3
CI1728	CI1728-AL	—	CI1728-SL	LN-209	3-1/2
CI1732	CI1732-AL	—	CI1732-SL	LN-210	4
CI1740	—	—	—	—	5
CI1748	—	—	—	—	6



Technical Specifications



**CIRB6R4 /
CIRB16R12**



**BU-201 /
BU-210**



**CI2404 /
CI2448**



**CI2704 /
CI2748**

Rated 105°C



**CI2604 /
CI2632**

With solid copper lug.

Cat. No.	Trade Size	Cat. No.	Trade Size
Reducing Bushings - NPS (Steel)		Insulated Metallic Bushings (Aluminum)	
CIRB6R4	3/4 x 1/2	CI2404	1/2
CIRB8R4	1 x 1/2	CI2406	3/4
CIRB8R6	1 x 3/4	CI2408	1
CIRB10R4	1-1/4 x 1/2	CI2410	1-1/4
CIRB10R6	1-1/4 x 3/4	CI2412	1-1/2
CIRB10R8	1-1/4 x 1	CI2416	2
CIRB12R4	1-1/2 x 1/2	CI2420	2-1/2
CIRB12R6	1-1/2 x 3/4	CI2424	3
CIRB12R8	1-1/2 x 1	CI2428	3-1/2
CIRB12R10	1-1/2 x 1-1/4	CI2432	4
CIRB16R4	2 x 1/2	CI2440	5
CIRB16R6	2 x 3/4		
CIRB16R8	2 x 1	Plastic Bushings	
CIRB16R10	2 x 1-1/4	CI2704	1/2
CIRB16R12	2 x 1-1/2	CI2706	3/4
Conduit Bushings (Zinc Die Cast)		CI2708	1
BU-201	1/2	CI2710	1-1/4
BU-202	3/4	CI2712	1-1/2
BU-203	1	CI2716	2
BU-204	1-1/4	CI2720	2-1/2
BU-205	1-1/2	CI2724	3
BU-206	2	CI2728	3-1/2
BU-207	2-1/2	CI2732	4
BU-208	3	CI2740	5
BU-209	3-1/2	CI2748	6
BU-210	4	Models CI2404 & CI2406 are in zinc.	

Cat. No.	Trade Size	Ground Wire Size (AWG)
Insulated Grounding Bushings (Aluminum)		
CI2604	1/2	14-6
CI2606	3/4	14-6
CI2608	1	14-6
CI2610	1-1/4	14-4
CI2612	1-1/2	14-4
CI2616	2	6-1/0
CI2620	2-1/2	6-1/0
CI2624	3	2-4/0
CI2628	3-1/2	2-4/0
CI2632	4	2-4/0



Rigid Conduit

Pull Elbows and Conduit Fittings

IBERVILLE®

Technical Specifications




**CI7204 /
CI7206**

Zinc Die Cast Locknut



**CI7304 (-G) /
CI7310 (-G)**


-G: with gasket



**CICA-1/2 /
CICA-2**



**CICA-2-1/2 /
CICA-4**



**CILRL-1/2 /
CILRL-2**

Supplied with 2 covers



**CILL-2 1/2 /
CILL-4**



**CILR-2 1/2 /
CILR-4**

Cat. No.	Trade Size	Dimensions		
		A	B	C
Pull Elbows, Rigid to Box (Zinc Alloy)				
CI7204	1/2	1-5/16	1-1/8	—
CI7206	3/4	1-5/8	1-5/16	—
Pull Elbows, Rigid to Rigid (Zinc Alloy)				
CI7304	1/2	1-5/16	1-1/8	—
CI7306	3/4	1-7/16	1-5/16	—
CI7304-G	1/2	1-5/16	1-1/8	—
CI7306-G	3/4	1-7/16	1-5/16	—
CI7308-G	1	2	1-5/8	—
CI7310-G	1-1/4	2-1/4	2	—
Rigid Conduit Fittings - “C” Type (Cast Aluminum)				
CICA-1/2	1/2	4-7/8	1-3/8	1-3/8
CICA-3/4	3/4	5-9/16	1-1/2	1-7/16
CICA-1	1	6-1/2	1-3/4	1-3/4
CICA-1-1/4	1-1/4	8-5/8	1-15/16	2-1/2
CICA-1-1/2	1-1/2	8-5/8	2-11/16	2-1/2
CICA-2	2	10-15/16	3	3-3/16
CICA-2-1/2	2-1/2	12-3/4	5-1/8	4-1/4
CICA-3	3	12-3/4	5-1/8	4-1/4
CICA-3-1/2	3-1/2	15	6-1/2	5-1/4
CICA-4	4	15	6-1/2	5-1/4
Rigid Conduit Fittings - “LRL” Type (Cast Aluminum)				
CILRL-1/2	1/2	4-7/16	1-11/16	2-1/8
CILRL-3/4	3/4	5-3/16	1-7/8	2-1/4
CILRL-1	1	6	2-3/16	2-1/2
CILRL-1-1/4	1-1/4	7-15/16	2-3/4	3-1/2
CILRL-1-1/2	1-1/2	7-15/16	3-1/4	3-1/2
CILRL-2	2	10-3/16	3-11/16	4-1/8
Rigid Conduit Fittings - “LL” Type (Cast Aluminum)				
CILL-2 1/2	2-1/2	12-1/4	5-1/8	5-3/4
CILL-3	3	12-1/4	5-1/8	5-3/4
CILL-3 1/2	3-1/2	14-3/8	6-1/4	6-3/4
CILL-4	4	14-3/8	6-1/4	6-3/4
Rigid Conduit Fittings - “LR” Type (Cast Aluminum)				
CILR-2 1/2	2-1/2	12-1/4	5-1/8	5-3/4
CILR-3	3	12-1/4	5-1/8	5-3/4
CILR-3 1/2	3-1/2	14-3/8	6-1/4	6-3/4
CILR-4	4	14-3/8	6-1/4	6-3/4

Gaskets and covers are included with all rigid conduit fittings. CICA-1/2 to CICA-2 and all CILRL are also suitable for use with EMT conduit.



Technical Specifications



**CILBA-1/2 /
CILBA-2**



**CIELBA-2 1/2 /
CIELBA-4**






**CITA-1/2 /
CITA-4**



**CITBA-1/2 /
CITBA-2**



**CIBC-1/2 /
CIBC-2**



**CIG-1/2 /
CIG-2**

Cat. No.	Trade Size	Dimensions		
		A	B	C
Rigid Conduit Fittings - "LB" Type (Cast Aluminum)				
CILBA-1/2	1/2	4-5/16	1-1/2	1-3/8
CILBA-3/4	3/4	4-15/16	1-7/8	1-9/16
CILBA-1	1	6-1/16	2-1/16	1-13/16
CILBA-1-1/4	1-1/4	7-7/8	2-15/16	2-1/2
CILBA-1-1/2	1-1/2	7-7/8	3-1/16	2-1/2
CILBA-2	2	10	3-3/4	3-3/16
CIELBA-2-1/2	2-1/2	13-3/8	5-1/4	5-1/8
CIELBA-3	3	13-3/8	5-1/4	5-1/8
CIELBA-3-1/2	3-1/2	16-1/8	6-11/16	5-7/8
CIELBA-4	4	16-1/8	6-11/16	5-7/8

Rigid Conduit Fittings - "T" Type (Cast Aluminum)				
CITA-1/2	1/2	4-7/8	1-3/8	2-1/16
CITA-3/4	3/4	5-9/16	1-3/4	2-1/8
CITA-1	1	6-1/2	2	2-1/2
CITA-1-1/4	1-1/4	8-11/16	2-5/8	3-1/2
CITA-1-1/2	1-1/2	8-11/16	3	3-9/16
CITA-2	2	10-7/8	3-1/4	4-3/16
CITA-2-1/2	2-1/2	12-5/8	6-3/8	5-3/4
CITA-3	3	12-5/8	6-3/8	5-3/4
CITA-3-1/2	3-1/2	14-7/8	7-1/8	6-3/4
CITA-4	4	14-7/8	7-1/8	6-3/4

Rigid Conduit Fittings - "TB" Type (Cast Aluminum)				
CITBA-1/2	1/2	4-3/8	1-3/8	1-3/8
CITBA-3/4	3/4	5-1/8	2-1/8	1-9/16
CITBA-1	1	6	2-1/2	1-13/16
CITBA-1-1/4	1-1/4	8-1/8	3-1/2	2-1/2
CITBA-1-1/2	1-1/2	8-1/8	3-1/2	2-1/2
CITBA-2	2	10-1/4	4-5/16	3-1/8


Gaskets and covers are included with all rigid conduit fittings. CILBA and CITA-1/2 to CITA-2 are also suitable for use with EMT conduit

Cat. No.	Trade Size	Cat. No.	Trade Size
Blank Covers for Aluminum Conduit Fittings (Stamped Aluminum)		Gaskets for Aluminum Conduit Fittings (Neoprene)	
CIBC-1/2	1/2	CIG-1/2	1/2
CIBC-3/4	3/4	CIG-3/4	3/4
CIBC-1	1	CIG-1	1
CIBC-1-1/4	1-1/4	CIG-1-1/4	1-1/4
CIBC-2	2	CIG-2	2

For 1-1/2, use CIBC-1-1/4

For 1-1/2, use CIG-1-1/4





**CI6R4 /
CI24R20**



**CI3504 * /
CI3516 ***


Technical Specifications

Cat. No.	Trade Size
Reducing Washers (Steel)	
WA-110 *	1/2 x 3/8
CI6R4	3/4 x 1/2
CI8R4	1 x 1/2
CI8R6	1 x 3/4
CI10R4	1-1/4 x 1/2
CI10R6	1-1/4 x 3/4
CI10R8	1-1/4 x 1
CI12R4	1-1/2 x 1/2
CI12R6	1-1/2 x 3/4
CI12R8	1-1/2 x 1
CI12R10	1-1/2 x 1-1/4
CI16R4	2 x 1/2
CI16R6	2 x 3/4
CI16R8	2 x 1
CI16R10	2 x 1-1/4
CI16R12	2 x 1-1/2
CI20R4	2-1/2 x 1/2
CI20R6	2-1/2 x 3/4
CI20R8	2-1/2 x 1
CI20R10	2-1/2 x 1-1/4
CI20R12	2-1/2 x 1-1/2
CI20R16	2-1/2 x 2
CI24R4	3 x 1/2
CI24R6	3 x 3/4
CI24R8	3 x 1
CI24R10	3 x 1-1/4
CI24R12	3 x 1-1/2
CI24R16	3 x 2
CI24R20	3 x 2-1/2
Knockout Closures (Steel)	
CI3504 *	1/2
CI3506 *	3/4
CI3508 *	1
CI3510 *	1-1/4
CI3512 *	1-1/2
CI3516 *	2


* Not CSA approved



Technical Specifications



**500-SC /
503-SC**



**PC-3/8 /
PC-4**



**RCS-1/2 /
RCS-2**



**RC-1/2 /
RC-4-SC**



**EC-1/2 /
EC-3**

Cat. No.	Trade Size	Jaw Opening	Tap Base and Back	Dimensions		
				A	B	C
Beam Clamps (Malleable Iron)						
500-SC	1/4NC	15/16	1/4-20	1	1-1/4	1-7/16
501	5/16NC	7/8	5/16-18	1-9/16	1-9/16	1-11/16
502	3/8NC	1	3/8-16	2	1-7/8	1-3/4
503-SC	1/2NC	1	1/2-13	2-1/2	2-3/8	2-3/8

Cat. No.	Trade Size	Cat. No.	Trade Size
RCS Type Beam Clamps (Steel)		EC Type Beam Clamps (Malleable Iron)	
RCS-1/2	1/2	EC-1/2	1/2
RCS-3/4	3/4	EC-3/4	3/4
RCS-1	1	EC-1	1
RCS-1-1/4	1-1/4	EC-1-1/4	1-1/4
RCS-1-1/2	1-1/2	EC-1-1/2	1-1/2
RCS-2	2	EC-2	2
PC Type Beam Clamps (Malleable Iron)		EC-2-1/2	2-1/2
PC-3/8	3/8	EC-3	3
PC-1/2	1/2	RC Type Beam Clamps (Malleable Iron)	
PC-3/4	3/4	RC-1/2	1/2
PC-1	1	RC-3/4	3/4
PC-1-1/4	1-1/4	RC-1	1
PC-1-1/2	1-1/2	RC-1-1/4	1-1/4
PC 2SC	2	RC-1-1/2	1-1/2
PC-2-1/2	2-1/2	RC-2-SC	2
PC-3	3	RC-2-1/2	2-1/2
PC-3-1/2	3-1/2	RC-3	3
PC-4	4	RC-3-1/2	3-1/2
		RC-4-SC	4



Rigid Conduit

Accessories

IBERVILLE®

Technical Specifications



HA-801



**CI8004 /
CI8008**



**CI8104 /
CI8116**



**FP-401 /
FP-406**

Cat. No.	Trade Size
Conduit Nipples (Insulated)	
HA-801	1/2
HA-802	3/4
HA-803	1
HA-804	1-1/4
HA-805	1-1/2
HA-806	2
HA-807	2-1/2
HA-808	3
HA-809	3-1/2
HA-810	4
Conduit Nipples (Zinc Alloy)	
CI8004	1/2
CI8006	3/4
CI8008	1
HA-204	1-1/4
HA-205	1-1/2
HA-206	2
HA-207	2-1/2
HA-208	3
HA-209	3-1/2
HA-210	4
3/4" Offset Nipples (Zinc Alloy)	
CI8104	1/2
CI8106	3/4
CI8108	1
CI8110	1-1/4
CI8112	1-1/2
CI8116	2
Flange Plates	
FP-401 *	1/2
FP-402 *	3/4
FP-403 *	1
FP-404 *	1-1/4
FP-405 *	1-1/2
FP-406 *	2

* Not CSA certified



Technical Specifications



CI1203 /
CI1216 /



CI1503 /
CI1548



CIEFA-1/2 /
CIEFA-4



CI7538

Cat. No.	Trade Size	Max. Conduit Dia.	Hole Size
One Hole Rigid Straps (Galvanized Steel)			
CI1203	3/8	0.68	1/4
CI1204	1/2	0.84	1/4
CI1206	3/4	1.05	1/4
CI1208	1	1.32	5/16
CI1210	1-1/4	1.66	7/16
CI1212	1-1/2	1.90	7/16
CI1216	2	2.38	9/16
Two Hole Rigid Straps (Galvanized Steel)			
CI1503	3/8	0.68	3/16
CI1504	1/2	0.84	3/16
CI1506	3/4	1.05	3/16
CI1508	1	1.32	3/16
CI1510	1-1/4	1.66	1/4
CI1512	1-1/2	1.90	1/4
CI1516	2	2.38	9/32
CI1520	2-1/2	2.88	3/8
CI1524	3	3.50	3/8
CI1528	3-1/2	4.00	1/2
CI1532	4	4.50	1/2
CI1540	5	5.56	1/2
CI1548	6	6.63	1/2

Cat. No.	Trade Size
Service Entrance Heads (Cast Aluminum)	
CIEFA-1/2	1/2
CIEFA-3/4	3/4
CIEFA-1	1
CIEFA-1-1/4	1-1/4
CIEFA-1-1/2	1-1/2
CIEFA-2	2
CIEFA-2-1/2	2-1/2
CIEFA-3	3
CIEFA-3-1/2	3-1/2
CIEFA-4	4

Consult page 10 for technical specifications.

Cat. No.	Max. Flex. Conduit Dia.	Hole Size
One Hole Double Sided Strap (Galvanized Steel)		
CI7538*	1.05	3/16"

*Any combination of 3/8", 1/2" and 3/4"
EMT, rigid conduit, flexible conduit or teck cables

