




PER VERSIONI POLARIZZATE VEDERE DETTAGLIO
(SEE DETAIL FOR POLARIZATION VERSION)


CODICE FORNITORE "A 047"
(SUPPLIER CODE "A 047")

NO. DI IMPRONTA STAMPO
(MOULD CAVITY IDENTIF. NO.)

SEZIONE A-A
(SECTION A-A)

CAVITA' ADATTE PER CONTATTI P/N:
(CAVITIES SUITABLE FOR CONTACTS P/N:)
282374-1 SEZ. 0.3-0.5 mm² (COD.FIAT 1 /23197/44)
282375-1 SEZ. 0.75-1.5 mm² (COD.FIAT 1 /24834/44)

NUM. DI CAVITA'
(CIRCUIT. IDENTIF. NO.)








DETTAGLIO VERSIONI POLARIZZATE
(DETAIL OF POLARIZATION VERSION)



- 1) QUOTA VALIDA SOLO PER VERSIONE 282368-1
(VALID DIMENSION ONLY FOR 282368-1 VERSION)
- 2) QUOTA VALIDA PER VERSIONI POLARIZZATE P/N 282368-2, -3, -4
(VALID DIMENSION ONLY FOR P/N 282368-2, -3, -4 VERSION)
- 3) PER RAPPRESENTAZIONE DIMA CONTROPARTE VEDERE FOGLIO 2 DI 2
(FOR COUNTERPART DETAIL SEE SHEET 2 OF 2)

NON DISPONIBILE (NOT AVAILABLE)		282372-4		GRIGIO (GREY)		282368-4	
NON DISPONIBILE (NOT AVAILABLE)		282372-3		BLU (BLUE)		282368-3	
NON DISPONIBILE (NOT AVAILABLE)		282372-2		NERO (BLACK)		282368-2	
282631-1 VERS. ORIZZONTALE (HORIZONTAL VERS.)		282372-1		BIANCO (NATURAL)		282368-1	
CONTROP. P.C.B. (P.C.B. HEADER ASSY)		PORTAMASCHI VOLANTE (CAP HOUSING)		COLORE (COLOUR)		MATERIALE (MATERIAL)	
						NUMERO (PART NUMBER)	
				CUSTOMER DWG. FOR REFERENCE ONLY		DISEGNO PER CLIENTE SOLO PER RIFERIMENTO	
				THIS DRAWING IS UNPUBLISHED		RELEASE FOR PUBLICATION	
				© COPYRIGHT 1987 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING.		19	
				TOLLERANZE, SE NON DIVERSAMENTE SPECIFICATO (TOLERANCES, UNLESS OTHERWISE SPECIFIED)		DIAM. ISOLANTE (INS. DIA. RANGE)	
				± 0.3		RANGO FILO (WIRE RANGE)	
				ANGOLI (ANGLES)		SCALA (SCALE)	
				± 2°		2:1	
				B1 REVISED PER ECR-13-004824 M.G. 20MAR 2015		DIS. M. PALMA 18 JUN '97	
				B RELEASED AND REVISED FOR ETOC-0248-97 M.P. 01-7 97		DESCRIZIONE (DESCRIPTION) 070 SERIES MULTILOCK* CONN. PLUG HOUSING 18 POSITION (PORTAFEMINE) DOUBLE ROW	
				2 AGG. CODICE FIAT R.M. 25-10 93		LOC. SIZE NUMERO (INS. DIM. NO.)	
				1 AGGIORNATO R.M. 1-4 93		C-282368	
				REV. (REVISION RECORD)		REV. (SHEET)	
				DIS. DATA (DR) (DATE)		B1 1 01 2	

SEZIONE A-A
(SECTION A-A)



SEZIONE G-G
(SECTION G-G)



TAB: OTTONE TEMPRA 4, STAGNATO
(TAB: BRASS TEMPER 4, TIN PLATED)

CONIARE LE BAVE DI TRINCIATURA
(NO TRIMMING BURRS ADMITABLE)

				DO NOT SCALE		UNLESS OTHERWISE SPECIFIED	
				REMOVE BURRS BREAK EDGES		METRIC (mm) INCHES	
				SURFACE TEXTURE ✓		 	
				G. TY REQ. 'D' PER UNIT		EUROPEAN PROJECTION	
				MATL.		THIRD ANGLE PROJECTION	
				HT. TR.		2 DEC. PLACE ±0.3 1 DEC. PLACE ±0.1 2 DEC. PLACE ±0.05	
				FINISH		2 DEC. PLACE ±0.3 3 DEC. PLACE ±0.03 1 DEC. PLACE ±0.0625	
				DR.		ANGLES ±0°30'	
				CHK.		SCALE	
				APP.		3:1	
						 TE Connectivity	
						NAME	
						070 SERIES MULTILOCK* CONN 18 POS.	
						DOUBLE ROW (DIME DI MONTAGGIO)	
						LOC./SIZE SHEET	
						I A2 2 of 2	
						DWG. NO.	
						C-282368	
REV. LTR.		REVISION RECORD		DR. DATE		E.C.N.	
						REV	
						B1	