

A

B

C


D

E

F

REV.	MODIFICATION.	DATE	DRN
02	CO2010945	22/06/10	SF
03	CO2011122	22/03/11	SF
04	CO2011130	08/04/11	DT
05	CO2011160	01/07/11	SF

PSBM-3-01A-RT \ PSBM-3-19A-RT

TYPICAL RELEASE
TAB LOCATION0.80[0.031] THICK DOUBLE
ADHESIVE TAPE(RMS-24)


NOTES

1. THE COLOUR OF THE LINER MAY VARY THIS WILL NOT AFFECT THE TECHNICAL PROPERTIES OF THE PART.
2. PARTS AVAILABLE IN BLACK. ADD "BK" TO END OF PART NUMBER. EXAMPLE: PSBM-10-01A-RTBK
3. PARTS AVAILABLE WITHOUT ADHESIVE BY SPECIAL ORDER.

INFORMATION CONTAINED IN THIS DOCUMENT IS CONFIDENTIAL TO
RICHCO INTERNATIONAL Co. Ltd. AND MAY NOT BE DISCLOSED OR
REPRODUCED IN WHOLE OR PART WITHOUT THEIR WRITTEN CONSENT.

RICHCO, INC.
WWW.RICHCO-INC.COM

ALL DIMENSIONS IN mm[inches]
GENERAL TOLERANCES ± 0.25
UNLESS OTHERWISE STATED
1 DECIMAL PLACE $\pm$
2 DECIMAL PLACES $\pm$
ANGULAR $\pm 1^\circ$

THIRD
ANGLEMATERIAL:
SEE NOTESCOLOUR:
NATURALDESCRIPTION:
PUSH SPACER BASE MINATUREPART No:
See TableDRG No:
105-0901

NPR No:

SHEET SIZE **A4**DRN
SFDATE
22/06/10CHKD
TCDATE
22/06/10SCALE
NTSSHEET No.
1 OF 1

MATERIAL NYLON 6/6 UL94 V2 (RMS-01)	MATERIAL NYLON 6/6 UL94 V0 (RMS-19)	'A' DIM
PSBM-3-01A-RT	PSBM-3-19A-RT	4.8[.189]
PSBM-4-01A-RT	PSBM-4-19A-RT	6.4[.252]
PSBM-5-01A-RT	PSBM-5-19A-RT	7.9[.311]
PSBM-6-01A-RT	PSBM-6-19A-RT	9.5[.374]
PSBM-7-01A-RT	PSBM-7-19A-RT	11.1[.437]
PSBM-8-01A-RT	PSBM-8-19A-RT	12.7[.500]
PSBM-9-01A-RT	PSBM-9-19A-RT	14.3[.563]
PSBM-10-01A-RT	PSBM-10-19A-RT	15.9[.626]
PSBM-12-01A-RT	PSBM-12-19A-RT	19.1[.752]
PSBM-14-01A-RT	PSBM-14-19A-RT	22.2[.874]

A

B

C

D

E

FORM No. 0143/00