


## Miniature Relampable Indicator Light

### Description and Features



The Chicago Miniature Lamp Miniature Indicator Lights are versatile, industry standard, front panel indicators capable of accepting a variety of T-2 and T-3 1/4 miniature bayonet based incandescent and neon lamps. These indicator lights accept a variety of different lens styles and colors, and are excellent for providing a large, bright, easily noticed status indicator. The lamp is not included with this indicator light; please order the required lamp separately.

## Specifications

| Part Number: | Description                       | Lens Part No: | Description                    |
|--------------|-----------------------------------|---------------|--------------------------------|
| 5100-822     | Solder Lug Terminals, No Resistor | 25P-306*      | Transparent Dome               |
| 5100-823     | Screw Type Terminals, No Resistor | 25P-307**     | Translucent Dome               |
| 5100-824     | .250 Q.C. Terminals, No Resistor  | 25P-326*      | Transparent Fluted Dome        |
|              |                                   | 25P-606*      | Transparent Cylindrical        |
|              |                                   | 25P-607**     | Translucent Cylindrical        |
|              |                                   | 25P-626*      | Transparent Fluted Cylindrical |

\* R = Red, A = Amber, G = Green, C = Clear

\*\* R = Red, Y = Yellow, G = Green, W = White

|                          |                                                                              |
|--------------------------|------------------------------------------------------------------------------|
| Mounting Hole:           | .688                                                                         |
| Mounting Centers:        | .969                                                                         |
| Maximum Panel Thickness: | .406                                                                         |
| Housing/Lens Material:   | Glass filled polyester                                                       |
| Bezel:                   | Stainless steel                                                              |
| Hex Nut:                 | Zinc plated steel                                                            |
| Lockwasher:              | Chromate treated steel                                                       |
| Lenses:                  | High temperature lexan                                                       |
| Approvals:               | UL listed (except Q.C. terminal versions)                                    |
| Electrical Rating:       | up to 250 Volts, up to 3 Watts (contact factory for specific product rating) |