

Distributed by:




**JAMECO**<sup>®</sup>  
ELECTRONICS

**www.Jameco.com ♦ 1-800-831-4242**


The content and copyrights of the attached  
material are the property of its owner.

Jameco Part Number 70755


P.C.B. Socket 2.54mm (0.100")




ROHS



Straight Type




Right Angle Type  
Single Row






Single Row P.C.B. Layout


Dimensions	
Positions	2 thru 40, 4 thru 80
A	2.54 * Position No.
B	2.54 * Position No. -2.54



Double Row P.C.B. Layout



Straight Type



Right Angle Type  
Double Row

# Product Specification

## Material

**Insulator :** Glass-Filled Thermoplastic  
UL94V-0 rates, Color-Black

**Contact :** Brass or Phosphor Bronze  
Plated full gold or selected gold in  
mating area, 100u" min. tin-lead on  
on termination area, with entire contact  
under-plated 50u" min. Nickel

## Electrical

**Contact Resistance :** 20 milliohms  
Max at 1 AMP DC.

**Insulation Resistance :** 5000  
megohms at 500 VDC

**Dielectric Withstanding Voltage :**  
500 VAC/rms 60Hz for 1 minute

**Current Rating :** 1 AMP

**Volatge Rating :** 250 VAC/rms  
60Hz