

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301030015](#)
Status: **Active**
Overview: [Hand Lamps](#)
Description: Watertite Wet Location Incandescent Hand Lamp, 100W with Screw Release Grounded Guard, Cord Type 16/3 SOOW, 7.62m (25.0') Cord Length

Documents:
[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification
CSA LR85374

General
Product Family Portable Lighting
Series [130103](#)
NEMA Configuration NEMA 5-15
NEMA Rating NEMA 4X
Outlet None
Overview [Hand Lamps](#)
Product Name Watertite
Type Hand Lamps
UPC 78678861300

Physical
Cord Length - Primary 7.62m (25.0')
Cord Length - Secondary N/A
Depth 120.65mm (4.750")
Duty Wet Location
Guard Included Yes
Guard Type Grounded, Screw Release
Height 457.20mm (18.000")
Length N/A
Material - Globe Tempered Glass
Material - Guard #8 Gauge Zinc-plated Steel
Mounting Style Hand Held
Packaging Type Carton
Socket Construction N/A

Electrical
Bulb Type Incandescent
Cord Type - Primary 16/3 SOOW
Lamp Type A21
Lamp Wattage - Maximum 100W
Lumens 1000
On/Off Switch No
Voltage (Fixture) - Maximum 120V AC

Material Info
Engineering Number 1203A163



EU ELV
Not Reviewed

EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[130103](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION