




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
DF	X0		R1	REVISED PER ECO-11-005030	11MAR11	RK	HMR

- 1

FOR USE WITH: RG-142/U, 142A/U, 142B/U, 58A/U & 400/U, BELDIN 9246
2. SEE I.S. 6755.
3. USE HAND TOOL: 69710-2
PNEUMATIC TOOL: 69365-8
EXTRACTION TOOL: 58095-1
4. IMPEDANCE: 31 OHMS APPROXIMATELY.



OBSOLETE

58212-1	1	9-221357-0	5-221358-1	Y	5-228596-4
59993-1	RG-179/U,179A/U,179B/U,187/U & 187A/U	9-228603-0	5-1757117-2	X	5-228596-2
59993-1	RG-174/U,188/U & 316/U	9-228603-0	5-1757117-1	X	5-228596-1
59993-1	RG-178/U,178A/U & 178B/U	221824-3	228622-3	X	228596-5
58212-1	1	221357-3	221358-1	Y	228596-4
59993-1	RG-188 TYPE DOUBLE BRAIDED	221205-3	228622-1	X	228596-3
59993-1	RG-179/U,179A/U,179B/U,187/U & 187A/U	228603-3	1757117-2	X	228596-2
59993-1	RG-174/U,188/U & 316/U	228603-3	1757117-1	X	228596-1
DIE SET	USE WITH CABLE	2 FERRULE	1 SOCKET ASSY	VIEW	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B.WERNER 26-AUG-91	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK D.DOYE 26-AUG-91				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D.DOYE 26-AUG-91	NAME			
0 PLC ± -		PRODUCT SPEC				
1 PLC ± -		APPLICATION SPEC	SIZE CAGE CODE DRAWING NO RESTRICTED TO			
2 PLC ± -		WEIGHT -				
3 PLC ± -		CUSTOMER DRAWING	A200779C-228596			
4 PLC ± -		SCALE 8:1				
ANGLES ± -		SHEET 1 OF 1	REV R1			
FINISH -						