


CATALOG LISTING	CIRCUIT MADE WITH TOGGLE LEVER IN		
	KEYWAY SIDE (1-2,4-5)	CENTER (1-2,4-5)	OPPOSITE KEYWAY (2-3,5-6)
112TW19-1	ON	OFF	ON
112TW19-2	OFF	NONE	ON
112TW19-3	ON	NONE	ON
112TW19-21	NONE	OFF	ON
112TW19-31	NONE	ON	ON
112TW19-4	MOM OFF	NONE	ON
112TW19-5	MOM ON	OFF	ON
112TW19-6	MOM ON	NONE	OFF
112TW19-7	MOM ON	OFF	MOM ON
112TW19-8	MOM ON	NONE	ON
112TW19-51	NONE	ON	MOM ON
112TW19-61	MOM ON	OFF	NONE

ELECTRICAL RATING


28 VDC & 125 VAC
5 AMP RES
2 AMP IND
1 AMP LAMP

LEVER STYLE A




LEVER COLOR CODE


COLOR IDENT	COLOR
001	WT-07 WHITE
002	BK-09 BLACK
003	BL-05 BLUE
004	RD-08 RED
005	GN-08 GREEN
006	OR-06 ORANGE
007	GY-95 GRAY
008	GY-08 GRAY





LOCKWASHER



LOCKING RING



KNURLED NUT



NOTES

- ① FURNISHED UNASSEMBLED
- 2 - TERMINATION WILL ACCEPT CRIMP CONTACT CONFORMING TO M39029/1-101
- ③ MATTE FINISH
- ④ BRIGHT FINISH
- ⑤ SUFFIX MUST BE ADDED FOR DESIRED LEVER STYLE AND COLOR. (EXAMPLE: 112TW19-1-A001)

THIRD ANGLE PROJECTION

SCALE 2:1

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED TOLERANCES ARE

ONE PLACE () ± 0

TWO PLACE (00) ± 0

THREE PLACE (000) ± 0

ANGLES ±

WEIGHT 0.42 LB MAX

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[112TW19-7A-001](#)