


SOT23 PNP SILICON PLANAR HIGH VOLTAGE TRANSISTOR

ISSUE 3 - OCTOBER 1995

FMMT597

COMPLEMENTARY TYPE FMMT497
PARTMARKING DETAIL - 597



ABSOLUTE MAXIMUM RATINGS.

PARAMETER	SYMBOL	VALUE	UNIT
Collector-Base Voltage	V_{CBO}	-300	V
Collector-Emitter Voltage	V_{CEO}	-300	V
Emitter-Base Voltage	V_{EBO}	-5	V
Peak Pulse Current	I_{CM}	-1	A
Continuous Collector Current	I_C	-0.2	A
Base Current	I_B	-200	mA
Power Dissipation at $T_{amb}=25^{\circ}C$	P_{tot}	500	mW
Operating and Storage Temperature Range	$T_j; T_{stg}$	-55 to +150	$^{\circ}C$

ELECTRICAL CHARACTERISTICS (at $T_{amb} = 25^{\circ}C$).

PARAMETER	SYMBOL	MIN.	MAX.	UNIT	CONDITIONS.
Collector-Base Breakdown Voltage	$V_{(BR)CBO}$	-300		V	$I_C = -100\mu A$
Collector-Emitter Breakdown Voltage	$V_{(BR)CEO}$	-300		V	$I_C = -10mA^*$
Emitter-Base Breakdown Voltage	$V_{(BR)EBO}$	-5		V	$I_E = -100\mu A$
Collector Cut-Off Current	I_{CBO}		-100	nA	$V_{CB} = -250V$
Emitter Cut-Off Current	I_{EBO}		-100	nA	$V_{EB} = -4V$
Collector-Emitter Cut-Off Current	I_{CES}		-100	nA	$V_{CES} = -250V$
Emitter Saturation Voltages	$V_{CE(sat)}$		-0.25 -0.25	V V	$I_C = -50mA, I_B = -5mA$ $I_C = -100mA, I_B = -20mA^*$
	$V_{BE(sat)}$		-1.0	V	$I_C = -100mA, I_B = -20mA^*$
Base-Emitter Turn-on Voltage	$V_{BE(on)}$		-0.85	V	$I_C = -100mA, V_{CE} = -10V^*$
Static Forward Current Transfer Ratio	h_{FE}	100 100 100	300		$I_C = -1mA, V_{CE} = -10V$ $I_C = -50mA, V_{CE} = -10V^*$ $I_C = -100mA, V_{CE} = -10V^*$
Transition Frequency	f_T	75		MHz	$I_C = -50mA, V_{CE} = -10V$ $f = 100MHz$
Output Capacitance	C_{obo}		10	pF	$V_{CB} = -10V, f = 1MHz$

*Measured under pulsed conditions. Pulse width=300 μs . Duty cycle $\leq 2\%$

Spice parameter data is available upon request for this device

FMMT597

TYPICAL CHARACTERISTICS

