



Order symbol: CAB ABS 405020 G
Product nbr: 8183361
Description: Cabinet, ABS, Grey door
Remarks: Latches on the short side

EAN: 6418074020406
El. number:
Finland: 3424322
Denmark: 8212020744
Italy: 7811050
Sweden: 2540079
Norway:

Including: Cabinet base, door with EPDM gasket, latches, screws for mounting plate/DIN-rail and corner plugs.

Sample photo

Dimensions:		Length	Width	Height	Rating:
mm:		500	400	200	Ingress Protection (EN 60529): IP 65
inch:		19.7	15.7	7.9	Impact Resistance (EN 62262): IK 08
Materials:					Electrical insulation: Totally insulated
Material:		ABS			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:		RAL 7035			Flammability Rating (UL 746 C 5): UL 94 HB
Cover colour:		RAL 7035			Glow Wire Test (IEC 695-2-1) °C: 650
Gasket material:		EPDM			NEMA Class: NEMA 1, 4, 4X, 12, 13
Temperatures:					Certificates:
Short term:		-40 ... 80 °C			Fimko
Continuous:		-40 ... 60 °C			Europe EN 62208: 2003
Short term:		-40 ... 175 °F			Gost R
Continuous:		-40 ... 140 °F			
Accessories:					
EKIV 54		Mounting plate			
EKIV 37		DIN-35 Mounting rail			
DS35370E1		DIN-35 Mounting rail			
EKIV 47		DIN-35 Mounting rail			
DS35470E1		DIN-35 Mounting rail			
FP A 54		Swing-out door/Front plate			
MB 12225 AL		Swing door set			
FP 54		Front plate			
FP 18X2-54		Front plate			
DRF 54		DIN rail frame set			

